

Ground Fault Products

Portable GFCI Cord Drops



GFP201251P



Extra Heavy Duty Industrial Circuit Guard® Portable GFCI - Type 4X

Description	Cord length	Amperage	Voltage	Catalog Number
Portabe GFCI Cord Drop with Black	10' (304.8 cm)	20A	125V AC	GFP201251P
SEOOW Cable and Kellems Mesh	10' (304.8 cm)	20A	250V AC	GFP202501P
Strain Relief. Automatic Set	10' (304.8 cm)	20A	208V AC	GFP202081P
	10' (304.8 cm)	30A	125V AC	GFP301251P
	10' (304.8 cm)	30A	250V AC	GFP302501P
	10' (304.8 cm)	30A	208V AC	GFP302081P
	10' (304.8 cm)	30A	3Ø 208V AC	GFP302083P
	10' (304.8 cm)	30A	3Ø 240V AC	GFP302403P
	25' (762.0 cm)	20A	125V AC	GFP201251P25
	25' (762.0 cm)	20A	250V AC	GFP202501P25
	25' (762.0 cm)	20A	208V AC	GFP202081P25
	25' (762.0 cm)	30A	125V AC	GFP301251P25
	25' (762.0 cm)	30A	250V AC	GFP302501P25
	25' (762.0 cm)	30A	208V AC	GFP302081P25
	25' (762.0 cm)	30A	3Ø 208V AC	GFP302083P25
	25' (762.0 cm)	30A	3Ø 240V AC	GFP302403P25

See Page K-19 for product specifications and dimensions



GFHW86108

Extra Heavy Duty Industrial Circuit Guard® Hard Wired 60A GFCI - Type 4X

Description	Amperage	Voltage	Catalog Number
60 Amp Single or 3 -Phase GFCI Class A Automatic Set	60A	1Ø or 3Ø 208V AC	GFHW86108

Specifications

Rated Voltage:	208VAC (150V to ground max) "Class-A"
Operating Voltage Range:	85% to 110% of rated
Current:	Up to 60 Amps or Device Rating
Horsepower:	Up to 20 HP 3Ø/ 7.5HP 1Ø
Frequency:	60 Hz.
Trip Level:	5mA +/- 1mA
Response Time	25ms max at 500Ω fault
Power up:	Auto: Output is on immediately upon power up
Display:	Illuminated TEST/RESET pushbutton, triple indication of Protecting & Power-out versus Fault
Enclosure:	High impact polycarbonate 8x10x4 inch, NEMA 4X
Operational Temperature:	-35° C to 50° C (-31° F to 122° F)
Connections:	60" splicing lead wires and 1" NPT conduit fittings for integration to flexible, EMT, PVC, or burial conduit
Short Circuit:	10KA (panel tested), higher with appropriate fusing
Dielectric With stand:	1500 VRMS across contact, 4000V to enclosure
Voltage Surge With stand:	4000V/2000A 20-times per ICE 6100D-4-5
Agency:	Listed to UL943

