

Ground Fault Products



Features and Benefits

Extra Heavy Duty Industrial and Hospital Grade GFCI Receptacles Tamper-Resistant and Weather Resistant

- Corrosion resistant construction includes nickel plated brass mounting strap, line/load terminals, face contacts, internal contacts and wiring terminal clamps; stainless steel terminal and mounting screws
- Selective double layer conformal coating of printed circuit board, critical components and connections
- Superior materials including polyester "V0" thermoplastic housing (UV Resistant); 7025 high thermal conductivity copper alloy contacts
- Dust Test (UL 943) compliant; resistance to contaminants, moisture and dust



AUTOGUARD® Self Test GFCI Receptacles Tamper-Resistant and Weather Resistant



Description	Rating	Color	Industrial	Industrial Hospital Grade
Extra Heavy Duty Industrial Ground Fault Receptacle 15A 125V Feed Through Tamper and Weather Resistant		Black	GFSG5262BLK	GFSG8200BLK
		Brown	GFSG5262	GFSG8200
		Gray	GFSG5262GRY	GFSG8200GRY
		Ivory	GFSG5262I	GFSG8200I
		Red	GFSG5262R	GFSG8200R
Extra Heavy Duty Industrial Ground Fault Receptacle 20A 125V Feed Through Tamper and Weather Resistant		Black	GFSG5362BLK	GFSG8300BLK
		Brown	GFSG5362	GFSG8300
		Gray	GFSG5362GRY	GFSG8300GRY
		Ivory	GFSG5362I	GFSG8300I
		Red	GFSG5362R	GFSG8300R
		White	GFSG5362W	GFSG8300W

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with both a matching color thermoplastic wallplate, and a SS26 302/304 super stainless steel wallplate. 20 amp feed-through capability. Note – yellow version comes with SS plate only See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.

GFCI Receptacle Specifications per GFCI Products Listed (Pages K-3 to K-8)

Trip Level	4 to 6 mA.
Trip Time	.025 second nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15% (102V to 132V).
Amperage	15A/20A, 20A Feed-Thru.
Maximum Interrupting Capacity	10,000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Dust Resistant	Meets UL 943, section 6.20 for resistance to dust contaminants
Corrosion Resistant	Meets UL 943, section 6.21 for resistance to corrosion
FCC Part 15 Class B	Certified conformance to radiated and conducted emission testing per FCC
Immunity to noise	Exceed UL 943 of .5V over a frequency range of 150kHz to 230MHz disturbances
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978 CSA Certified.
Codes	Meets all NEC® and CEC requirements. NEMA WD-6 ANSI 73.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).