

# SpikeShield® Power Quality Products

## Features and Benefits

### Heavy Duty Relocatable Power Taps for Industrial, Commercial and Retail Applications

- Heavy-duty 18 gauge galvanized steel housing with durable powder coat finish
- Available in 15A and 20A configurations
- 6 Ft. and 15 Ft. cord length options for all models
- 15A models feature a 45° angle plug
- 20A models feature a 90° angle plug
- All models come with built in circuit breaker for over current protection
- Church-key openings on the back of the RPT for temporary mounting ease
- White powder coat RPTs feature UL Listed Hospital Grade, Tamper-Resistant Receptacles
- Black powder coat RPTs feature Specification Grade, Tamper-Resistant Receptacles



Listed to UL1363



HBL6RPT620

HBL6RPT6BK



#### Housing Design and Safety

- Heavy-duty 18 gauge galvanized steel housing with durable powder coat finish
- White or Black powder coat RPTs feature Tamper-Resistant Receptacles
- Church-key openings on the back of the RPT for temporary mounting ease



#### Contacts and Cord

- All models come with built in circuit breaker for over current protection
- 6 ft. or 15 ft. cord length
- 45° angle plug (15A series)
- 90° angle plug (20A series)

### Relocatable Power Tap with Hospital Grade Tamper-Resistant Receptacles

Description	# of Outlets	Cord Length	Color	15A 125V	20A 125V
RPT, Heavy Duty Metal Housing	6	6 Ft.	White	<b>HBL6RPT6</b>	<b>HBL6RPT620</b>
	6	15 Ft.	White	<b>HBL6RPT15</b>	<b>HBL6RPT1520</b>

### Relocatable Power Tap with Specification Grade Tamper-Resistant Receptacles

Description	# of Outlets	Cord Length	Color	Catalog Number	20A 125V
RPT, Heavy Duty Metal Housing	6	6 Ft.	Black	<b>HBL6RPT6BK</b>	<b>HBL6RPT620BK</b>
	6	15 Ft.	Black	<b>HBL6RPT15BK</b>	<b>HBL6RPT1520BK</b>

### Relocatable Power Tap Specifications

#### Electrical Specifications

Current	15A	20A
Voltage	125V	125V
Frequency	60Hz	60Hz
Over Current Protection	15A CB	20A CB

#### Physical Specifications

Length	11.12" (282.4)
Width	2.22" (56.4)
Height	1.6" (40.5)

#### Environmental Specifications

Operating Temperature	-40°F to 160°F
	(-40°C to 70°C)

#### Certifications

cULus Listed UL1363 RPT



HBL6RPT6



HBL6RPT620BK