

SpikeShield® Power Quality Products

Specifications

320kA, 160kA and 120kA Service/Branch Panel Protection (Type 1 SPD)

Electrical Specifications

320kA Panel	160kA Panel	SCCR [◇]	I _n	MCOV †	Voltage Protection Rating (VPR)							
					L-N		L-G		N-G		L-L	
					320kA	160kA	320kA	160kA	320kA	160kA	320kA	160kA
HBL3P320B	HBL3P160B	200kA	20kA	320/160	900	700	900	700	800	600	1500	1000
HBL4P320B	HBL4P160B	200kA	20kA	320/160	900	700	900	700	800	600	1500	1000
HBL5P320B	HBL5P160B	200kA	20kA	320/160	N/A	N/A	1500	1200	N/A	N/A	2000	1500
HBL6P320B	HBL6P160B	200kA	20kA	320/160	1000/1200	900/1500	900/1200	900/1200	800	700	1500	1500
HBL8P320B	HBL8P160B	200kA	20kA	320/160	1500	1200	1500	1200	1200	1200	2000	2500
HBL9P320B	HBL9P160B	200kA	20kA	320/160	N/A	N/A	1800	1800	N/A	N/A	2500	2500
HBL10P320B	HBL10P160B	200kA	20kA	320/160	1500	1500	1500	1500	1500	1500	2500	2500
HBL11P320B	HBL11P160B	200kA	20kA	320/160	N/A	N/A	3000	2500	N/A	N/A	2500	2500

Note: Specification applies to both (B) and (DB) series.

Product Specifications

Max. Surge Current per Phase:	320kA and 160kA	Terminal Accommodation:	#10 AWG to #2 AWG
Max. Operating Temperature:	-20°F to 149°F (-4°C to 65°C)	Operating Frequency:	50/60 Hz
Diagnostics Indicators:	Push to Test Diagnostics, Red and Green Status LEDs, Dry Contacts, Audible Alarm and Surge Counter	EMI/RFI:	Up to -30dB
		Housing Rating:	NEMA 1
		Listing:	cULus UL1449 4th edition type 1 SPD, UL1283 5th edition, CSA C22.2 No. 269.2-13 1st edition, CSA 22.2, No. 8-13, 5th edition.
Dimensions:	11.04"W x 22.44"H x 7.87"D (320kA); 11.04"W x 20.32"H x 5.32"D (160kA)		
Weight:	37 lbs. Max. (320kA); 27 lbs. Max. (160kA)		

Wired-In Branch Panel Protection 100,000 Peak Amp Capacity (Type 2 SPD)

Electrical Specifications

Catalog Number	SCCR [◇]	I _n	MCOV †	Voltage Protection Rating (VPR)			
				L-N	L-G	N-G	L-L
HBL3W100C	200kA	20kA	150/270	900	1200	700	1500
HBL4W100C	200kA	20kA	150/270	900	1200	700	1500
HBL5W100C	200kA	20kA	300	N/A	N/A	N/A	1500
HBL6W100C	200kA	20kA	275/150	1000	1200	700	1500
HBL8W100C	200kA	20kA	320/640	1200	2000	1000	2500
HBL9W100C	200kA	20kA	640	N/A	N/A	N/A	3000
HBL10W100C	200kA	20kA	390/780	1500	2500	1500	3000
HBL11W100C	200kA	20kA	780	N/A	N/A	N/A	3000

Product Specifications

Max. Surge Current per Phase:	100kA	Terminal Accommodation:	#10 AWG 18.0" Wire Leads
Max. Operating Temperature:	-40°F to 140°F (-4°C to 60°C)	Operating Frequency:	50/60 Hz
Diagnostics Indicators:	Green Status LEDs, Dry Contacts, Audible Alarm	EMI/RFI:	Up to -30dB
		Housing Rating:	Type 4X
Dimensions:	9.9"W x 4.8"H x 3.1"D	Listing:	cULus UL 1449 4th edition type 2 SPD, UL1283 (Wye prod. only), CSA C22.2 NO. 8-M1986
Weight:	4.78 lbs	Warranty:	10 year

Wired-In High-Quality Surge Protective Device, Surge Arrestors, Single Phase and Three Phase (Type 2 SPD)

Electrical Specifications

Catalog Number	SCCR [◇]	I _n	MCOV †	Voltage Protection Rating (VPR)			
				L-N	L-G	N-G	L-L
HBL3W50	25kA	10kA	150 (L-N, L-G), 300 (L-L)	700	800	N/A	1200
HBLSDSA36	22kA	10kA	150	700	N/A	N/A	1200
HBL4SA40	200kA	10kA	180 (L-N), 360 (L-L)	700	N/A	N/A	1200
HBL5SA40	200kA	10kA	360 (L-L)	N/A	N/A	N/A	1200
HBL8SA40	200kA	10kA	420 (L-N), 840 (L-L)	1500	N/A	N/A	2500
HBL9SA40	200kA	10kA	840 (L-L)	N/A	N/A	N/A	2500
HBL10SA40	200kA	10kA	510 (L-N), 1020 (L-L)	1800	N/A	N/A	3000
HBL11SA40	200kA	10kA	1020 (L-L)	N/A	N/A	N/A	3000

Product Specifications

Service Voltage	Single Phase	Single Phase	Three Phase
Max. Surge Current per Phase:	50kA	36kA	40kA
Max. Operating Temperature:	-40°F to 149°F (-40°C to 65°C)	-40°F to 149°F (-40°C to 65°C)	-40°F to 149°F (-40°C to 65°C)
Diagnostics Indicators:	Green Status LED per line	Green Status LED per line	Green Status LED per line
Dimensions:	3.0"W x 3.6"H x 2.67"D	2.25"W x 2.25"H x 1.94"D	3.60"W x 3.0"H x 2.64"D
Weight:	1.8 lbs.	.72 lbs.	1.8 lbs.
Terminal Accommodation:	#12 AWG Wire Leads	#14 AWG Wire Leads	#12 AWG Wire Leads
Frequency:	50/60 Hz	50/60 Hz	50/60 Hz
EMI/RFI:	Up to -30dB	Up to -30dB	Up to -30dB
Housing Rating:	Type 4X	Type 4X	Type 4X
Listing:	UL1449 4th edition	UL1449 4th edition	UL1449 4th edition
Warranty:	10 year	2 year	2 year

◇SCCR: Short Circuit Current Rating | † MCOV: Maximum Continuous Operating Voltage | ‡ I_n: Nominal discharge current