

Features and Benefits

Stainless Steel Weatherproof Flip Covers

Stainless steel weatherproof flip covers are suitable for use in applications where corrosion and sanitation are vital concerns. Heavy duty 316 stainless steel provides an excellent finish and superior corrosion resistance in all applications. Models listed are typically used in indoor/outdoor applications such as, food/chemical processing, pharmaceutical and water treatment facilities.

- Manufactured in heavy duty 316 stainless steel for increased corrosion resistance
- Polished finish for a clean aesthetic appearance
- Smooth surfaces to allow ease of cleaning
- Duplex and GFCI versions
- UL Type 3R:
 - Rain-tight and sleet (Ice) resistant
 - Self-closing lid
- UL Type 4X:
 - Watertight, dust-tight and corrosion resistant for wash-down application
 - Latching cover



Industries Commonly Served

- Food and Beverage Production and Distribution
- Chemical Plants
- Water and Wastewater Treatment
- Pharmaceuticals and Cosmetics
- Refining and Extraction Sites
- Petrochemical Operations
- Marine and Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments

1-Gang Stainless Steel Weatherproof Flip Covers

Description	Catalog Number
1 Gang, Stainless Steel Duplex Cover, 3R	HBLSS83R
1 Gang, Stainless Steel GFCI Cover, 3R	HBLSS263R
1 Gang, Stainless Steel Duplex Cover, 4X	HBLSS84X
1 Gang, Stainless Steel GFCI Cover, 4X	HBLSS264X



HBLSS83R

1-Gang Stainless Steel While-In-Use Weatherproof Cover

Description	Catalog Number
1 Gang, Stainless Steel GFCI Cover, 3R	HBLSS26WIS



HBLSS263R



HBLSS84X



HBLSS26WIS

Specifications

Cover	Stainless Steel
Base	Stainless Steel
Hinge Pin	Stainless Steel
Spring	Stainless Steel
Base Gasket	Elastomer
Cover Gasket	Elastomer
Back Gasket	Eva Form
Ground Screw	Steel, Zinc Plated
Mounting Screw	Stainless Steel

Product Dimensions

Catalog Number	Height	Width	Depth	Opening
HBLSS83R	3.04" (77.2)	4.85" (123.2)	.88" (22.4)	2.62" (66.5)
HBLSS263R	3.04" (77.2)	4.85" (123.2)	.88" (22.4)	2.76" (70.0)
HBLSS84X	3.04" (77.2)	4.85" (123.2)	.88" (22.4)	2.62" (66.5)
HBLSS264X	3.04" (77.2)	4.85" (123.2)	.88" (22.4)	2.76" (70.0)
HBLSS26WIS	6.54" (166.1)	3.70" (93.9)	2.31" (58.7)	7.57" (192.3)

Dimensions in Inches (mm)