

Aluminum Ladder Tray

Straight Sections



Features

- For use indoors, outdoors or in harsh environments
- Aluminum Alloy 6063
- NEMA Class B or C
- Splice plates and hardware included*
- 12 foot sections with 9 inch rung spacing
- Rungs are welded to stringers for strength and continuity
- Use with Class 1 Fittings

Rail Height	Width	NEMA Class	NEMA Safe Load (lb/ft)	AMP Rating	Catalog Number
4"	6"	B	81	1000	LTB406
		C	100	1000	LTC406
	9"	B	81	1000	LTB409
		C	100	1000	LTC409
	12"	B	81	1000	LTB412
		C	100	1000	LTC412
	18"	B	81	1000	LTB418
		C	100	1000	LTC418
	24"	B	81	1000	LTB424
		C	100	1000	LTC424
	30"	B	81	1000	LTB430
		C	100	1000	LTC430
	36"	B	81	1000	LTB436
		C	100	1000	LTC436
6"	6"	B	89	1200	LTB606
		C	105	1200	LTC606
	9"	B	89	1200	LTB609
		C	105	1200	LTC609
	12"	B	89	1200	LTB612
		C	105	1200	LTC612
	18"	B	89	1200	LTB618
		C	105	1200	LTC618
	24"	B	89	1200	LTB624
		C	105	1200	LTC624
	30"	B	89	1200	LTB630
		C	105	1200	LTC630
	36"	B	89	1200	LTB636
		C	105	1200	LTC636

Note: 4" Rail Height has a Load Depth of 3". 6" Rail height has a Load Depth of 5". Total Width is Width + 1.5".

*Included hardware is geomet-plated steel.

