




## SystemOne Recessed 8\*/10-Gang Rectangular Floor Boxes, Covers and Plates For Use In Raised Access or Wood Floors

AFB series boxes are available from our factory as pre-wired assemblies with CONNEXION modular plug-n-play system

Style		
Box Type		
Standard	<b>AFB10G55</b>	
Chicago (No Knockouts)	<b>AFB10G55CHI</b>	
Min. Depth from Top of Floor Tile	5.95" (151.1)	
Cubic Inch (cm <sup>3</sup> ) Capacity per Gang	(2) 25 cu. in. (407.9 cm <sup>3</sup> ), (2) 50 cu. in. (819.4 cm <sup>3</sup> ), (2) 71 cu. in. (1163.5 cm <sup>3</sup> )	
Dimensions – A	5.74" (145.9)	
Dimensions – B	11.11" (282.2)	
Dimensions – C	10.66" (270.7)	
KO Trade Size: Ends	(2) ½", ¾", (2) ¾", 1", 1¼", 1½", (2) 1", 1¼", 1½", 2"	
Sides	(4) ¾", 1", 1¼", 1½"	
Bottom	(2) ½", ¾", (4) ½", ¾", 1", 1¼"	
Floor Thickness	.56" (1.2) - 2.12" (53.8)	
Cover Family	Rectangular	
Temporary Cover Included	✓	

Note: UL File Number E31999.

### Rectangular Covers





















(for use with raised access tiles and wood floors)

- Die cast construction available in five finishes
- UL 514A listed
- Maximum static load of 1500 lbs with 2x safety factor\*\*

Finish	Surface Style Covers	
	Without Insert	With Insert
Aluminum Powder Coat	<b>10GAFBCVRALU</b>	<b>10GAFBCVRALUC</b>
Black Powder Coat	<b>10GAFBCVRBK</b>	<b>10GAFBCVRBK</b>
Brass Powder Coat	<b>10GAFBCVRBRS</b>	<b>10GAFBCVRBRSC</b>
Bronze Powder Coat	<b>10GAFBCVRBRZ</b>	<b>10GAFBCVRBRZC</b>
Satin Nickel Powder Coat	<b>10GAFBCVRNK</b>	<b>10GAFBCVRNKC</b>

Note: \*\*Load applied through a 3 in. (76mm) mandrel in center of the cover.

### Plates for Use in SystemOne 8\*/10-Gang Floor Boxes

Plate Style	(1) Decorator Opening	(1) Duplex Opening	Blank	Decorator Opening Plate Including Hubbell ISF6GY	(2) Openings to Accommodate (6) Ortronics TracJack®	
Cat. No.	<b>FB10MPREC</b>	<b>FB10MPDUP</b>	<b>FB10MPBNK</b>	<b>FB10MPKEY</b>	<b>FB10MPTRAC</b>	
						
Plate Style	(2) Decorator	(2) Duplex Openings	(4) Extron® MAAP Modules	(4) Extron® AAP Modules	For (6) 1U Hubbell iStation Modules	Cable Feed Through with Bushing
Cat. No.	<b>FB10MP2A</b>	<b>FB10MP2E</b>	<b>FB10MPMAAP</b>	<b>FB10MPAAP</b>	<b>FB10MP2B</b>	<b>FB10MPFT</b>
						
Plate Style	(1) Twist-Lock® Opening 1.60 in. Dia. (Uses 2-Gangs)	(1) Simplex Opening 1.40 in. Dia. (Uses 2-Gangs)	(2) Twist-Lock® Opening 1.60 in. Dia. (Uses 3-Gangs)	(2) Simplex Opening 1.40 in. Dia. (Uses 3-Gangs)	(1) Opening for Appliance Receptacle (Uses 3-Gangs)	
Cat. No.	<b>FB10TLA</b>	<b>FB10TLX</b>	<b>FB10TLB</b>	<b>FB10TLY</b>	<b>FB10MP3GAPP</b>	
						
Plate Style	(3) Twist-Lock® Opening 1.60 in. Dia. (Uses 5-Gangs)	(3) Simplex Opening 1.40 in. Dia. (Uses 5-Gangs)	(2) 2-Gang. Meets NEMA Spacing. Ideal for Crestron® DM-TX Product and Power (Uses 5-Gangs)	(4) Single Service Openings Utilizing NEMA Wallplate (Uses 5-Gangs)		
Cat. No.	<b>FB10TLC</b>	<b>FB10TLZ</b>	<b>FB10MPNEMA2XG*</b>	<b>FB10MPNEMA4G*</b>		
						

Note: \*Use with FB10MPNEMA2XG and/or FB10MPNEMA4G for 8-gang configuration.

Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. FSR® is a registered trademark of FSR Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

Dimensions in Inches (mm)