



**BRP42**

Width: 10.125"

Height: 42"

## Bristol Park ordering guide

Bollards & Columns



## ordering logic

### model

BRP42	Bristol Park
-------	--------------

### lens material

<input type="checkbox"/>	A	acrylic
<input type="checkbox"/>	P	polycarbonate

### lens finish

<input type="checkbox"/>	C	clear
<input type="checkbox"/>	F	frosted
<input type="checkbox"/>	W	white

### source

<input type="checkbox"/>	UL	unlighted
<input type="checkbox"/>	LED	17, 24 & 48W
<input type="checkbox"/>	PSMH	50 - 70W
<input type="checkbox"/>	HPS	50 - 70W
<input type="checkbox"/>	CF	13 - 42W

### optics

<input type="checkbox"/>	IND5	indirect type V (LED)
<input type="checkbox"/>	INL	internal louvers
<input type="checkbox"/>	ENL	external louvers
<input type="checkbox"/>	GR3	glass refractor type III
<input type="checkbox"/>	GR5	glass refractor type V
<input type="checkbox"/>	BL	bare lamp

### electrical options

<input type="checkbox"/>	FS	fusing
<input type="checkbox"/>	PEC	photocell
<input type="checkbox"/>	QRS	quartz restrike
<input type="checkbox"/>	IQ	lamp/ballast diagnostics
<input type="checkbox"/>	LSP	lightning surge protector

### style options

<input type="checkbox"/>	CES	chain eye, single
<input type="checkbox"/>	CED	chain eye, double

### model (cont)

BRP42	Bristol Park
-------	--------------

### mounting options

<input type="checkbox"/>	AB	anchor base
<input type="checkbox"/>	DBE	direct burial extension

### color (see page 33 for additional information)

<input type="checkbox"/>	BB	black
<input type="checkbox"/>	BZ	bronze
<input type="checkbox"/>	BG	green
<input type="checkbox"/>	BW	white
<input type="checkbox"/>	BY	gray
<input type="checkbox"/>	RAL	RAL _____
<input type="checkbox"/>	OTHER	_____

### footnotes:

1. Medium socket is standard for all HID sources.
2. IND optics require LED source, LED source requires IND optics.
3. Factory suggests that BL option is selected only when a low wattage source is used in conjunction with non-clear lenses.
4. LED and CF sources utilize a 120-277 voltage-sensing electronic driver, HID sources utilize a Quad-Tap (120, 208, 240 & 277V) core & coil magnetic ballast. 12VDC LED drivers are available for solar power assembly integration, consult factory.
5. LED source shall be supplied at 4500K (CCT), specify is other color temp. is required (minimum quantities may apply).
6. Chain eye, unit only.