

Contemporary LED Wall Wash

RECESSED ARCHITECTURAL

FEATURES

- Narrow 3" aperture creates clean finished appearance
- Proprietary optical design provides excellent vertical uniformity while maintaining visual comfort
- Multiple optical distributions for varying wall wash applications
- 60,000 hour LEDs at L80 (up to 150,000 hours projected life) for reduced maintenance
- Four LED color choices and standard 80 CRI
- Optional 90 CRI for color sensitive applications
- Six lumen packages with outputs up to 1300 Lm/ft
- Best in class efficacy with up to 116 LPW
- Multiple driver options to satisfy different applications
- LED modules and electrical accessible from below
- QR code traceability
- Integral battery pack optional on most models
- DesignLights Consortium® (DLC) qualified; see www.designlights.org
- Five year warranty (Terms and Conditions apply)



LED



createchange

ORDERING INFORMATION

CWW	-		-		-		-		-	
MODEL	CRI	LUMEN OUTPUT	CEILING TYPE	DRIVER	OPTIONS					
CWW Contemporary LED Wall Wash	Blank >80 9 >90 ¹	XW Extra Low Watt VW Very Low Watt MW Medium Low Watt LW Low Watt ^{6,7} ML Medium Lumen ^{5,7} See Product Availability Table below.	G Grid SG Slot Grid F Drywall Flange	E Fixed Output ED 0-10V Dimming ED1 0-10V 1% Dimming ESD Step Dimming ^{2,4} LUT5 Hi-lume 1% EcoSystem LED driver with Soft-on, Fade-to-Black dimming technology ^{2,3,4} LUTH 5-Series EcoSystem LED driver ^{2,3,4}	ELL14 Emergency Battery Pack, 1400 Lumens ^{2,3,8} C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex GLR Fast Blow Fuse CP Chicago Plenum NYC NYC Compliant	DISTRIBUTION				
SIZE	COLOR TEMP									
2 2'	30 3000K									
4 4'	35 3500K 40 4000K 50 5000K									
VOLTAGE										
U 120V-277V										
347 347V										

¹ Not available with 2' 347V & LUT drivers

² Not available in 347V

³ For compatibility with Dual-Lite inverters, contact Hubbell Lighting Representative.

⁴ ESD, LUT5, and LUTH not compatible with 2' Drywall Flange (F) option.

⁵ Not compatible with thru wiring configuration.

⁶ Lumen package not available with ELL14 Emergency backup in 2' configuration

⁷ Lumen package not available with ELL14 Emergency backup in 4' configuration

⁸ Not available with 2' drywall flange (F) option

PRODUCT AVAILABILITY

SIZE	LUMEN PACKAGE	NOMINAL LUMENS	NOMINAL WATTS	LUMENS PER WATT
2	VW	1370 - 1539	15	90-103
	MW	1788 - 2067	20	87-102
	LW	2456 - 2806	27	91-103
4	XW	2554 - 2880	25	103-116
	VW	3119 - 3523	31	103-114
	MW	3430 - 3906	35	98-111
	LW	3901 - 4645	40	98-116
	ML	4712 - 5458	50	95-106

Nominal lumen range represents 3000K through 5000K. Lumens vary according to color temperatures, optics, and other factors. See photometric test(s).

