What is **REMOTE CAPACITY**?

Remote capacity models provide means for delivering excess DC power (wattage) to additional emergency signage and emergency lighting equipment during power outages. Any combination of remote lamp heads (refer to the remote head section of this catalog) and other equipment such as Dual-Lite Exit Signs with the '-DC' remote operation option (see LX, SE, LN4X or LED Series) may be added to the system as long as the total sum of the remote equipment wattage does not exceed the rated wattage capacity of the source unit.

Example: the AS80 has 65.6 watts of available remote capacity (80 watts minus 14.4 watts (two standard 7.2w integral lamp heads)). Any combination of remote lamp heads and exit signs (with the -DC option) may be added up to the 65.6 watts of extra capacity.



3.60

TOTAL WATTAGE CAPACITY REMAINING*

* The National Electric Code limits voltage drop to 5% of nominal. Actual results may vary. Circuit runs must be of sufficient capacity to maintain operating voltage when remote fixtures and/or exit signs are connected to the emergency lighting unit. Refer to the voltage drop tables for sizing and distance of wire run.





Indoor Remote Lighting Heads

SRH Series

Injection molded thermoplastic lamphead/round mounting plate assemblies. Mounts to $3\frac{1}{2}$ " octagonal or single gang boxes. For use with most commercial or industrial emergency fixtures. Standard finish is available in white or black. Single and twin lamp fixtures with a choice of incandescent or halogen PAR 36 lamps.







Outdoor Remote Lighting Heads

OMS Series

Outdoor aluminum spot with sealed lamp and swivel assembly. Furnished with round gasketed aluminum mounting plate. Mounts to $3 \rlap{l}_2$ " octagonal boxes.

ORDERING INFOR	MATION		
OMS			
MODEL	HEADS	FINISH	
	S Single	W White	0605 6 volt, 5.4 Watts Incandescent ¹
	D Double	B Black	0607 6 volt, 7.2 Watts Incandescent ¹
			0608 6 volt, 8 Watts Halogen
			0612 6 volt, 12 Watts Halogen
			0618 6 volt, 18 Watts Incandescent
			0620 6 volt, 20 Watts Halogen
			0625 6 volt, 25 Watts Incandescent
			1207 12 volt, 7.2 Watts Incandescent ¹
			1208 12 volt, 8 Watts Halogen
			1212 12 volt, 12 Watts Halogen
			1218 12 volt, 18 Watts Incandescent
			1225 12 volt, 25Watts Incandescent
			1235 12 volt, 35 Watts Incandescent
¹ Sealed Beam Type La	mp		1250 12 volt, 50 Watts Halogen

Replacement lamp part numbers and photometrics are available on the web at www.dual-lite.com.

Decorative Indoor Remote Lighting Heads

CPR Series

Injection molded thermoplastic decorative lamphead and mounting plate assembly. Mounts to 3¹/₂" octagonal or single gang boxes. Single and twin lamp fixtures. Choice of 5 watt MR16 Halogen, 10 watt MR16 Halogen, or 3 watt LED MR16. Choice of white or black housing finish.





*Only with O3L 3Watt LED available

Decorative Outdoor Remote Lighting Heads

OCR Series

Outdoor UL Wet Location Listed die cast aluminum lamp head and mounting plate assembly. Mounts to 3½" octagonal or square double gang boxes. Single or twin lamp fixtures. Choice of 5 watt MR16 Halogen or 3 watt LED MR16. Choice of white, black, or dark bronze housing finish.





*Only with 03L 3Watt LED available



Indoor Remote Head - CRHI



Outdoor Remote Head - CRHO

LED Remote Heads for Chicago Products

CRH Series

The CRH Series offers emergency lighting for commercial applications. Indoor remotes made of durable 20-gauge steel with glass lens. Outdoor remotes made of die-cast aluminum with glass lens. CRH works with Chicago approved products CCU2RC, CRURC, and CLSC with RC option.





All Metal Remote Lighting Heads

AHD

Stamped aluminum housing with metal swivel. Standard finish available in white or black. Choice of incandescent or halogen PAR 36 lamps.





Available with shatter containment option. Add "-L" to model number for Sealed Beam Lamps PAR36 only. Example: GNXSB0625-L



Environmental Lighting Head

GNX Series

Moisture resistant thermoplastic head in black finish with coated lamp terminals and sealed swivel assembly. Furnished with mounting plate. Available with a choice of incandescent or halogen PAR 36 lamps. Matches N4X series units.



¹Sealed Beam Type Lamp ²Not available on Sealed Beam Type Lamps





High Performance LED Remote

PGR Series

The PGR offers LED performance in a remote fixture. Architectural style for indoor or outdoor application. The unit is illuminated by 4 high power LED's arranged so that in the event of 1 or 2 LED failures the unit will continue to operate. The PGR accepts DC voltage which must be supplied from an external 6-12V DC emergency lighting unit. Housing and mounting plate are constructed of 1/8" die-cast aluminum and sealed with a 1/8" closed-cell silicone gasket. Housing finish is powder coated electro-deposition paint available in four colors: dark bronze, white, platinum silver and black. Remote can be wall-mounted by use of a universal molded-in template. Wired from the j-box through the back or through a conduit entry at the top. U.S. Patent No. D627,916

Input Power Requirements

12 watts at 6vDC, 13 watts at 12vDC

Specific LED information:

Lamp Color: neutral White, 4000K

- Color Rendering Index(CRI): 75
- Total Lamp Output: 445 Lumens min. Initial

LED Lamplife: 48,000 hrs. at 70% of Initial

LZ Series Matching Remote Lighting Heads

LZR

Architectural/commercial design. High performance MR-16 halogen lamps standard or optional energysaving 3 watt MR-16 LED. Mounts to standard electrical boxes using universal mounting plate provided. Fixture housing mounts to back plate in a choice of four mounting positions. Housings secured using locking screws provided. U.S. Patent Nos. D426,334, D441,475 and 6,045,242.

C1D2R/C1D2TR

Suitable for wet and damp location applications. Rated for NEC Class I, Division 2, Groups B, C and D as well as Class I, Zone 2, Group IIA, IIB + H₂ environments. Black housing and head assemblies. Single (C1D2R) and twin (C1D2TR) head models.



SINGLE REMOTE HEAD - WHITE	SINGLE REMOTE HEAD - BLACK	LAMP VOLTS	LAMP WATTS
LZRSW0605	LZRSB0605	6	5
LZRSW0610	LZRSB0610	6	10
LZRSW1205	LZRSB1205	12	5
LZRSW1210	LZRSB1210	12	10
LZRSW0603L	LZRSB0603L	6	3
LZRSW1203L	LZRSB1203L	12	3

TWIN REMOTE HEAD - WHITE	TWIN REMOTE HEAD – BLACK	LAMP VOLTS	LAMP WATTS
LZRDW0605	LZDB0605	6	5
LZRDW0610	LZRDB0610	6	10
LZRDW1205	LZRDB1205	12	5
LZRDW1210	LZRDB1210	12	10



MODEL NUMBERS		LAMPS*	
TWIN HEAD HUB LEFT SIDE ^{1,2}	VOLTS	WATTS	
C1D2TR-6V8W	6	8	
C1D2TR-6V12W	6	12	
C1D2TR-12V8W	12	8	
C1D2TR-12V12W	12	12	
	TWIN HEAD HUB LEFT SIDE ^{1,2} C1D2TR-6V8W C1D2TR-6V12W C1D2TR-12V8W	TWIN HEAD HUB LEFT SIDE ^{1,2} VOLTS C1D2TR-6V8W 6 C1D2TR-6V12W 6 C1D2TR-12V8W 12	

* PAR 36 Halogen sealed beam lamps.

 $^1{\rm Hub}$ Right Side — add "R" to end of model number. Example C1D2R-6V8WR. $^2{\rm Hubs}$ Both Sides — add "F" to end of model number. Example C1D2R-6V8WF.

UNITS ACCESSORIES

Mounting Brackets and Shelves

For mounting of AS Series industrial emergency lighting units.



MOUNTING BRACKETS AND SHELVES			
CAT. NO.	ТҮРЕ	DIMENSIONS	
WB-6	Bracket: use with any AS model		
6000	Shelf: use with AS180 through AS360	11" H × 14" L × 81⁄8" D	
L-6	Shelf: use with AS80 or AS130 only	11" H × 14" L × 8½"D	

Vandal Resistant Shields

For protection against vandalism or accidental damage. Prevents tampering with mountings and lamps.



VANDAL SHIELDS			
CAT. NO.	FOR USE WITH	DIMENSIONS	
VRS VRS-4X*	EZ-2, EZ-2R, LZ, LZ High Capacity, and EXT-122-EM-K Series units.	20"L × 10½"H × 7¾"D	
VRS3	LX and Sempra Series exits.	15½"L×11½"H×4½"D	

* VRS-4X supplied with a neoprene wall gasket

Wire Guards

Offered for most Dual-Lite emergency lights and exits. Constructed of heavy gauge steel, all wire guards are standard with chrome plating. Order as separate line item.





WIRE GUARDS			
CAT. NO.	FOR USE WITH	DIMENSIONS (INSIDE)	
WGLZ	LZ Series (except High-Capacity models).	6¼"H×14"L×4"D	
S6WG	Single remote heads.	8"H×8"L×8"D	
WGEL	EZ-2, EZ-2R, LZ High-Capacity Series and CV Series units. Twin remote heads.	8"H × 20"L × 8"D	
40G	LM Series with top mounted heads and NYXC tandem exits. AS Series, N4X Series and CVEC Series (15 and 30 watt models) units.	18½"H×20"L×12"D	
41G	Delite Cylinder Series and CVEC Series (50 and 100 watt models)	21"H × 23"L × 15"D	
WGLX	EXT-122-EM-K units. Wall mount LX, LED and Sempra Series exits.	10"H × 14"L × 2¼"D	
WGLXC	Ceiling mount LX, LED and Sempra exits	10¼"H × 13¾"L × 3½"D	
WGLXE	End mount LX, LED and Sempra exits	10½"H × 14½"L × 3½"D	
WGTW	Wall mount LT, Freedom LED, HCX, NYDC and NYX Series exits	16"H × 20"L × 7%"D	
WGTCE	Ceiling or end mount LT, HCX and Freedom LED Series exits. Ceiling mount NYDC and NYX Series exits	20"H × 15½"L × 8" D	
WG-MLT	Lite2 Series units. CMX Series exits	115/8"H × 135/8"L × 7"D	

SPECTRON®

Optional Self-Test/Self-Diagnostic Circuitry



Self-Testing Electronics System

Technologically advanced self-testing, self-diagnostic electronics provide increased reliability and decreased maintenance.

All Dual-Lite models ordered with the Spectron option provide:

- Visual indication of AC power status
- Visual indication of all self-diagnostic test cycles
- Visual indication of unit malfunctions including:
 - Battery disconnected
 - Battery fault
 - Charger fault
 - Transfer Fault
 - Lamp Fault

Features

- Meets UL 924 standards for self-testing/self-diagnostic models
- Provides automatic self-diagnostic monitoring and testing of unit operation
- Automatically performs routing maintenance and assures operational readiness at all times
- Monitors charger and lamp operation
- Routine discharge cycles insure optimum battery performance and maximize useful life
- Automatic self-test every 28 days and extended operation self-test every 6 months
- Automatic low voltage disconnect
- Automatic unit transfer in brownout conditions
- Automatic 15-minute time-delay retransfer (TDR) standard on emergency lighting units - allows HID fixtures to come to full brightness before allowing the emergency unit to turn off
- Automatic AC lockout
- Flashing LED indication of unit malfunction
- All detected malfunctions retained in memory until corrected and retested
- Test switch allows system check at any time
- Supports exit sign flashing options



Test Intervals

...the Spectron self-testing/self-diagnostic system conducts tests to verify proper operation continuously and on monthly and semi-annual intervals ...The Spectron System, as required by the National Electrical Code and the National Fire Protection Association, performs all routine test cycles under full load.

Manual tests may also be performed at any time. A malfunction during any self-test will be indicated by the external status indicators.

Continuous

...the Spectron system verifies all functions that are critical for emergency operation.

The diagnostic circuit checks functions such as charger operation, battery connection, voltage, and AC supply line. The Spectron system verifies these functions and compares them to predetermined microcontroller parameters. Operation outside these parameters will cause a visual malfunction indication on the unit's Spectron display panel.

Every 28 days

...the Spectron system conducts a short duration test. This test activates the transfer circuit and discharges the battery, simulating a power failure. The test ensures proper battery capacity and the unit's emergency transfer capability.

Every 6 Months

...the Spectron system conducts an extended selfdiagnostic test cycle with full lamphead illumination. The test simulates a power failure and verifies the unit's operation to code.

At Any Time

...the Spectron system can test for proper operation. This is accomplished by pushing the manual test switch. The microcontroller will cause the unit to switch to emergency operation mode and a self-diagnostic cycle to begin.