

BRP42

Bristol Park




DECORATIVE

FEATURES


- The BRISTOL PARK Bollard is a luminaire with an LED heat sink and an LED engine containing 12 high powered indirect LEDs. The LED engine is concealed in the shaft and pointed upwards into an indirect reflector to eliminate glare. The optics are narrow beams designed to provide glare free indirect lighting.
- The upper housing is a cast aluminum dome top secured to a one-piece cast aluminum top assembly with concealed screws and is available with either a flat top or domed top.
- The Lower Housing is 8" IN DIAMETER and constructed of .125" wall 6063-T5 extruded aluminum which connects to the top of the mounting tenon with internal bolts, inaccessible after installation.
- Lens & Optical System: Beacon LED bollards feature an LED module and heat sink which shall be removable and upgradeable. The drivers shall be mounted on a removable plate and protected by a 20,000 amp transient surge protector.

ORDERING INFORMATION

BRP42							
MODEL BRP42 Bristol Park		LED COLOR 3K 3000K 4K 4000K 5K 5000K	VOLTAGE UNV 120-277V		STYLE OPTIONS CES Chain Eye, Single CED Chain Eye, Double		COLOR BBT Basic Black Textured BMT Black Matte Textured WHT White Textured MBT Metallic Bronze Textured BZT Bronze Textured DBT Dark Bronze Textured GYS Gray Smooth DPS Dark Platinum Smooth GNT Green Textured MST Metallic Silver Textured MTT Metallic Titanium Textured OWI Old World Iron RAL _____
LENS OPTIONS FINISH AC Acrylic, Clear AF Acrylic, Frosted	ENGINE-WATTS 12NB-36 36 Watts		OPTICS IND5 Indirect Type V 360°	MOUNTING OPTIONS AB Anchor Base			



BOLT PATTERN



Visit www.beaconproducts.com for up-to-date availability information