

EZ-2/EZ-2R

Commercial Emergency Light

EMERGENCY LIGHTING



FEATURES

- Emergency unit for surface or recessed commercial applications
- EZ installation with nylon hinges
- High impact, 5VA flame rated, UV stabilized, white thermoplastic housing (EZ-2)
- Heavy gauge galvanized sheet metal housing (EZ-2R)
- Fully adjustable, glare free incandescent lamp heads
- Maintenance-free lead-calcium battery with fully automatic charger
- Temperature range: 20°C to 30°C (68°F to 86°F), damp: 10°C to 40°C (50°F to 104°F)
- UL 924 Listed; UL 924 Damp Location Listed (EZ-2I model only)

ORDERING INFORMATION

EZ-2				
MODEL	MOUNTING	RATING	SELF DIAGNOSTICS	OPTIONS
	Blank Surface R Recessed	Blank Standard Model D Damp Location Listing ¹	Blank None I Spectron Self-test/ Self-diagnostic Electronics (Damp location listed standard on EZ-2I surface mount only)	V Voltmeter ¹

¹EZ-2 only

SPECIFICATIONS


BASE CATALOG NUMBER	ELECTRICAL							
	OUTPUT VOLTS	OUTPUT WATTS		AC INPUT			STANDARD LAMP	REMOTE CAPABILITY
		1.5 HOURS	2 HOURS	VOLTS	AMPS	WATTS		
EZ-2, EZ2R and EZ-2-V	6	10.8	--	120	.080	8.4	5.4W	No
EZ-2I and EZ-2RI	6	14.4	--	120	.080	8.4	7.2W	No
				277	.030	8.8		

ACCESSORIES

MODEL	DESCRIPTION
VRS	Vandal resistant shield
VRS-4X	Vandal resistant shield with neoprene gasket
WGEL	Wire guard
F-CBM	Troffer mounting kit for suspended ceilings (EZ-2R only)


ELECTRONICS

- 120/277 60 Hz VAC operation, test switch and LED AC-On indicator light
- Transformer isolation, surge, transient and low voltage disconnect protection
- Reverse polarity, short circuit and AC lockout protection



EZ-2

A	5 3/4" (14.6 cm)
B	11" (27.9 cm)
C	3 7/8" (9.8 cm)
D	7 3/4" (19.7 cm)
E	9 1/8" (23.2 cm)
F	5" (12.7 cm)
G	6 1/8" (15.6 cm)



EZ-2R



EZ-2R

