

MARSHAL Decorative LED Twin Head Motion Sensor

Attractive security floodlight set. Powerful LED system saves energy and maintenance over traditional lighting sources.

- 2 adjustable heads and 1 adjustable motion sensor
- Replaces twin 150w incandescent lamps
- 180 degree coverage
- 120V/60Hz LED
- Dark Bronze or white finish
- Die-cast aluminum decorative heads
- 120V operation
- Listed to UL1598 for use in wet locations



tradeSELECT®

FLOODLIGHTING

STOCK ORDERING INFORMATION

Catalog Number	Mount	Color	Beam Pattern	Wattage	Voltage	CCT/CRI	Lumens	LPW	Weight lbs. (kg)
ML-2L3K-1-DB	Ceiling/Wall	Dark Bronze	Wide (6x6)	26.6w	120	3000K/83	2104	79	2.2 (1)
ML-2L3K-1-WH		White							

PERFORMANCE INFORMATION

Series Number	Equivalency		Energy Savings	Delivered Lumens	System Watts	Lumens Per Watt	Beam Pattern	CCT/CRI	Voltage
	INCANDESCENT	CFL							
ML-2L3K-1-DB	150W	2x42W	82%	2104	26.6w	79	Wide (6x6)	3000K/83	120

Motion Sensor Only



STOCK ORDERING INFORMATION

Catalog Number	Mount	Color	Description
MS-DB	1/2" threaded	Dark Bronze	180° coverage motion sensor only
MS-WH	1/2" threaded	White	180° coverage motion sensor only

DIMENSIONS

