

Q Series

Quartz Floods – Commercial Grade



- General and accent flood lighting where short burning hours are planned,
- Instant on/off
- 150 to 500w capability
- Die-cast aluminum construction for long life
- Single screw door closure for easy installation
- Tempered glass lens protects lamp
- 1/2" Cast swivel knuckle fits standard boxes and covers
- Wide, uniform beam for even illumination
- 120V lamps are included
- Units offered in dark bronze or white powder paint finish
- Listed to UL1598 for use in wet locations



FLOODLIGHTING

ORDERING INFORMATION

Catalog Number	Wattage/Voltage	Color	Photometry NEMA/IES H° x V°	Weight lbs. (kg)	EPA ft² (m²)
Lamp Included					
Q-150-W	150w/120V	White	6(124°) x 6(124°)	1.4 (0.6)	.14 (.01)
Q-500-B	500w/120V	Bronze	6(100°) x 5(86°)	2.6 (1.2)	.6 (.05)



	A	B	C	D
Q150X	5 7/16"	3 7/8"	5 1/2"	4"
	138 mm	98 mm	139 mm	100 mm
Q500X/ Q300X	3 5/8"	7 23/32"	8 13/16"	
	92 mm	196 mm	227 mm	