



EU Type Examination Certificate CML 23ATEX1002X Issue 0

- 1 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU
- 2 Equipment **APEX C*e Range of Cable Glands**
- 3 Manufacturer **Hawke International (A Division of Hubbell Limited) (A member of the Hubbell Group of Companies)**
- 4 Address Oxford Street West,
Ashton-under-Lyne,
Lancashire,
OL7 0NA
United Kingdom

- 5 The equipment is specified in the description of this certificate and the documents to which it refers.

- 6 CML B.V., Chamber of Commerce No 67386717, Koopvaardijweg 32, 4906CV Oosterhout, The Netherlands, Notified Body Number 2776, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 12.

- 7 If an 'X' suffix appears after the certificate number, it indicates that the equipment is subject to conditions of safe use (affecting correct installation or safe use). These are specified in Section 14.
- 8 This EU Type Examination certificate relates only to the design and construction of the specified equipment or component. Further requirements of Directive 2014/34/EU Article 13 apply to the manufacture of the equipment or component and are separately certified.
- 9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the confidential report, has been demonstrated through compliance with the following documents:

EN IEC 60079-0:2018

EN IEC 60079-7:2015+A1:2018

EN 60079-31:2014

- 10 The equipment shall be marked with the following:



II 2G

II 1D

Ex eb IIC Gb

Ex ta IIIC Da

Ts= -60°C to +130°C

IP66/67



This certificate shall only be copied
in its entirety and without change

www.CMLEx.com

S. Roubedakis
Technical Manager



CML 23ATEX1002X
Issue 0

11 Description

The Hawke APEX C*e Range of cable glands are designed to form a seal around the outer sheath of a cable and are intended for use with a range of circular cables including armoured, non-armoured and braided cables. The gland type includes an integral armour/braid grounding device. The suitable service temperature is -60°C to +130°C.

These cable glands are manufactured in brass, or stainless steel; all of which may be plated to suit the application. The glands may be provided with metric or imperial (NPT) entry threads (alternative thread types maybe applied). These cable glands are available in sizes Os (M16) up to and including F (M75). The glands utilise thermoset rubber seals.

The Hawke APEX C*e cable gland is comprised of the following components:

1. Entry
2. Deluge Boot
3. Armour Clamping Ring(s)
4. Middlenut
5. Compression Seal
6. Slip Ring
7. Backnut

The gland assemblies as described above are rated for ingress protection of IP66/67. Use of Hawke IP sealing washers may be considered a suitable sealing method to maintain IP rating to the enclosure (see conditions of use) and will maintain the service temperature of the APEX cable gland range.

These cable glands may be fitted with a Hawke Gland Mounted Clamp (GMC) accessory. When fitted, no additional clamping is required for fixed installations.

The APEX C*e is provided with configurable armour clamping options, typically marked with either CUe, CXe or CWe where:

- U = suits all types of Braid, Tape and Wire Armour
- X = generally suits Braid and Tape
- W = generally suits Wire Armour

All variants of the APEX C*e are suitable for installation onto unarmoured circular cable and are dimensionally identical with the exception of the type of ring supplied.

12 Certificate history and evaluation reports

Issue	Date	Associated report	Notes
0	08 May 2023	R16051A/00	Issue of Prime Certificate

Note: Drawings that describe the equipment are listed in the Annex.



CML 23ATEX1002X
Issue 0

13 Conditions of Manufacture

None

14 Specific Conditions of Use (Special Conditions)

The following conditions relate to safe installation and/or use of the equipment.

- i. When the glands are used for increased safety or dust protection the entry thread shall be suitably sealed (in accordance with EN 60079-14) to maintain the ingress protection rating of the associated enclosure. Not applicable when Hawke IP 66/67 sealing washer is used.
- ii. Glands for use with conduit, unarmoured or braided cables are only suitable for fixed installations, the cable for which must be effectively clamped to prevent pulling and twisting (does not apply when fitted with rear clamping device or Hawke Gland Mounted Clamp (GMC)).

Certificate Annex

Certificate Number CML 23ATEX1002X
Equipment APEX C*e Range of Cable Glands
Manufacturer Hawke International (A Division of Hubbell Limited) (A member of the Hubbell Group of Companies)



The following documents describe the equipment or component defined in this certificate:

Issue 0

Drawing No	Sheets	Rev	Approved date	Title
320002	1 of 1	B	08 May 2023	Armour Clamping Ring
320007	1 of 1	B	08 May 2023	Deluge Boot
320011	1 to 3	A	08 May 2023	Thread Specification
320093	1 of 1	A	08 May 2023	APEX C*e Schedule Drawing
320098	1 of 1	A	08 May 2023	APEX C-Type Compression Seal Entry
320101	1 of 1	A	08 May 2023	Dedicated RAC
320103	1 of 1	A	08 May 2023	Middlenut
320104	1 of 1	A	08 May 2023	APEX E/C Type Backnut seal
320105	1 of 1	A	08 May 2023	APEX E/C Type Backnut
320106	1 of 1	A	08 May 2023	Gland metallic materials