



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification Scheme for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.: IECEx SIR 09.0064X

Issue No: 15

Certificate history:

Status: **Current**

Page 1 of 5

Issue No. 15 (2017-10-10)

Issue No. 14 (2017-03-23)

Issue No. 13 (2017-02-24)

Issue No. 12 (2016-07-11)

Issue No. 11 (2015-06-30)

Issue No. 10 (2015-04-02)

Issue No. 9 (2014-05-09)

Issue No. 8 (2014-02-28)

Issue No. 7 (2013-09-24)

Issue No. 6 (2013-09-02)

Issue No. 5 (2013-02-27)

Date of Issue: **2017-10-10**

Applicant: **Chalmit Lighting**
(Trading as Hadar Lighting)
388 Hillington Road
Glasgow G52 4BL
United Kingdom

Equipment: **HDL 106 Warrior Modular Floodlight/Bulkhead**

Optional accessory:

Type of Protection: **Increased Safety, Encapsulation and Dust**

Marking:
Refer to the Annexe

*Approved for issue on behalf of the IECEx
Certification Body:*

C Ellaby

Position:

Deputy Certification Manager

*Signature:
(for printed version)*

Date:

C. Ellaby
2017-10-10

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting the [Official IECEx Website](http://www.iecex.com).

Certificate issued by:

SIRA Certification Service
CSA Group
Unit 6, Hawarden Industrial Park
Hawarden, Deeside, CH5 3US
United Kingdom

sira
CERTIFICATION





IECEx Certificate of Conformity

Certificate No: IECEx SIR 09.0064X

Issue No: 15

Date of Issue: 2017-10-10

Page 2 of 5

Manufacturer: **Chalmit Lighting**
(Trading as Hadar Lighting)
388 Hillington Road
Glasgow G52 4BL
United Kingdom

Additional Manufacturing location(s):

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended.

STANDARDS:

The electrical apparatus and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards:

IEC 60079-0 : 2011 Edition:6.0	Explosive atmospheres - Part 0: General requirements
IEC 60079-18 : 2009 Edition:3	Explosive atmospheres Part 18: Equipment protection by encapsulation "m"
IEC 60079-31 : 2008 Edition:1	Explosive atmospheres – Part 31: Equipment dust ignition protection by enclosure "t"
IEC 60079-7 : 2006-07 Edition:4	Explosive atmospheres - Part 7: Equipment protection by increased safety "e"

*This Certificate **does not** indicate compliance with electrical safety and performance requirements other than those expressly included in the Standards listed above.*

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in

Test Report:

GB/SIR/ExTR10.0030/00	GB/SIR/ExTR10.0211/00	GB/SIR/ExTR11.0016/00
GB/SIR/ExTR11.0166/00	GB/SIR/ExTR12.0313/00	GB/SIR/ExTR13.0047/00
GB/SIR/ExTR13.0262/00	GB/SIR/ExTR13.0295/00	GB/SIR/ExTR14.0052/00
GB/SIR/ExTR14.0111/00	GB/SIR/ExTR15.0095/00	GB/SIR/ExTR15.0157/00
GB/SIR/ExTR16.0143/00	GB/SIR/ExTR16.0143/01	GB/SIR/ExTR17.0028/00
GB/SIR/ExTR17.0059/00	GB/SIR/ExTR17.0215/00	

Quality Assessment Report:

GB/BAS/QAR06.0027/06



IECEx Certificate of Conformity

Certificate No: IECEx SIR 09.0064X

Issue No: 15

Date of Issue: 2017-10-10

Page 3 of 5

Schedule

EQUIPMENT:

Equipment and systems covered by this certificate are as follows:

The Type HDL 106 Warrior Modular Floodlight/Bulkhead comprises an aluminium or stainless steel rectangular base with clear or translucent polycarbonate cover. The cover is secured to the base by four M6 x 16mm screws. The module is intended for use in fixed installations and is provided with appropriate mounting brackets for this purpose.

The base of the enclosure houses an encapsulated power supply and control board. An LED assembly is mounted to the base of the enclosure, such that it sits above the encapsulated power supply and control board, but behind the outer polycarbonate cover. The LED assembly comprises two compartments, each with integral polycarbonate cover, which are effectively encapsulated onto an aluminium base plate. Each compartment is fitted with 24 LEDs; the LEDs can be white, infra red, coloured or a combination. The base of the enclosure is also fitted with Exe certified terminals, which provide connection facilities for incoming cables and between the control board and LED assembly. The interior of the enclosure may also be fitted with an encapsulated fuse assembly.

Up to 8 cable entry holes may be provided depending on customer requirements.

Internal and external earthing facilities are provided.

The units are designed for use on an electrical supply of either 100 to 254 V 50/60 Hz or 24 V ac/dc dependent upon their construction.

An optional photocell may be supplied, which is located in an appropriate cable entry hole and provided with a steel or stainless steel shroud.

Up to 6 modules may be interlinked to provide overall higher output assemblies.

SPECIFIC CONDITIONS OF USE: YES as shown below:

- i. Except for internal wiring, not more than one single or multiple strand lead shall be connected into either side of any terminal, unless multiple conductors have been joined in a suitable manner, e.g. two conductors into a single insulated crimped boot lace ferrule.
- ii. Leads connected to the terminals shall be insulated for the appropriate voltage and this insulation shall extend to within 1 mm of the metal of the terminal throat.
- iii. When terminals in accordance with certificate IECEx SIR 05.0035U are used, all terminal screws, used and unused, shall be tightened down to between 0.5 Nm and 0.7 Nm.
- iv. When terminals in accordance with certificate IECEx SIR 05.0037U are used, all terminal screws, used and unused, shall be tightened down to between 1.2 Nm and 2 Nm.
- v. When terminals in accordance with certificates IECEx SIR 05.0035U and IECEx SIR 05.0037U are used, they shall only be installed and wired with cable within a temperature range of -10°C to 80°C.
- vi. When cross-connecting combs are used on terminals to certificates IECEx SIR 05.0035U and IECEx SIR 05.0037U, the relevant conditions of certification associated with those certificates shall be applied.
- vii. Cable entry holes shall be fitted with either an appropriately certified cable gland or appropriately certified blanking element. These shall provide and maintain a minimum enclosure ingress protection of IP66 or IP67 as appropriate.
- viii. If more than 8 individual LEDs are not illuminated, the LED assembly shall be replaced.
- ix. The supply circuit must be protected by a fuse capable of withstanding a prospective short circuit current of 1500 A.
- x. The HDL106E and HDL106NE, the battery powered emergency versions, are suitable for an ambient temperature range of -20°C to +50°C when installed with the terminal cross-link in accordance with the manufacturer's installation instructions, which achieves a 100% output, i.e. 48 illuminated LEDs. The HDL106E and HDL106NE are suitable for an ambient temperature range of -20°C to +55°C when the terminal cross-link is not installed, which achieves 50% output, i.e. 24 illuminated LEDs.

Refer to EQUIPMENT (Continued) for additional Conditions



IECEx Certificate of Conformity

Certificate No: IECEx SIR 09.0064X

Issue No: 15

Date of Issue: 2017-10-10

Page 4 of 5

EQUIPMENT (continued):

Conditions of Manufacture:

The Manufacturer shall comply with the following condition of manufacture:

- i. Every unit, including fuse assembly when fitted, shall be subjected to a routine dielectric strength test of at least 1508 V r.m.s. a.c. applied for at least 1 s, or at least 1810 V r.m.s. a.c. applied for at least 100 ms, between all terminals and the equipment enclosure, in accordance with Clause 9.2 of IEC 60079-18:2009.
- ii. Every unit shall be subjected to a visual inspection in accordance with Clause 9.1 of IEC 60079-18:2009.

Additional Specific Conditions of Use

- i. When the Lexan polycarbonate lens is fitted, the equipment shall only be used in areas with a low risk of mechanical impact.
- ii. Under certain extreme circumstances, the non-metallic parts incorporated in the enclosure of this equipment may generate an ignition-capable level of electrostatic charge therefore; the equipment shall not be installed in a location where the external conditions are conducive to the build-up of electrostatic charge on such surfaces. In addition, the equipment shall only be cleaned with a damp cloth.



IECEX Certificate of Conformity

Certificate No: IECEx SIR 09.0064X

Issue No: 15

Date of Issue: 2017-10-10

Page 5 of 5

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above):

This issue recognises the following changes; refer to the certificate annex to view a comprehensive history:

- i. The Makrolon polycarbonate lens has been replaced by a Lexan polycarbonate lens diffuser.
- ii. The drawings were revised to include the new lens details and minor editorial changes.

Annex:

[IECEX SIR 09.0064X Iss 15 Annex.pdf](#)

Annexe to: IECEx SIR 09.0064X Issue 15
Applicant: Chalmit Lighting
Apparatus: HDL106 Warrior Modular Floodlight/Bulkhead



Marking

HDL106S and HDL106N (100 V to 254 V 50/60 Hz)

Ex e mb IIC T4 Gb	Ex e mb IIC T3 Gb
Ex tb IIIC T103°C Db IP66/67**	Ex tb IIIC T103°C Db IP66/67**
Ta = -20°C to +50°C	Ta = -20°C to +59.5°C

HDL106E and HDL106NE

Ex e mb IIC T4 Gb	
Ex tb IIIC T103°C Db IP66/67**	
Ta = -20°C to +50°C*	Ta = -20°C to +55°C*

HDL106N (18 V to 54 V AC/DC)

Ex e mb IIC T4 Gb
Ex tb IIIC T87°C Db IP66/67**
Ta = -20°C to +55°C

HDL106A

Ex e mb IIC T6 Gb	Ex e mb IIC T5 Gb
Ex tb IIIC T70°C Db IP66/67**	Ex tb IIIC T85°C Db IP66/67**
Ta = -20°C to +50°C	Ta = -20°C to +65°C

* See certificate conditions.

** When the polycarbonate diffuser option is fitted, IP rating becomes IP66 only"

Full Certificate Change History

Issue 1 – this Issue introduced the following changes:

1. Modification to the Special Condition for Safe Use viii/ix from the original certification. The Special Condition for Safe Use is modified to state: "The LED assembly shall be replaced following the failure of no more than 8 individual LEDs
2. The optional addition of a coloured glass plate to the inside of the LED assembly housing was recognised

Issue 2 – this Issue introduced the following change:

1. The introduction of two alternative encapsulated power supply and control board assemblies.

Issue 3 – this Issue introduced the following change:

1. The addition of an optional, aluminium battery housing to the rear of the unit, this allows battery operation. In this arrangement, the unit is designated as a HDL106E Emergency LED Floodlight.
2. The Description of Equipment was amended to clarify that the applicable electrical rating depends on the construction of the unit.

Issue 4 – this Issue introduced the following changes:

1. The introduction of a new luminaire, type reference HDL106A, with a T6 temperature classification.
2. Following appropriate assessment to demonstrate compliance with the requirements of a later standard, IEC 61241-1:2004 Ed. 1 was replaced by IEC 60079-31:2008 Ed. 1.
3. The inclusion of an extra wide beam (90°) version.
4. The option of a 'warm white light version' and the separation of the 'yellow light version' into two categories; 'yellow filter white light' and 'yellow filter warm white light' was endorsed.
5. A 'single compartment' LED enclosure version was recognised.

Issue 5 – this Issue introduced the following change:

1. Following appropriate assessment to demonstrate compliance with the requirements of the latest version of IEC 60079-0, the document previously listed, IEC 60079-0:2007 Ed 5, was replaced by that currently listed

Date: 10 October 2017

Page 1 of 3

Form 9530 Issue 1

Sira Certification Service

Unit 6 Hawarden Industrial Park,
Hawarden, CH5 3US, United Kingdom

Tel: +44 (0) 1244 670900
Fax: +44 (0) 1244 681330
Email: ukinfo@csagroup.org
Web: www.csagroupuk.org

Annexe to: IECEx SIR 09.0064X Issue 15
Applicant: Chalmit Lighting
Apparatus: HDL106 Warrior Modular Floodlight/Bulkhead



Issue 6 – this Issue introduced the following change:

1. The marking in the certificate was corrected to:
 - * Remove information that is not relevant to IECEx applications
 - * Correct the reference quoted for the standard version.

Issue 7 – this Issue introduced the following change:

1. The value of three, board mounted resistors, R1, R7 and R15, was changed from 47 kΩ 0.12 W to 22 kΩ 0.27 W.

Issue 8 – this Issue introduced the following change:

GB/SIR/ExTR13.0295/00

1. The use of an alternative control board for the emergency version of the luminaire was approved.
2. It was recognised that an optional switch may be mounted in the wall of the casting of the emergency version of the luminaire.
3. Type GP770DHT Battery packs were allowed to be used in the emergency battery enclosure.

GB/SIR/ExTR14.0052/00

1. The certification drawings were updated to show how the LED Assembly cables are sheathed.
2. The following changes to the encapsulation process were recognised:
 - The clear LED cover is now sealed to the base of the LED Light Engine plaque using silicone compound prior to encapsulation to create a sealed void.
 - Silicone compound is applied to the cables at the rear of the LED tray to plug the cable entry hole.
 - The curing times of the encapsulant have been increased.

Issue 9 – this Issue introduced the following change:

1. The use of an alternative power supply and control board for use with a 24V ac/dc supply was approved.
2. The recognition of a new product code "N" for a high output LED.
3. The product code was modified to recognise additional cable entry options.
4. Drawing WF-710 was removed from the list of certified documents.

Issue 10 – this Issue introduced the following change:

1. A new version of the High Output LED Modular Floodlight/Bulkhead was introduced; this version has a low voltage power supply, 18 V to 54 V AC/DC, and is suitable for an ambient temperature range of -20°C to +55°C.
2. Because of previous inconsistencies, the model numbers of the currently available versions of the Transportable Modular Floodlight/Bulkhead were clarified, see list below; the marking section was amended to recognise the safety information applicable to these versions.

HDL106	Generic Name
HDL106S	Standard Version
HDL106A	T6 Rating Version
HDL106N	High Output LED Version (100 V to 254 V 50/60 Hz)
HDL106N	High Output LED Version (18 V to 54 V AC/DC)
HDL106E	Emergency Version

3. The application of a Trimite coating on the lens cover was permitted.
4. The voltage range of the high voltage version quoted in Product Description was changed from 100 to 240 V 50/60 Hz to 100 to 254 V 50/60 Hz as detailed in section 1.7 of Sira report R19590A/00 and on the manufacturer's drawings.

Issue 11 – this Issue introduced the following changes:

1. The option of using an encapsulated fuse on the neutral terminal of the equipment was introduced.
2. Removal of the word "Luminaire" from the Product Name.
3. The option of using blue LEDs was introduced.
4. The dust certification code was amended to reflect the 'alternative' marking recognised by the standards.
5. The condition relating to the fuse protecting the circuit was modified to remove reference to the optional fuse.

Sira Certification Service

Unit 6 Hawarden Industrial Park,
Hawarden, CH5 3US, United Kingdom

Tel: +44 (0) 1244 670900
Fax: +44 (0) 1244 681330
Email: ukinfo@csagroup.org
Web: www.csagroupuk.org

Annexe to: IECEx SIR 09.0064X Issue 15
Applicant: Chalmit Lighting
Apparatus: HDL106 Warrior Modular Floodlight/Bulkhead



Issue 12 – this Issue introduced the following changes:

- 1 Correct typographical error on certificate. The battery which is currently listed as being "GP770DHT" has been corrected to read "GP700DHT".
- 2 Increase of the ambient temperature to +65°C for the "T6 version". Alternate temperature markings were introduced.
- 3 Increase of the ambient temperature to +59.5°C for "High Voltage Assembly C" control board option of the HDL106S version. Alternate temperature markings were introduced.
- 4 Increase of the ambient temperature to +55°C for the emergency version when operated at a 50% output. Alternate temperature markings were introduced.
- 5 Introduction of a fuse on the control board for the HDL106N (18 V to 54 V AC/DC) version.
- 6 Removal of two control board options from the scope of the certification.
- 7 Recognition of the HDL106NE version.

Issue 13 – this Issue introduced the following changes:

- 1 The certificate was transferred:

From: Hadar Lighting Jubilee Industrial Estate Ashington Northumberland NE63 8UG United Kingdom	To: Chalmit Lighting (Trading as Hadar Lighting) 388 Hillington Road Glasgow G52 4BL United Kingdom
--	--
- 2 A typographical error was corrected in the Specific Conditions of Use

Issue 14 – this Issue introduced the following change:

- 1 The introduction of a glass lens diffuser design as an optional alternative to the existing polycarbonate diffuser.

Issue 15 – this Issue introduced the following changes:

- 1 The Makrolon polycarbonate lens has been replaced by a Lexan polycarbonate lens diffuser.
- 2 The drawings were revised to include the new lens details and minor editorial changes.