



WIRE SIZE SERVICE ENTRANCE GROUND LUG	
MAXIMUM WIRE SIZE	TIGHTENING TORQUE (in-lb)
#6 AWG	45
#1/0 AWG	50
#250MCM AWG	325

PRESSURE SYSTEM CONNECTION
1/2" NPT

* LINE TERMINALS – WIRE CAPACITY AND QUANTITY

MAXIMUM MOTOR HORSEPOWER					WIRE SIZE PER PHASE (75°C Cu)	TIGHTENING TORQUE (in-lb)
200–208V	220–240V	380–415V	440–480V	550–600V		
5–40	5–40	5–75	5–75	–	(1)#8–#1/0 AWG	120
50–60	50–75	100–125	100–150	–	(1)#2/0–#250MCM AWG	225
75–100	100–125	150–200	200–250	–	(1)#2/0–#500MCM AWG	375
125–150	150–200	250–300	300–400	–	(2)#2/0–#250MCM AWG	375
200–250	250–300	350–500	500–600	–	(2)#2/0–#350MCM AWG	375
300	–	600–700	700	–	(3)#3/0–#400MCM AWG	375
					(4)#4/0–#500MCM AWG	375

* MOTOR TERMINALS – WIRE CAPACITY AND QUANTITY

MAXIMUM MOTOR HORSEPOWER					WIRE SIZE PER PHASE (75°C Cu)	TIGHTENING TORQUE (in-lb)
200–208V	220–240V	380–415V	440–480V	550–600V		
5–60	5–75	5–125	5–150	–	(1)#6–#1 AWG	120
75–100	100–125	150–200	200–250	–	(1)#1/0–#3/0 AWG	200
125–200	150–250	250–400	300–500	–	(1)#4/0–#500MCM AWG	275
250–300	300	500–700	600–700	–	(2)#2/0–#350MCM AWG	275
–	–	–	–	–	–	–

NOTES:

- * 1.) FOR CORRECT FIELD WIRE SIZING, REFER TO THE NATIONAL ELECTRICAL CODE, NFPA-70.
2.) MOTOR CONNECTIONS SHOWN ARE TYPICAL. SINCE MOTOR CONNECTIONS VARY WIDELY, REFER TO THE MOTOR MANUFACTURER'S CONNECTION DIAGRAM FOR SPECIFIC WIRING ARRANGEMENT.



REV	DATE	BY	DESCRIPTION	DRAWN	DAMA	11-18-15
B	08/30/18		UPDATED WIRE CAPACITY AND WIRE SIZE TABLES.	CHECK	DAMA	11-18-15
				APPD		
FIELD CONNECTIONS, MODEL MPT430 WYE-DELTA OPEN TRANSITION START ELECTRIC FIRE PUMP CONTROLLER WITH TRANSFER SWITCH						
<div> METRON A Division of Hubbell Industrial Controls, Inc. 4301 Cheyenne Drive, Archdale, NC 27263 USA </div>						
OPTIONS:						
HCMPTF430TS						
SCALE NTS						SHEET 2 OF 2