

CERTIFICATE OF COMPLIANCE

Certificate Number 20190823-E84940
Report Reference E84940-20190521
Issue Date 2019-AUGUST-23

Issued to: HAWKE INTERNATIONAL, DIV OF HUBBELL LTD
OXFORD ST W
ASHTON-UNDER-LYNE
OL7 ONA, UNITED KINGDOM

**This certificate confirms that
representative samples of**

CABLE SEALING FITTINGS FOR USE IN HAZARDOUS
LOCATIONS

See Addendum.

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety:

UL 2225, Cable and Cable-Fittings For Use In Hazardous
(Classified) Locations.
CSA C22.2 No. 174-18, Cables and cable glands for use in
hazardous locations.
UL 514B & CSA C22.2 No. 18.3-12, Conduit, Tubing, and
Cable Fittings.

Additional Information:

See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number 20190823-E84940
Report Reference E84940-20190521
Issue Date 2019-AUGUST-23

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Cable Sealing Fitting, Type 711, may be followed by M, followed by -X, followed by letters A, B, C, C2, D, E, or F for use in Class I, Groups A, B, C and D; Class II, Groups E, F and G; Class III Hazardous Locations. For use with cable type MC-HL and ITC-HL. For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Thread sizes 1/2 to 3 in. NPT inclusive or M20 to M75 inclusive, for vertical or horizontal mounting.

Cable Sealing Fitting, Type 710, may be followed by M, followed by -X, followed by letters A, B, or C for use in Class I, Groups A, B, C and D Hazardous Locations. For use with cable type TC-ER-HL (up to 1 in.). For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Thread sizes 1/2 to 1 in. NPT inclusive or M20 to M25, for vertical or horizontal mounting.

Cable Sealing Fitting, Type 710, may be followed by M, followed by -X, followed by letters A, B, C, C2, D, E or F for use in Class I, Groups A, B, C and D; Class II, Groups E, F and G; Class III Hazardous Locations. For use with cable type ITC-HL. For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Threads sizes 1/2 to 3 in. NPT inclusive or M20 to M75 inclusive, for vertical or horizontal mounting.

Cable Sealing Fitting, Type 753, may be followed by M, followed by -X, followed by letters Os, O, A, B, C, C2, D, E or F for use in Class I, Division 2, Groups A, B, C and D; Class II, Division 2, Groups F and G; Class III Hazardous Locations. For use with cable type PLTC and ITC. For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Thread size 1/2 to 3 in. NPT inclusive or M20 to M75 inclusive, for vertical or horizontal mounting.

Cable Sealing Fitting, Type 711, may be followed by M, followed by -X, followed by letters A, B, C, C2, D, E, or F for use in Class I, Division 2, Groups A, B, C and D; Class II, Division 2, Groups F and G; Class III, Division 2 Hazardous Locations. For use with cable type MC. For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Thread sizes 1/2 to 3 in. NPT inclusive or M20 to M75 inclusive, for vertical or horizontal mounting.

Cable Sealing Fitting, Type 710, may be followed by M, followed by -X, followed by letters Os, O, A, B, C, C2, D, E or F for use in Class I, Division 2, Groups A, B, C and D; Class II, Division 2, Groups F and G; and Class III, Division 2 Hazardous Locations. For use with cable type TC-ER, TC, PLTC, PLTC-ER, ITC or ITC-ER. For use with the manufacturer's sealing compounds Hawkeseal 2 (EP2132), Hawkeseal 3 (QSP2122), or Express (X099-41-2). Thread sizes 1/2 to 3 in. NPT inclusive or M20 to M75, for vertical or horizontal mounting.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

