

# Assembly Instructions for: PL 6\*\* Series Junction Boxes



**HAWKE**  
International

AI 273 / Issue AF - 08/22

**IMPORTANT:** This document should be read carefully before commencing installation

Zones of Use for Terminal Box - as defined in IEC/EN 60079-0 and IEC/EN 60079-10-1

Group II Category 1G, for use in Zone 0 (plus Zone 1 and Zone 2).

Group II Category 1D, for use in Zone 20 (plus Zone 21 and Zone 22).

Group II Category 2G, for use in Zone 1 (plus Zone 2).

Group II Category 2D, for use in Zone 21 (plus Zone 22).

Service Temperature: PL 6\*\* -60°C to +75°C

Minimum Installation Temperature: -5°C

## Certification Details

Box Type: PL6\*\* Series

Ex II 2G Ex eb IIC T\* Gb, Ex II 2D Ex tb IIIC T\*\*\*C Db IP66

Ex II 2G Ex ib IIC T\* Gb, Ex II 2D Ex ib IIIC T\*\*\*C Db IP66

Ex II 1G Ex ia IIC T\* Ga, Ex II 1D Ex ia IIIC T\*\*\*C Da IP66


Baseefa 06ATEX0117X

IEC Ex BAS06.0028X

BAS21UKEX0047X

IEx 16.0143X

[Ex] No EA3C RU C-GB.HA91.B.00260/21



W = Maximum Dissipated Wattage

N = No. of Terminals Fitted

F = Combined Terminal Resistance

I = Maximum Current

$$W = N \times F \times I^2$$

$$N = W / F \times I^2$$

$$I = \sqrt{W / N \times F}$$

Note: Combined Terminal Resistance = Resistance of Maximum Conductor Length (see BS 6360 and table below) + Terminal Resistance

Box Type	Maximum Power Dissipation (Watts)																Max. Cable Length Per Terminal (M)	
	T6	T6 80°C	T6 -60°C +40°C	T6	T6 80°C	T6 +55°C	T6	T6 80°C	T6 +65°C	T5	T5 95°C	T5 +40°C	T5	T5 95°C	T5 +55°C	T5	T5 95°C	T5 +65°C
PL 612	4.1			2.5			1.5			5.6			4.1			3.0		0.127
PL 615	6.4			4.0			2.4			8.8			6.4			4.8		0.175
PL 620	11.4			7.1			4.2			15.6			11.4			8.5		0.240
PL 626	11.4			7.1			4.2			15.6			11.4			8.5		0.275
PL 630	20.8			13.0			7.8			28.6			20.8			15.6		0.365
PL 642	20.8			13.0			7.8			28.6			20.8			15.6		0.432
PL 644	20.8			13.0			7.8			28.6			20.8			15.6		0.528

Connection Solutions

[www.ehawke.com](http://www.ehawke.com)

Hawke International is a division of Hubbell Ltd.  
Registered No. 669157 in England. Registered Office:  
Cannon Place, 78 Cannon Street, London EC4N 6AF.

A member of the Hubbell Group of Companies

UK Office  
Oxford Street West,  
Ashton-Under-Lyne,  
Lancashire. OL7 0NA. UK  
Sales: +44 (0) 161 830 6698  
Technical: +44 (0) 161 830 6697  
Fax: +44 (0) 161 830 6648  
E-mail: sales@ehawke.com

AI 273 - Issue AF / Page 1 of 6

#### CONDITIONS FOR SAFE USE:

1. Unused entry holes must be fitted with stopping plugs as listed on the ZPL6 component certificate Baseefa06ATEX0116U. The operating temperature range and Ingress Protection rating of the enclosure is limited to that of the stopping plug fitted.
2. Any breathing and draining device as listed on the ZPL6\*\* component certificate Baseefa06ATEX0116U may be fitted. The breather/drain device must be installed in its correct orientation in the bottom face of the junction box. The operating temperature range and Ingress Protection rating of the junction box is limited to that of the breather/drain device fitted.
3. All terminal screws, used and unused, shall be fully tightened down by the end user.
4. Insulation of conductors must extend to within 1mm of the metal of the terminal throat unless specified otherwise on the terminal certificate.
5. No more than one single or multi-stranded lead shall be connected to either side of any terminal unless multiple conductors have been joined in a suitable manner, e.g. two conductors into a single insulated bootlace ferrule, or any method indicated on the terminal certificate.
6. Terminals and their accessories shall be installed in such a manner that the creepage distances and clearances between the terminal and adjacent components, enclosure walls and covers comply with the requirements of EN 60079-7 and EN 60079-11 for the rated voltage of the equipment.
7. Terminal temperatures must not exceed the operating range specified on the component certificate for the terminal.
8. All terminals, and accessories such as cross-connectors, shall be installed in accordance with the terminal manufacturers instructions.
9. The maximum voltage, current and dissipated power shown on the rating label must not be exceeded.
10. When connecting conductors of cross section below the maximum allowed for the particular terminal then the maximum amps per pole must be reduced in-line with the maximum amps permitted for a terminal equivalent to the conductor size fitted e.g. If a terminal that can take a 10mm<sup>2</sup> conductor at 40Amps is fitted with a 4mm<sup>2</sup> conductor then the current shall be reduced to a maximum of 22Amps, or the rating marked on the apparatus label, whichever is the lower.
11. When label fixing is by screws complete with Nyloc nuts then the Ingress Protection Rating is IP66.
12. Unused entries may be fitted with alternative stopping plugs and or breather drains to those listed in the schedule. The user is responsible for ensuring that the protection concept, temperature class and relevant IP rating are maintained.
13. When fuse terminals are fitted, the low ambient temperature is limited to -25°C and the junction box becomes a defined arrangement.

#### EXTERNAL EFFECTS AND AGGRESSIVE SUBSTANCES:

The end user shall take into consideration for health and safety regulations when changing environmental conditions and in the presence of extraneous voltages, humidity, vibrations, contamination and other external effects, take into account the limits of the operating conditions established by Hawke International.

Equipment parts used must be appropriate to the intended mechanical and thermal stresses and capable of withstanding attack by existing or foreseeable aggressive substances.

#### TO OPEN THE LID:

1. Disconnect power (isolate all circuits).
2. Untighten the lid securing screws.
3. Carefully remove the lid ensuring the gasket is not displaced or damaged.

#### TO CLOSE THE LID:

1. Check that the gasket is correctly located in the groove in the underside of the lid and undamaged. Ensure that the correct lid is refitted.
2. Locate and tighten all the lid securing screws into the box body.

#### ENCLOSURE INSTALLATION (E)

- a) The IP rating of the enclosure must be maintained for the area of use (e.g. IP6\* for Zone 21 dust environment) by the use of correct arrangement of cable/gland/sealing arrangements and in accordance with the installation codes as detailed in IEC/EN 60079-14 - IEC/EN 60079-31 and these installation instructions.
- b) The enclosure may be ready supplied with cable entries. Where the customer drills cable entries they must be installed in accordance with the component certificate BAS06ATEX0116U or IEC Ex No: BAS06.0027U and enclosure limitations, these specify a maximum clearance on the entry thread of 0.7mm for plain holes and where adjacent cable entries are installed sufficient clearance must be maintained to allow for the fitting of sealing/retaining washers and the rotation of the cable gland hexagons, and leave a minimum of material between adjacent holes in line with the above certificate number(s).

#### TERMINAL WIRING (TW)

- a) All wiring must be carried out in accordance with the relevant code of practice and/or instructions e.g. IEC/EN 60079-14 and IEC/EN 60079-31.
- b) When used as a general purpose junction box or marshalling box the circuits carrying currents  $\geq 1\text{A}$  shall be individually protected against over current such that the protective device operates effectively at no more than 1.45 times the current carrying capacity of the smallest conductor used in that circuit.
- c) The installer shall ensure creepage and clearance distances are not reduced, especially between intrinsically safe (is) and non-is circuits (e.g. 50mm clearance).
- d) The use of any cross connection devices between adjacent terminal ways shall be in accordance with the requirements of the relevant component certificate listed on Drg. D9160.

#### EARTHING:

- a) Junction boxes shall be earthed in accordance with the relevant code of practice e.g. IEC/EN 60079-14 and IEC/EN 60079-31.
- b) The PL 6\*\* series boxes are supplied fitted with an internal earth terminal.
- c) The PL 6\*\* series boxes may be supplied fitted with or without an internal earth continuity plate.

Note : An optional internal / external earth stud is available.

**SCHEDULE OF TERMINALS FITTED (T6 40C AND T5 55C)**

PL 612 Terminal Capacity Data										
Terminal Type	Conductor Size mm <sup>2</sup>		Max. Volts	Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max		Term. Qty.	Amps	Term. Qty.	Amps			
WDU2.5N	0.5	2.5	440	12	15	9	17	0.001371	10	0.4 - 0.6
WDU2.5	0.5	2.5	690	10	17	9	17	0.001311	10	0.4 - 0.8
UT 2.5	0.14	2.5	690	10	15	10	15	0.001351	9	0.5 - 0.6
WDU 4	0.5	4.0	690	9	22	9	22	0.000875	10	0.5 - 1.0
UT 4	0.14	4.0	690	9	20	9	20	0.000845	9	0.6 - 0.8
WDU 6	0.5	6.0	690	6	29	6	29	0.000567	12	0.8 - 1.6
UT 6	0.2	6.0	690	6	28	6	28	0.000591	10	1.5 - 1.8
WDU10	1.5	10.0	690	5	40	5	40	0.000384	12	1.2 - 2.4
UT 10	0.5	10.0	690	5	39	5	39	0.000372	10	1.5 - 1.8
HTB6*	0.5	6.0	550	1	37	1	37	N/A	12	1.0 - 2.0

PL 615 Terminal Capacity Data												
Terminal Type	Conductor Size mm <sup>2</sup>		Max. Volts	Rail Orientation**		Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max				Term. Qty.	Amps	Term. Qty.	Amps			
WDU2.5N	0.5	2.5	440	D/V/H		17	14	12	17	0.001726	10	0.4 - 0.6
WDU2.5	0.5	2.5	690	D/V/H		17	15	12	17	0.001666	10	0.4 - 0.8
UT 2.5	0.14	2.5	690	D/V/H		16	15	16	15	0.001706	9	0.5 - 0.6
WDU 4	0.5	4.0	690	D/V/H		14	20	11	22	0.001096	10	0.5 - 1.0
UT 4	0.14	4.0	690	D/V/H		13	20	13	20	0.001066	9	0.6 - 0.8
WDU 6	0.5	6.0	690	D/V/H		10	29	10	29	0.000715	12	0.8 - 1.6
UT 6	0.2	6.0	690	D/V/H		10	28	10	28	0.000739	10	1.5 - 1.8
WDU10	1.5	10.0	690	D/V/H		8	40	8	40	0.000472	12	1.2 - 2.4
UT 10	0.5	10.0	690	D/V/H		7	39	7	39	0.000460	10	1.5 - 1.8
WDU16	1.5	16.0	690	D/V/H		6	53	6	53	0.000362	16	3.0 - 4.0
UT 16	1.5	16.0	690	D/V/H		6	53	6	53	0.000361	14	2.5 - 3.0
HTB6*	0.5	6.0	550	D/V/H		1	37	1	37	N/A	12	1.0 - 2.0

PL 620 Terminal Capacity Data										
Terminal Type	Conductor Size mm <sup>2</sup>		Max. Volts	Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max		Term. Qty.	Amps	Term. Qty.	Amps			
WDU 2.5N	0.5	2.5	440	27	13	16	17	0.002208	10	0.4 - 0.6
WDU 2.5	0.5	2.5	690	24	14	17	17	0.002148	10	0.4 - 0.8
UT 2.5	0.14	2.5	690	26	14	22	15	0.002188	9	0.5 - 0.6
WDU 4	0.5	4.0	690	20	20	16	22	0.001396	10	0.5 - 1.0
UT 4	0.14	4.0	690	21	19	20	20	0.001366	9	0.6 - 0.8
WDU 6	0.5	6.0	690	15	28	14	29	0.000915	12	0.8 - 1.6
UT 6	0.2	6.0	690	16	27	15	28	0.000939	10	1.5 - 1.8
WDU10	1.5	10.0	690	12	40	12	40	0.000591	12	1.2 - 2.4
UT 10	0.5	10.0	690	12	39	12	39	0.000579	10	1.5 - 1.8
WDU16	1.5	16.0	690	9	53	9	53	0.000437	16	3.0 - 4.0
UT 16	1.5	16.0	690	10	51	9	53	0.000436	14	2.5 - 3.0
WDU 35	2.5	35.0	690	6	80	6	80	0.000270	18	4.0 - 5.0
UT 35	1.5	35.0	690	7	70	7	70	0.000074	18	3.2 - 3.7
WDU 50N	6.0	50.0	690	5	88	5	88	0.000242	24	3.5 - 6.0
UKH 50	16.0	50.0	690	5	87	5	87	0.000192	24	6.0 - 8.0
WDU 70N	10.0	70.0	690	4	117	3	129	0.000206	22	9.0 - 12.0

Note: Terminals listed are only suitable for a minimum operating temperature of -50°C.

\* Refer to Fig. 1 for HTB terminal limitations

\*\* V = Vertical

H = Horizontal

D = Diagonal

**SCHEDULE OF TERMINALS FITTED (T6 40C AND T5 55C)**

Terminal Type	Conductor Size mm <sup>2</sup>		Max. Volts	Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max		Term. Qty.	Amps	Term. Qty.	Amps			
WDU 2.5	0.5	2.5	690	38	11	15	17	0.002407	10	0.4 - 0.8
UT 2.5	0.14	2.5	690	41	10	20	15	0.002447	9	0.5 - 0.6
WDU 4	0.5	4.0	690	32	15	14	22	0.001557	10	0.5 - 1.0
UT 4	0.14	4.0	690	34	14	18	20	0.001527	9	0.6 - 0.8
WDU 6	0.5	6.0	690	24	21	12	29	0.001023	12	0.8 - 1.6
UT 6	0.2	6.0	690	25	20	13	28	0.001047	10	1.5 - 1.8
WDU10	1.5	10.0	690	19	30	10	40	0.000655	12	1.2 - 2.4
UT 10	0.5	10.0	690	20	29	11	39	0.000643	10	1.5 - 1.8
WDU 16	1.5	16.0	690	16	38	8	53	0.000477	16	3.0 - 4.0
UT 16	1.5	16.0	690	17	37	8	53	0.000476	14	2.5 - 3.0
WDU 35	2.5	35.0	690	12	57	6	80	0.000289	18	4.0 - 5.0
UT 35	1.5	35.0	690	12	68	11	70	0.000077	18	3.2 - 3.7

Terminal Type	Conductor Size mm <sup>2</sup>		Max. Volts	Rail Orientation**		Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max		V/H	D	Term. Qty.	Amps	Term. Qty.	Amps			
WDU 2.5	0.5	2.5	690	V/H	76	9		22	17	0.003074	10	0.4 - 0.8
				D	55	11						
UT 2.5	0.14	2.5	690	V/H	76	9		29	15	0.003114	9	0.5 - 0.6
				D	53	11						
WDU 4	0.5	4	690	V/H	64	12		20	22	0.001972	10	0.5 - 1.0
				D	46	15						
UT 4	0.14	4	690	V/H	62	13		26	20	0.001942	9	0.6 - 0.8
				D	44	15						
WDU 6	0.5	6	690	V/H	48	18		18	29	0.001300	12	0.8 - 1.6
				D	35	21						
UT 6	0.2	6	690	V/H	46	18		19	28	0.001324	10	1.5 - 1.8
				D	33	21						
WDU 10	1.5	10	690	V/H	36	26		15	40	0.000819	12	1.2 - 2.4
				D	28	30						
UT 10	0.5	10	690	V/H	36	26		16	39	0.000807	10	1.5 - 1.8
				D	26	31						
WDU 16	1.5	16	690	V/H	30	34		12	53	0.000580	16	3.0 - 4.0
				D	22	40						
UT 16	1.5	16	690	V/H	30	34		12	53	0.000579	14	2.5 - 3.0
				D	22	40						
WDU 35	2.5	35	690	V/H	22	53		9	80	0.000336	18	4.0 - 5.0
				D	16	62						
UT 35	1.5	35	690	V/H	22	61		16	70	0.000082	18	3.2 - 3.7
				D	16	70						
WDU 50N	6	50	690	D	11	80	8	88	0.000291	24	3.5 - 6.0	
UKH 50	16	50	690	D	11	87	11	87	0.000241	24	6.0 - 8.0	
WDU 70N	10	70	690	D	11	88	5	129	0.000239	22	9.0 - 12.0	

Note: Terminals listed are only suitable for a minimum operating temperature of -50°C.

\* Refer to Fig. 1 for HTB terminal limitations

\*\* V = Vertical

H = Horizontal

D = Diagonal

**SCHEDULE OF TERMINALS FITTED (T6 40C AND T5 55C)**

Terminal Type	PL 642 Terminal Capacity Data										
	Conductor Size mm <sup>2</sup>		Max. Volts	Rail Orientation**	Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	
	Min	Max			Term. Qty.	Amps	Term. Qty.	Amps			
WDU 2.5	0.5	2.5	690	V	104	7	19	17	0.003571	10	
				H	122	6					
UT 2.5	0.14	2.5	690	V	100	7	24	15	0.003611	9	
				H	118	6					
WDU 4	0.5	4	690	V	88	10	18	22	0.002281	10	
				H	102	8					
UT 4	0.14	4	690	V	84	10	21	20	0.002251	9	
				H	100	9					
WDU 6	0.5	6	690	V	64	14	15	29	0.001506	12	
				H	78	10					
UT 6	0.2	6	690	V	64	14	16	28	0.001530	10	
				H	74	13					
WDU 10	1.5	10	690	V	52	20	13	40	0.000942	12	
				H	62	13					
UT 10	0.5	10	690	V	48	21	14	39	0.000930	10	
				H	60	19					
WDU 16	1.5	16	690	V	40	28	11	53	0.000657	16	
				H	50	16					
UT 16	1.5	16	690	V	40	28	11	53	0.000656	14	
				H	48	25					
WDU 35	2.5	35	690	H	18	55	8	80	0.000371	18	4.0 - 5.0
UT 35	1.5	35	690	H	18	63	14	70	0.000086	18	3.2 - 3.7
WDU 50N	6	50	690	H	16	63	8	88	0.000317	24	3.5 - 6.0
UKH 50	16	50	690	H	14	74	10	87	0.000267	24	6.0 - 8.0
WDU 70N	10	70	690	H	14	75	4	129	0.000257	22	9.0 - 12.0

Terminal Type	PL 644 Terminal Capacity Data									
	Conductor Size mm <sup>2</sup>		Max. Volts	Maximum Physical Terminal Content		Reduced Terminal Content at Maximum Terminal Amps		Combined Terminal Resistance (Ohms)	Insulation Stripping Length (mm)	Terminal Tightening Torque (Nm)
	Min	Max		Term. Qty.	Amps	Term. Qty.	Amps			
WDU 2.5	0.5	2.5	690	171	5	15	17	0.004282	10	0.4 - 0.8
UT 2.5	0.14	2.5	690	168	5	20	15	0.004322	9	0.5 - 0.6
WDU 4	0.5	4.0	690	144	7	15	22	0.002724	10	0.5 - 1.0
UT 4	0.14	4.0	690	138	7	18	20	0.002694	9	0.6 - 0.8
WDU 6	0.5	6.0	690	108	10	13	29	0.001802	12	0.8 - 1.6
UT 6	0.2	6.0	690	105	10	14	28	0.001826	10	1.5 - 1.8
WDU10	1.5	10.0	690	87	14	11	40	0.001118	12	1.2 - 2.4
UT 10	0.5	10.0	690	84	14	12	39	0.001106	10	1.5 - 1.8
WDU 16	1.5	16.0	690	69	19	9	53	0.000768	16	3.0 - 4.0
UT 16	1.5	16.0	690	69	19	9	53	0.000767	14	2.5 - 3.0
WDU 35	2.5	35.0	690	51	31	7	80	0.000421	18	4.0 - 5.0
UT 35	1.5	35.0	690	51	34	12	70	0.000092	18	3.2 - 3.7
WDU 50N	6	50.0	690	30	43	7	88	0.000354	24	3.5 - 6.0
UT 50	16	50.0	690	26	51	8	87	0.000304	24	6.0 - 8.0
WDU 70N	10	70.0	690	26	53	4	129	0.000283	22	9.0 - 12.0

Note: Terminals listed are only suitable for a minimum operating temperature of -50°C.

\* Refer to Fig. 1 for HTB terminal limitations

\*\* V = Vertical

H = Horizontal

D = Diagonal

## Fig. 1 - When HTB terminals are fitted the following limitations apply:

Table 1

Max. No. conductors of same size connected to each terminal

Conductor Size (sq. mm.)	Maximum No. of Cores
10	2
6	3
4	4
Smaller Conductors > or = 0.5 sq. mm.	4

Conductors be either all solid or all stranded

Table 2

Alternatively, the following PAIRS of conductor combinations may be fitted in one terminal

1.5mm <sup>2</sup> solid with:	1.5mm <sup>2</sup> solid or 2.5mm <sup>2</sup> stranded or 4mm <sup>2</sup> stranded or 6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded
1.5mm <sup>2</sup> stranded with:	0.9mm <sup>2</sup> stranded or 1.2mm <sup>2</sup> stranded or 1.5mm <sup>2</sup> stranded or 2.2mm <sup>2</sup> or 2.5mm <sup>2</sup> stranded or 4mm <sup>2</sup> stranded or 6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded.
2.5mm <sup>2</sup> solid with:	0.9mm <sup>2</sup> stranded or 1.2mm <sup>2</sup> stranded or 2.2mm <sup>2</sup> solid or 2.5mm <sup>2</sup> solid or 4mm <sup>2</sup> solid or 6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded
2.5mm <sup>2</sup> stranded with:	2.5mm <sup>2</sup> stranded or 4mm <sup>2</sup> stranded or 6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded
4mm <sup>2</sup> stranded with:	4mm <sup>2</sup> stranded or 6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded
6mm <sup>2</sup> stranded with:	6mm <sup>2</sup> stranded or 10mm <sup>2</sup> stranded
10mm <sup>2</sup> stranded with:	10mm <sup>2</sup> stranded

Alternatively, the following THREE of conductor combinations may be fitted in one terminal  
Two 2.5mm<sup>2</sup> solid conductors and one 6mm<sup>2</sup> stranded conductor

### SCHEDULE OF LIMITATIONS FOR HTB 6 TERMINALS:

- 1) Leads connected to the terminals shall have insulation extending to within 3mm of the terminal throat and the bare end of each lead shall not extend more than 3mm beyond the other side of the slot and shall remain straight. Maximum stripping length 16mm.
- 2) The terminal cap of each terminal, used and unused, shall be fully tightened down by the end user.
- 3) Conductors of different sizes and configurations shall not be inserted into the same terminal throat/slot except for the specific combinations listed in Tables 1 & 2.
- 4) When installed in an enclosure the creepage and clearance distances between the terminals, adjacent equipment and enclosure walls must comply with the requirements of IEC/EN 60079-7.
- 5) When installed in plastic enclosures, there shall be at least 3mm clearance between the inside of the removable cover/lid of the enclosure and the terminal screws after the connections have been made and the terminal screws and cover/lid have been fully tightened down.
- 6) For conductor sizes less than 1mm<sup>2</sup> but not less than 0.5mm<sup>2</sup>, the maximum current rating shall not exceed 1 amp.

Declaration of Conformity in accordance with European Directive 2014/34/EU and UK Statutory Instrument 2016/1107

Manufacturer: Hawke International, Oxford Street West, Ashton-under-Lyne, OL7 0NA, United Kingdom

Equipment: PL6 Enclosure Series

Provisions of the Directive fulfilled by the Equipment: Group II Category 2G Ex eb IIC T\* Gb, II 2D Ex tb IIC T\*\*C Db IP66  
Group II Category 2G Ex ib IIC T\* Gb, II 2D Ex ib IIC T\*\*C Db IP66  
Group II Category 1G Ex ia IIC T\* Ga, II 1D Ex ia IIC T\*\*C Da IP66

Harmozized Standards used: EN 60079-0:2018, EN60079-7:2015+A1:2018, EN60079-11:2012, EN60079-31:2014

Notified Body for EU-Type Examination: SGS Fimko 0598 Helsinki Finland  
EU-type Examination Certificate: Baseefa06ATEX0117X  
Notified Body for production: 0598

Approved Body for UK-Type Examination: SGS Baseefa 1180 Buxton UK  
UK-type Examination Certificate: BAS21UKEX0047X  
Approved Body for production: 1180

On behalf of the above named company, I declare that on the date the equipment, accompanied by this declaration, is placed on the market the equipment conforms with all technical and regulatory requirements of the above listed directives.

  
Andrew Reid  
Technical Manager