

## NEMA SIZE 2 SINGLE POLE S UNDER VOLTAGE RFI AY FRONT CONNECTED FOLIO 7A FOR DC OPERATION

## INSTRUCTIONS

RATING: Relay rating is 8, 12, 25, or 50 amperes continuous depending upon blowout coil supplied.

ELECTRICAL INTERLOCKS: These consist of stationary contacts mounted on the base and a moving contact attached to the magnet arm. The moving contact should provide  $\frac{1}{8}$  " follow-up when the magnet arm reaches its limit of travel, either completely closed or completely opened. The rating of these electrical interlocks is as follows:

	Max. Inrush	Cont. Amps.	Rupturing Capacity Amps. Inductive			
			115V.	2507.	440V.	550V.
A.C. D.C.	30 30	10 15	10 2.5	10 1.0	5 .4	5 .4

OPERATING COILS: Continuous duty operating coils are furnished for 115 volts and 230 volts. For 550 volts, the 230 volt coil is used and connected in series with a suitable resistor.


To remove the coil, loosen and rotate the stop plate out of the way and loosen the screws securing the spring retaining plate to the frame. Compress the arm spring and unhook the spring pin from the spring plate. The magnet arm may then be worked out of its bearing, exposing the coil. Remove core cap and coil terminal screws.

The relay will pick up and seal on 80% normal voltage, with the coil hot, will stand 110% voltage continuously, and will hold in to approximately 15% of normal voltage.

Time delay dropout can be provided by the addition of a condenser and resistor to give time delays of .3, A, .6, or .8 seconds.

MAGNET AIR GAP: The air gap is provided by means of a nonmagnetic spacer between the core and the frame which are held together by a brass screw. The armature seals directly against the core plate. See that this point of contact is free of any sticky, foreign material.

BEARINGS: Knife edge bearings are used and require no oiling. After assembly or adjustment, merely see that the knife edge bearing is properly located in its seat so that the arm moves freely. The arm spring has no adjustment but is sufficient to maintain the magnet arm properly in its bearing.



CONTACTS AND CONTACT SPRINGS: The contacts have coin silver facing and the follow-up with new contacts is  $1/4\,^{\prime\prime}$  which is equivalent to  $\frac{1}{8}$ " when measured on the contact arm opposite the contact spring pin. When contacts wear through the silver facing, the contacts should be replaced. The contact spring pressure is not adjustable. The initial pressure should be approx, one pound, and the final sealed pressure approx. 1  $\frac{1}{2}$  pounds. There is sufficient tolerance in the assembly of arms to permit alignment of the contacts. When replacing contact tips, see that they are properly aligned and that the contact springs do not bind. Always have the arc shields fully down when operating the relay under load.


(Continued on Page 4)

May, 1968

Page 2



NEMA SIZE 2 SINGLE POLE S UNDER VOLTAGE RELAY FRONT CONNECTED, FOLIO 7A





Page 3

## NEMA SIZE 2 SINGLE POLE S UNDER VOLTAGE RELAY FRONT CONNECTED, FOLIO 7A

NOTE: Indented items are component parts of item immediately preceding.

Item No.	List No.	Description	Item No.	List No.	Description
1	SS-0746-A	Assembled Arc Shield, Complete	39	EL-2-A	Control Circuit Arm, complete for Open and
2	SS-0770	Arc Shield, 2 req'd.			Closed Control Circuit
3	\$5-0753	Blowout Ear, 2 reg'd	40	EL-47	Control Circuit Arm, only
<b>⊗</b> 4	29418-14648	Binding Post	41	EL-62	Control Circuit Support
5		8-32x%6" R.H. Aluminum Screw		\$\$-0795	Spring Plate
6		1/4"-20x1/2" H.Sti. Machine Screw	43		10-24x½" R.I. Screw and Lk. Washer, 2 req'd
7	ZO-1150	Cup Washer, 2 req'd	44		10-24x1" R.I. Screw and Lk. Washer, 2 req'd
8	S-0317-A	Assembled Terminal Block	45	55-0922-A	Armature
9	SS-0781	Blowout Core (Not Shown)	46	SS-0796-A	Assembled Contact Bracket
10		10-24x1¾″ R.I. Screw, Nut and Lk. Washer	47		1/4"x1/2" Cotter Pin
11	SS-0750	Contact Bracket	48	ZS-0349	Spring Guide
12		Base, Advise Name Plate marking	†49	55-0896	Contact Spring.
13	55-0806	Stop Bar			
14	SS-0827-A	Assembled Frame	50	SS-0786	Guard
15	L-1721	Coil Terminal Stud, for 1" Base	51	SS-0754	Contact Finger, only
16	L-1722	Coil Terminal Stud, for 11/4" Base	52	A58895-851-58 SS-0898	Contact tip (silver faced) (For Relays)
1 <i>7</i>		10-24x¾" R,Stl. Mach. Screw and Lk. Washer		`	•
118	55-0782-AE	Operating Coil, 115 volt	†53	SS-0755-AS SS-0755-A	Aux. Contact arm (For Relays)
†19	SS-0785-AE	Operating Coil, 230 volt	54		14"-20x34" Everdur Hex. Machine Screw and
20	55-0798	Spring Retaining Plate			lk. Washer
21		10-24x3/8" R.I. Screw and Lk. Washer, 2 reg'd.	55	LT-1067	Core Cap
†22	EL-109-A	Assembled Contact	56	S-0107-A	Assembled Core
23		10-32x¾″ R. Stl. Mach. Screw and Lk. Washer	57	55-0803	Non-Magnetic Spacer (At rear of Core, no
24	EL-100-A	Contact Block			shown)
†25	55-0802	Arm Spring	58	\$\$-0805	Stop Plate
26	FP-28H1-10	Terminal	59		¼"-20x¾" H.I. Cap Screw and Ik. Washe
27	FP-28C20	Terminal, 2 reg'd,	60		1/4"-20x1/2" H.J. Cap Screw and Lk. Washe
28		1/4"-20x1/2" H. Sil. Machine Screw and 1k. Washer		( A50005-042-50 ( A50005-040-01	Contact Tip (silver faced) (For Relays) Contact Tip (For Contactors)
29	\$-0317-A	Assembled Terminal Block	62	\$\$-0752	Arc Horn
30		½2"x¾" cotter pin	63		10-24x1½″ R.i. Mach. Screw, Nut and Lk Washer
31	55-0769-A	Assembled Spring Pin		SS-0867-A	Blowout Coil, for 8 Amp. Service
†32	S-0305-A	Assembled Connector		SS-0891-A	Blowout Coil, for 12 Amp. Service
33		1/4"-20x1/2" H.I. Cap Screw and Lk. Washer	64	SS-0748-A SS-0747-A	Blowout Coil, for 25 Amp. Service
†34	EL-84-A	Contact Bridge, 1 req'd. for Item 38, 2 req'd. for Item 39	65		#6x5%" Wafer Hd. Type "U" Drive Screw 2 req'd
35	EL-87	Spring Retainer, 2 req'd	66	29418-14128	Binding Post, 3 req'd.
†36	EL-49	Spring	<b>●</b> 67	22955-14489	Binding Screw, 3 reg'd
37		10-24x¾″ R.I. Screw and Lk. Washer, 4 reald.	68	SS-0771	Arc Shield Spacer, 2 req'd
38	EL-1-A	Control Circuit Arm, complete for Open or Closed Control Circuit	†69	\$\$-0828-A	Assembled Connector, for Use on Relays with out Control Circuit

†Essential Parts for General Maintenance.


•Minor revisions since previous issue



May, 1968

## NEMA SIZE 2 SINGLE POLE S UNDER VOLTAGE RELAY FRONT CONNECTED, FOLIO 7A

This contact assembly has been designed to provide extra contact wipe. Where greater wipe is needed on existing contactors, the necessary parts can be purchased separately or the new complete assembled contact arm SS-0955-A (as illustrated below) can be installed quickly and easily.



item No.	List No.	Description		
80	SS-0957-A	Assembled Contact Bracket		
81	\$\$-0958	Armature Centering Plate		
82	55-0960	Spring Plate		
83	\$\$-0959	Retaining Plate		
34		10-24 x ¾" R.I. Machine Screw and Lk. Washer		

NOTE: Parts not numbered are the same as parts on Page 2.

ADVISE NAMEPLATE MARKING WHEN ORDERING SPARE PARTS