



**KILLARK®**

## INSTALLATION, OPERATION & MAINTENANCE DATA SHEET

“EZ” / “HLEZ” - “Silicone Free” SERIES MOUNTING ACCESSORIES



PENDANT



WALL BRACKET



CEILING



25° STANCHION

## “EZ” / “HLEZ” - “Silicone Free” SERIES MOUNTING ACCESSORIES

### **CAUTION:**

Before installing, make sure you are compliant with area classifications, failure to do so may result in bodily injury, death and property damage. Do not attempt installation until you are familiar with the following procedures. All installation must comply with the applicable Electrical Code.

Make sure that the circuit is de-energized before starting installation or maintenance.

Verify that the installation is grounded. Failure to ground will create electrical shock hazards, which can cause serious injury and or death.

Technical information, advice and recommendations contained in these documents is based upon information that Killark believes to be reliable. All the information and advice contained in these documents is intended for use only by persons having been trained and possessing the requisite skill and know-how and to be used by such persons only at their own discretion and risk. The nature of these instructions is informative only and does not cover all of the details, variations or combinations in which this equipment may be used, its storage, delivery, installation, check out, safe operation and maintenance. Since conditions of use of the product are outside of the care, custody and control of Killark, the purchaser should determine the suitability of the product for his intended use, and assumes all risk and liability whatsoever in connection therewith.

**KILLARK®**



3940 Dr. Martin Luther King Drive  
St. Louis, MO 63113

P/N KIL00912461 FORM NO. K1272 9/04 ERO-6-41-04

Page 1 of 2



FIGURE 1




FIGURE 2



FIGURE 3




FIGURE 4

## 1. INSTRUCTIONS FOR INSTALLATION

**NOTE:** Outlet box threads must be lubricated to prevent galling. Lightly lubricate with **Hi temp Silicone free** grease, for ease of future maintenance.

**NOTE:** Refer to marking on fixture nameplate for required supply wire temperature rating. Fixture mount must be grounded. Connect the ground wire to the green screw provided inside the mounts (except wall bracket mount).

For Marine applications, all wiring including supply wires, must be stranded wire and meet the USCG (CFR46) Section (110-113).

## 2. PENDANT MOUNT (See Figure 1):

Install pendant mount to conduit and secure with locking set screw. Remove terminal block from the mount by loosening (2) mounting screws. Connect the ground wire to the green screw. Connect supply wires to the terminal block. Reinstall terminal block and securely tighten it in place.

## 3. CEILING MOUNT (See Figure 2):

Install ceiling mount on support surface, using the (4) external mounting holes. Remove terminal block from the mount and connect electrically, as described under Pendant Mount. Plug unused conduit entries with close-up plugs provided.

## 4. STANCHION MOUNT (See Figure 3):

Install stanchion mount on conduit and tighten locking set screw. Remove terminal block from the mount and connect electrically as described under Pendant Mount above.

## 5. WALL BRACKET MOUNT (See Figure 4):

Install wall bracket mount on support surface, using the (2) external mounting holes. Unscrew and remove inspection cap 'A'. Pull out Black (Line) 'B', White (Neutral) 'C' and Green (Ground) 'D' wires through the inspection hole (wires will extend out about 6 inches). Use wire nuts 'E' to connect ground & power wires to the above extensions. Push the wires back in and replace the cap 'A'. Plug unused conduit openings with close-up plugs provided.