



KILLARK®

INSTALLATION, OPERATION & MAINTENANCE DATA SHEET

KILLARK SEALING COMPOUND SC11W



KILLARK SEALING COMPOUND SC11W

CAUTION:

Before installing, make sure you are compliant with area classifications, failure to do so may result in bodily injury, death and property damage. Do not attempt installation until you are familiar with the following procedures. All installation must comply with the applicable Electrical Code.

Make sure that the circuit is de-energized before starting installation or maintenance.

Verify that the installation is grounded. Failure to ground will create electrical shock hazards, which can cause serious injury and or death.

IMPORTANT:

Please read these instructions carefully before installing or maintaining this equipment. Good electrical practices should be followed at all times and this data should be used as a guide only.

Technical information, advice and recommendations contained in these documents is based upon information that Killark believes to be reliable. All the information and advice contained in these documents is intended for use only by persons having been trained and possessing the requisite skill and know-how and to be used by such persons only at their own discretion and risk. The nature of these instructions is informative only and does not cover all of the details, variations or combinations in which this equipment may be used, its storage, delivery, installation, check out, safe operation and maintenance. Since conditions of use of the product are outside of the care, custody and control of Killark, the purchaser should determine the suitability of the product for his intended use, and assumes all risk and liability whatsoever in connection therewith.

KILLARK®

Chalmit

Victor
Lighting

Vantage
Technology

RIG POWER

HAWKE
International

3940 Dr. Martin Luther King Drive
St. Louis, MO 63113

P/N KIL00921442 FORM NO. K1442 ERO-8-037-14 10/14

Page 1 of 2

DIRECTIONS FOR INSTALLATION

1. Prior to mixing, the pouring spout needs to be in an upright position making sure that there is no dry compound in the pouring spout.
2. For mixing, squeeze the pouch until inner liquid container breaks. Continue to squeeze outer pouch for three minutes until compound and water are thoroughly mixed making sure that there is no dry compound left in the spout, corners or anywhere else in the package.
3. The proper consistency is fluid enough to pour slowly, like thick gravy. Use pouch contents within 15 minutes of mixing. **NOTE:** Discard any material that becomes too stiff to use. Never attempt to restore workability by stirring in more water.

CAUTION: Sealing compound is to be mixed only at a temperature above 40°F/4°C and only poured into fittings that have been brought to a temperature of 40°F/4°C. Poured seals must not be exposed to temperatures below 40°F/4°C for at least 72 hours. Compound must be allowed 72 hours to cure to full strength before energizing the system.

	ENY	EYS	EY/EYD
1/2"	7	3	11
Z	5	3	5
1"	3	1	2

FOR INDUSTRIAL USE ONLY



3940 Dr. Martin Luther King Drive
St. Louis, MO 63113

P/N KIL00921442 FORM NO. K1442 ERO-8-037-14 10/14

Page 2 of 2