
# HJS Series, Cat6 & Cat6A Shielded Jack


Mounting Instructions






Step 1: Strip off at least 25mm of jacket from end of cable.

NOTES: IDC is suitable for 22~24 AWG wires.




Step 2: Insert the wires into the cap through the holes. Lay the wires to the correct positions based on the color code (T568A/T568B)



Step 3:

Cut the excess wires off. The tips of the wires should protrude no more than 0.5mm.



Step 4:


Put the cap on the IDC tower. The arrows on the jack and the cap should face the same direction. Put the cap into position.

HUBBELL PREMISE WIRING • HUBBELL INCORPORATED (Delaware) • 23 Clara Drive, Mystic, CT 06355 • Ph: (800) 626-0005 • Fax: (860) 535-8328 • www.hubbell-premise.com

# HJS Series, Cat6 & Cat6A Shielded Jack

Mounting Instructions





Step 5:

jaw.

Close the jaws until fixed. Fix the cable tie to the

### Step 6:


shielding lug.

#### Step 7


Cut the excess tie wrap off as close to the strain relief ring as possible. Ensure that the end of tie wrap is positioned upward

Screwdriver

### Disassembly Instruction:



Step 2: Insert the screwdriver into the slot and rotate it to open the



HUBBELL PREMISE WIRING • HUBBELL INCORPORATED (Delaware) • 23 Clara Drive, Mystic, CT 06355 • Ph: (800) 626-0005 • Fax: (860) 535-8328 • www.hubbell-premise.com