

IN-LINE CORD SWITCHES

Installation Instructions

Cat. No.	Wire Size
RS101W	No. 18/2 – 16/2 AWG SPT
RS1011	No. 18/2 – 16/2 AWG SPT

GENERAL INFORMATION:

CAUTION: RISK OF ELECTRIC SHOCK.

- Unplug the cord before installation.
- Never wire energized electrical components.


CAUTION: USE COPPER CONDUCTORS ONLY.

NOTICE:


- For installation by a qualified person in accordance with national and local electrical codes.
- Verify that the cord type, device type and rating are suitable for this application prior to installation.

INSTALLATION:

- Determine the location on the cord where the switch will be installed.
 - Identify the ribbed and smooth side of the cord.
 - Carefully slit the cord approximately 1" and then spread the smooth and ribbed sides apart. (See illustration)
- Note:** Be careful not to cut into the cord insulation exposing the conductor.



- Identify the smooth side of the cord and cut apart at the center of the slit section.
- Place the ribbed side of the cord into the channel passing around the switch mechanism. (See illustration)



- Place each leg of the smooth side of the cord into the separated channel on the other side of the switch mechanism.
- Align the halves of the switch, press together and tighten the four screws to 4 – 6 in-lbs.

Note: Do not over-tighten the assembly screws.

