








POLE TOP BRACKETS	Cat.#		
	Job	Type	
			Approvals

ORDERING INFORMATION

SPOKE TYPE BRACKETS

(order as separate part #, field installed)

Catalog Number	Description	Max allowable load per tenon	Bracket EPA, MAX.	Bracket weight, MAX
SB1	Single	60 lbs (27.2 kg)	0.6	18
SB2-180	Twin, 2@180	60 lbs (27.2 kg)	1.0	27
SB2-90	Twin, 2@90	60 lbs (27.2 kg)	0.8	27
SB3-120	3 @ 120	60 lbs (27.2 kg)	0.9	36
SB3-90	3 @ 90	60 lbs (27.2 kg)	1.0	36
SB4-90	4 @ 90	60 lbs (27.2 kg)	1.0	45



A	B
9"	8" , 12" , 18" , 30"
229 mm	203 mm, 305 mm, 457 mm, 762 mm

ORDERING INFORMATION – ORDERING EXAMPLE: SB-2-180-PT25-BL

SB	-		-		-		-	
		CONFIGURATION		LENGTH		POLE TENON SIZE		COLOR
		1		8"		PT20 2" pipe tenon (2.38" O.D.)		DB Dark bronze textured
		2-180		12"		PT25 2.5" pipe tenon (2.88" O.D.)		BL Black textured
		2-90		18"		PT35 3.5" pipe tenon (4.0" O.D.)		WH White textured
		3-120		24"				GR Gray textured
		3-90		30"				PS Platinum silver smooth
		4-90						GYS Light gray smooth
								BZT Bronze textured
								BBT Basic black textured

Hubbell Outdoor • 701 Millennium Boulevard • Greenville, SC 29607 • Phone: 864-678-1000

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2017 HUBBELL LIGHTING, All Rights Reserved • For more information visit our website: www.hubbellighting.com • Printed in USA **POLEBRKTS-SPEC** **SEPTEMBER 22, 2017 2:03 PM**



Beacon Products • 2041 58th Avenue Circle East Bradenton, FL 34203 • Phone: 800-345-4928

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2017 BEACON PRODUCTS, All Rights Reserved • For more information visit our website: www.beaconproducts.com • Printed in USA **POLEBRKTS-SPEC** **SEPTEMBER 22, 2017 2:03 PM**



HUBBELL
Lighting