

4/5-Gang Recessed Floor Boxes

The 4/5-Gang box provides a uniform look with rectangular or round covers that are available in several finishes to complement existing décor. Electrical devices are mounted vertically and are mounted to the plate prior to securing it to the box. Four removable knockout plates allows for 2" conduit feed-thru allowing for dual service capacity.

Box





- 3.75" deep wiring device chambers
- 14 gauge galvanized sheet metal
- Optional fusion-bonded, green epoxy paint for on-grade use
- Floor boxes accept field installed metallic 2" threaded hubs and PVC hubs
- Patented PVC conduct adapters can be used on the floor boxes—CFBHUB200PVC (2 in. feed-thru) and CFBHUB125PVC (1¼" feed-thru)
- Pre-pour and post-pour adjustment
- Labor saving, easy mount device plates



Cover

- Rectangular covers- maximum static load of 1,500 lbs. with 2x safety factor
- Round covers- maximum static load of 1,000 lbs. with 2x safety factor
- Available in round and rectangular, recessed and furniture feed styles
- Recessed covers open a full 180°
- Large hide-away cable egress doors
- Listed to UL 514A and UL Scrubwater compliant
- Die cast aluminum cover construction
- All covers are ADA compliant

4/5-Gang Floor Boxes

Style	Rectangular Cover		Round Cover	
				
Standard Box	CFB45G55E	-	CFB45G55RE	-
Corrosion-Resistant (On-grade)	-	CFB45G55CRE	-	CFB45G55RCRE
Recommended Pour Depth	6.00" (152.4)		6.25" (158.8)	
Min. Depth of Pour	5.50" (139.7)		6.25" (158.8)	



Rectangular Covers



Available finishes

Aluminum Powder Coat Black Powder Coat Brass Powder Coat Bronze Powder Coat Satin Nickel Powder Coat

Finish	Surface Cover Dimensions 11½ in. x 10 in.		Flush Cover Dimensions 10½ in. x 9 in.	
	Without Insert	With Insert	Without Insert	With Insert
Aluminum Powder Coat	610GCCVRALU	610GCCVRALUC	610GTCVRALU	610GTCVRALUC
Black Powder Coat	610GCCVRBK	610GCCVRBK	610GTCVRBK	610GTCVRBK
Brass Powder Coat	610GCCVRBRS	610GCCVRBRS	610GTCVRBRS	610GTCVRBRS
Bronze Powder Coat	610GCCVRBRZ	610GCCVRBRZ	610GTCVRBRZ	610GTCVRBRZ
Satin Nickel Powder Coat	610GCCVRNK	610GCCVRNK	610GTCVRNK	610GTCVRNK




8 Inch Round Covers



Available finishes

Brushed Aluminum Black Powder Coat Brass Plated Bronze Plated Gray Powder Coat Satin Nickel Plated

Finish	Flush Surface
Brushed Aluminum	CFBS1R8CVRALU
Black Powder Coat	CFBS1R8CVRBLK
Brass Plated	CFBS1R8CVRBRS
Bronze Plated	CFBS1R8CVRBRZ
Gray Powder Coat	CFBS1R8CVRGRY
Satin Nickel Plated	CFBS1R8CVRNKL



Plates for use in SystemOne 4/5-Gang floor boxes

Cat. No.	Plate Style	Cat. No.	Plate Style
FB10MPREC	(1) Decorator opening	FB10MPDUP	(1) Duplex opening
FB10MPBNK	1-gang blank plate	FB10MPKEY	(1) Opening with Hubbell 6-port frame for keystone jacks
FB10MPTRAC	(2) Openings for (6) Ortronics TracJack®	FB10MPFT	Cable feed through with bushing
Cat. No.	Two Gang Plate Style	Cat. No.	Two Gang Plate Style
FB10MP2A	Decorator openings	FB10MP2E	Duplex openings
FB10TLX	(1) Simplex opening 1.40 in. diameter	FB10TLA	(1) Twist-Lock® opening 1.60 in. diameter
FB10MP2B	(6) 1U Hubbell iStation modules	FB10MPMAAP	Siemon CT Series
FB10MPAAP	(4) Extron® AAP openings		
Cat. No.	Three Gang Plate Style	Cat. No.	Three Gang Plate Style
FB10TLY	(2) Simplex opening 1.40 in. diameter	FB10TLB	(3) Twist-Lock® opening 1.60 in. diameter
FB10MP3GAPP	(1) Opening for appliance receptacle, requires 2-gang industry plate for trim out		
Cat. No.	Five Gang Plate Style	Cat. No.	Five Gang Plate Style
FB10TLC	(3) Simplex opening 1.40 in. diameter	FB10TLZ	Twist-Lock® opening 1.60 in. diameter
FB10MPNEMA2XG	(2) 2-gang. Meets NEMA spacing. Ideal for Crestron® DM –TX product and power. Ships with low voltage divider.	FB10MPNEMA4G	(4) Single service openings utilizing NEMA wallplate. (No low voltage divider option.)

Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

Pre-Wired Devices Plates

Description	Type	15A	20A
Duplex, gray	Standard	PWFB10MPCR15GRY	PWFB10MPCR20GRY
	Tamper-Resistant	PWFB10MPCR15GRYTR	PWFB10MPCR20GRYTR
Decorator, gray	Standard	PWFB10MPDR15GRY	PWFB10MPDR20GRY
	Tamper-Resistant	PWFB10MPDR15GRYTR	PWFB10MPDR20GRYTR



A proud member of the Hubbell family.