

# Quick Turn Custom Fiber Trunk Assemblies Program

## Pre-Terminated Fiber Trunk Quick Ship Program

Hubbell's flexible modular cabling system provides the customization and bandwidth you need for today's high-performance networks. FIBERHUBB™ MPO and LC assemblies simplify your network with less cabling and lower installation costs than legacy infrastructure.




### Program Details

- Standard part numbers readily available in stock
- Lead times as little as 2-5 Days ARO
- Easy Product Configuration & Quick Quoting Process
- Price list with standard parts and per FT adder
- Assembled in USA
- Additional custom options available with varying lead times.

### Product Features

- Available in OM4 & SM Plenum fiber with LC or MPO Connectors
- Customizable length and labeling available in all fiber counts
- Built with Corning ClearCurve® fiber
- Premium low-loss connector options provide easy polarity and gender field changes
- 100% Tested with Test Results Included

Scan QR Code Below



Call your local Territory Manager for pricing & information today

### Catalog Number Configurator

**\*All Indoor Trunks Begin with FPC-LTP for Loose Tube Plenum Cable\***

Fiber Count	Cat #	Fiber Type	Cat #	Jacket Color	Cat #	End A	Cat #	End B	Cat #	Polarity	Cat #	Labeling	Cat #	Length	Cat #	Pulling Eye	Cat #
12	<b>12</b>	OM4	<b>M4</b>	Aqua (OM4)	<b>AQ</b>	MPO	<b>MPO</b>	MPO	<b>MPO</b>	Type A	<b>A</b>	Custom label	<b>CL</b>	Feet	<b>1-1999</b>	Yes	<b>PE</b>
24	<b>24</b>	OS2	<b>SM</b>	Yellow (OS2)	<b>YW</b>	LC	<b>LC</b>	LC	<b>LC</b>	Type B	<b>B</b>					No	<b>NPE</b>
48	<b>48</b>			Any	<b>XX</b>			Open	<b>X</b>	Type C	<b>C</b>						
72	<b>72</b>																
96	<b>96</b>																
144	<b>144</b>																

Example part: **FPC-LTP12M4AQ-MPO-MPO-A-10FT-NPE**

Fiber cord, plenum, 12F, OM4, MPO to MPO, Type A, 10 Feet, No pulling eye  
(Assumes FPC-LTP for loose tube plenum cable construction)


\*Above configuration table represents common builds. Custom fiber counts, cable construction, and jacket colors available upon request. Contact a Hubbell representative for more information.

# Fiber Optic Cable

**FIBERHUBB**<sup>™</sup>  
Let Hubbell Be Your Fiber Connection

## Core cable offering stocked for prime availability

- Fully supported by the Hubbell Mission Critical<sup>®</sup> 25-year warranty
- Custom cable cuts available upon request
- Lead times from 2-5 days after receipt of order for stocked cable
- Rugged constructions available for both indoor and indoor/outdoor applications
- RoHS compliant, flame-retardant cable
- E-Z strip buffer with new dash style color stripes for contractor-friendly termination
- Manufactured in the USA



### Plenum Indoor Interlock Armored Tight Buffer

Strand Count	Fiber Type	Color	Diameter Inches (mm)	Cable Weight (lb/ft)	Reel Capacity	Catalog No.
6	OM3	Aqua	0.512 (13.0)	0.165	6,000 (48" reel)	<b>HFCD15006P3</b>
6	OS2	Yellow	0.512 (13.0)	0.165	6,000 (48" reel)	<b>HFCB15006PS</b>
12	OM4	Aqua	0.579 (14.7)	0.170	6,000 (48" reel)	<b>HFCD15012P4</b>
12	OS2	Yellow	0.579 (14.7)	0.170	6,000 (48" reel)	<b>HFCD15012PS</b>
24	OM4	Aqua	0.638 (16.2)	0.190	5,000 (48" reel)	<b>HFCD15024P4</b>

*HFCB designates Hubbell Premise Wiring branded cable jacket*

### Plenum and Riser Indoor/Outdoor Tight Buffer

Strand Count	Fiber Type	Color	Diameter Inches (mm)	Cable Weight (lb/ft)	Reel Capacity	Catalog No.
6	OM3	Black	0.189 (4.8)	0.020	10,000 (30" reel)	<b>HFCD14006P3BK</b>
6	OS2	Black	0.189 (4.8)	0.020	10,000 (30" reel)	<b>HFCD14006RSBK</b>

To learn more about availability of Hubbell Core Series cable, reach out to your local Hubbell distributor or representative.



A proud member of the Hubbell family.