



**DG0667R**

600 Series




Stainless Steel Solid

PROJECT ID/  
CONTRACT NO: \_\_\_\_\_

LOCATION: \_\_\_\_\_

**ENGINEERING SPECIFICATION:**

POLYCAST® DG0667R IS DESIGNED FOR PIPE RUNS, E.G., SECONDARY CONTAINMENT, OR CABLE RUNS. ESPECIALLY SUITED FOR AREAS EXPOSED TO MILD ACIDS OR BASES. REMOVABLE COVER ALLOWS FULL ACCESS. FOR USE WITH GRATE HOLD-DOWN DEVICE PART NO. DA0642S (NOT SHOWN). THIS GRATE IS ADA COMPLIANT. AVAILABLE IN 24" OR 48" LENGTHS.



**DIN APPLICATION LOAD CLASS C:**  
Curb sides, highway shoulders, and parking areas  
Designed for a distributed pressure of 56,200 lbs (250 kN).

**Meets the following Standards & Specifications:**

- DIN 19580 / DIN EN 1433 Drainage Channels for Vehicular and Pedestrian Areas
- The Americans with Disabilities Act of 1990: 4.5.4
- ASME A112.6.3: Section 7.12 Heel Resistant Strainers and Grates
- Australian Standard AS 3996-2006 Clause 3.3.6



www.polycastrain.com  
Toll Free Number:  
1-800-346-3062