

***Tamper-Resistant and
Weather Resistant Receptacles***
— the new standard in electrical safety.



BRYANT



Tamper-Resistant and Weather Resistant Duplex Receptacles

Why Tamper-Resistant?

The tamper-resistant code requirement is all about safety.

- Approximately 2,400 children per year suffer electrical outlet related injuries.
- For years, the design and use of tamper-resistant receptacles has been proven effective in pediatric areas and hospital installations nationwide. It makes sense to have them in homes as well.
- The additional cost per device is minimal and well worth it.
- Required by states that adopt 2008 NEC®.

What Do These Code Requirements Mean?

Tamper-Resistant



Tamper-Resistant Duplex Receptacles

Complies with NEC 406.11
Complies with NEC 210.52
Complies with NEC 511.18c

All 125V, 15A and 20A receptacles shall be listed tamper-resistant receptacles per NEC Article 406.11, "Tamper-Resistant Receptacles in Dwelling Units".



These symbols appear throughout for easy identification.



Schools



Pediatric Healthcare Facilities



Lobbies



Day-Care Centers

Tamper-Resistant (TR) receptacles incorporate internal mechanisms to limit access to energized internal components.

TR receptacles are a mandatory requirement in the 2008 NEC for use in dwelling unit outlets. There are also many other applications where the use of TR receptacles can provide an additional level of electrical safety such as Schools, Pediatric Facilities, Lobbies and Day-Care Centers.

Weather Resistant



Weather Resistant Duplex Receptacles

Complies with NEC 406.8(A)

All 125V and 250V, 15A and 20A receptacles shall be listed as weather resistant type per NEC Article 406.8, "Receptacles in Damp and Wet Locations".



Transit Centers



Washdown Areas



Amusement Parks



Open Air Markets


Weather Resistant (WR) receptacles installed outdoors or in wet and damp locations are subject to more demanding temperature variations, direct sunlight and unusual mechanical abuse than those in a typical dry environment. Bryant's WR receptacles are specifically designed to withstand these environments and conditions.

Ground Fault Receptacles



- Patented tamper-resistant protection
- Limits improper access to energized contacts
- No power at face if reverse wired
- Flashing RED LED, indicates device has lost capability to provide ground fault protection
- Open terminal design
- Accepts fork terminals
- Automatic grounding feature and internal back wire facilitate installation


Commercial & Hospital Grade Ground Fault Receptacles



**Commercial Grade
Tamper-Resistant
Weather Resistant
Back & Side Wired
15A 125V
NEMA 5-15R**

Color
Almond
Black
Brown
Gray
Ivory
Light Almond
Office White
Red
White

**GFTR15AL
GFTR15BK
GFTR15
GFTR15GY
GFTR15I
GFTR15LA
GFTR15OW
GFTR15R
GFTR15W**



**Hospital Grade
Tamper-Resistant
Weather Resistant
Back & Side Wired
15A 125V
NEMA 5-15R**

**GF82ALTR
GF82BKTR
GF82TR
GF82GYTR
GF82ITR
GF82LATR
GF82OWTR
GF82RTR
GF82WTR**

Color
Almond
Black
Brown
Gray
Ivory
Light Almond
Office White
Red
White

**20A 125V
NEMA 5-20R**


**GFTR20AL
GFTR20BK
GFTR20
GFTR20GY
GFTR20I
GFTR20LA
GFTR20OW
GFTR20R
GFTR20W**

**20A 125V
NEMA 5-20R**

**GF83ALTR
GF83BKTR
GF83TR
GF83GYTR
GF83ITR
GF83LATR
GF83OWTR
GF83RTR
GF83WTR**

Commercial Grade Receptacles

Fashion Series®



• Self-grounding staple for fast and easy installation

• Durable construction using nylon face and base

• Easy access split circuit tab
• Accepts fork terminals

• Fashion Series® provides modern architectural appearance
• Decorator face

• Sturdy construction wrap-around galvanized steel strap

Commercial Grade Fashion Series® Receptacles



Color

Almond
Black
Brown
Gray
Ivory
Light Almond
White

**Back & Side Wired
15A 125V
NEMA 5-15R**

**DRS15AL
DRS15BLK
DRS15
DRS15GRY
DRS15I
DRS15LA
DRS15WHI**

**Tamper-Resistant
Back & Side Wired
15A 125V
NEMA 5-15R**

**DRS15ALTR
DRS15BLKTR
DRS15TR
DRS15GRYTR
DRS15ITR
DRS15LATR
DRS15WTR**

**Weather Resistant
Tamper-Resistant
Back & Side Wired
15A 125V
NEMA 5-15R**

**DRS15ALWRTR
DRS15BLKWRTR
DRS15WRTR
DRS15GRYWRTR
DRS15IWRTR
DRS15LAWRTR
DRS15WWRTR**

Color

Almond
Black
Brown
Gray
Ivory
Light Almond
White

**20A 125V
NEMA 5-20R**

**DRS20AL
DRS20BLK
DRS20
DRS20GRY
DRS20I
DRS20LA
DRS20WHI**


**20A 125V
NEMA 5-20R**

**DRS20ALTR
DRS20BLKTR
DRS20TR
DRS20GRYTR
DRS20ITR
DRS20LATR
DRS20WTR**


**20A 125V
NEMA 5-20R**

**DRS20ALWRTR
DRS20BLKWRTR
DRS20WRTR
DRS20GRYWRTR
DRS20IWRTR
DRS20LAWRTR
DRS20WWRTR**

Commercial Grade Receptacles Standard Duplex



Commercial Grade Standard Duplex Receptacles



Color	Tamper-Resistant Side Wired 15A 125V NEMA 5-15R	Tamper-Resistant Back & Side Wired 15A 125V NEMA 5-15R	Weather Resistant Back & Side Wired 15A 125V NEMA 5-15R	Weather Resistant Tamper-Resistant Back & Side Wired 15A 125V NEMA 5-15R
Almond	CRS15ALTR	CBRS15ALTR	CBRS15ALWR	CBRS15ALWRTR
Black	CRS15BLKTR	CBRS15BLKTR	CBRS15BLKWR	CBRS15BLKWRTR
Brown	CRS15TR	CBRS15TR	CBRS15WR	CBRS15WRTR
Gray	CRS15GRYTR	CBRS15GRYTR	CBRS15GRYWR	CBRS15GRYWRTR
Ivory	CRS15ITR	CBRS15ITR	CBRS15IWR	CBRS15IWRTR
Light Almond	CRS15LATR	CBRS15LATR	CBRS15LAWR	CBRS15LAWRTR
White	CRS15WTR	CBRS15WTR	CBRS15WWR	CBRS15WWRTR
Color	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R
Almond	CRS20ALTR	CBRS20ALTR	CBRS20ALWR	CBRS20ALWRTR
Black	CRS20BLKTR	CBRS20BLKTR	CBRS20BLKWR	CBRS20BLKWRTR
Brown	CRS20TR	CBRS20TR	CBRS20WR	CBRS20WRTR
Gray	CRS20GRYTR	CBRS20GRYTR	CBRS20GRYWR	CBRS20GRYWRTR
Ivory	CRS20ITR	CBRS20ITR	CBRS20IWR	CBRS20IWRTR
Light Almond	CRS20LATR	CBRS20LATR	CBRS20LAWR	CBRS20LAWRTR
White	CRS20WTR	CBRS20WTR	CBRS20WWR	CBRS20WWRTR

Bryant Quick-Tech™ Duplex Receptacles

Bryant's new Quick-Tech™ receptacle provides a quick and simple method to wire a receptacle!



Quick-Tech™ Pigtailed Terminal



QT6R1

Description

Clear Connector with 6" Leads - Solid Wire

Clear Connector with 6" Leads - Stranded Wire

Catalog Numbers

QT6R1

QT6R2

Quick-Tech™ Specification Grade Duplex Receptacles



QT5262I



Color

Almond
Black
Brown
Gray
Ivory
Light Almond
Red
White


15A 125V NEMA 5-15R

QT5262AL
QT5262BK
QT5262
QT5262GY
QT5262I
QT5262LA
QT5262R
QT5262W

20A 125V NEMA 5-20R

QT5362AL
QT5362BK
QT5362
QT5362GY
QT5362I
QT5362LA
QT5362R
QT5362W

Dimensions Inches (mm)



Quick-Tech™ Hospital Grade Duplex Receptacles



QT8200W



Color

Almond
Black
Brown
Gray
Ivory
Light Almond
Red
White


15A 125V NEMA 5-15R

QT8200AL
QT8200BK
QT8200
QT8200GY
QT8200I
QT8200LA
QT8200R
QT8200W


20A 125V NEMA 5-20R

QT8300AL
QT8300BK
QT8300
QT8300GY
QT8300I
QT8300LA
QT8300R
QT8300W

Dimensions Inches (mm)



Tamper-Resistant Receptacles



Residential Tamper-Resistant Performance

Protection is always available with tamper-resistant receptacles. They are reliable, automatic and permanent. With attention to design and performance, Bryant has developed a new shutter mechanism to enable tamper-resistance to be built into standard and decorator duplexes, single receptacles, floor boxes and other power devices. At Bryant, performance is our history, safety is our goal—now for your home.

Color	Standard Duplex Self-Grounding 15A 125V
Almond	RR15SALTR
Black	RR15SBKTR
Brown	RR15STR
Gray	—
Ivory	RR15SITR
Light Almond	RR15SLATR
White	RR15SWTR



Standard Duplex Quick Thread 15A 125V
RR15QALTR
RR15QBKTR
RR15QTR
—
RR15QITR
RR15QLATR
RR15QWTR



Decorator Duplex Self-Grounding 15A 125V
RRD15SALTR
RRD15SBKTR
RRD15STR
RRD15SGYTR
RRD15SITR
RRD15SLATR
RRD15SWTR



Color	Standard Duplex Cut Ears 15A 125V
Almond	RR15KALTR
Black	RR15KBKTR
Brown	RR15KTR
Gray	—
Ivory	RR15KITR
Light Almond	RR15KLATR
White	RR15KWTR



Standard Single Receptacle 15A 125V
RR151ALTR
RR151BKTR
RR151TR
RR151GYTR
RR151ITR
RR151LATR
RR151WTR



Standard Single Receptacle 20A 125V
RR201ALTR
RR201BKTR
RR201TR
RR201GYTR
RR201ITR
RR201LATR
RR201WTR



Color	Decorator Single Receptacle 15A 125V
Almond	RRD151ALTR
Black	RRD151BKTR
Brown	RRD151TR
Gray	RRD151GYTR
Ivory	RRD151ITR
Light Almond	RRD151LATR
White	RRD151WTR



Decorator Single Receptacle 20A 125V
RRD201ALTR
RRD201BKTR
RRD201TR
RRD201GYTR
RRD201ITR
RRD201LATR
RRD201WTR



Standard Combo SP Switch 15A 120V Receptacle 15A 125V
RC108ALTR
—
RC108TR
—
RC108ITR
RC108LATR
RC108WTR



Color	Standard Combo 3W Switch 15A 120V Receptacle 15A 125V
Almond	RC308ALTR
Black	—
Brown	RC308TR
Gray	—
Ivory	RC308ITR
Light Almond	RC308LATR
White	RC308WTR



Decorator Combo SP Switch 15A 120V Receptacle 15A 125V
RCD108ALTR
RCD108BKTR
—
RCD108GYTR
RCD108ITR
RCD108LATR
RCD108WTR



Decorator Combo 3W Switch 15A 120V Receptacle 15A 125V
RCD308ALTR
RCD308BKTR
—
RCD308GYTR
RCD308ITR
RCD308LATR
RCD308WTR



Tamper-Resistant and Weather Resistant Receptacles

—the new standard in electrical safety.



Contact Information

Regional Managers

Northeast Region Dave Jones

Office: 401-792-3976
Fax: 401-792-3926
e-mail: djones@hubbell.com

Southeast Region Tony Scenna

Office: 270-780-0303
Fax: 270-780-0304
e-mail: tscenna@hubbell.com

National Account Manager Modular/Mobile Homes & Recreational Vehicles Glenn Jensen

Office: 574-273-1243
e-mail: gjensen@hubbell.com

Midwest Region Randy Sengbusch

Office: 262-942-4827
Fax: 262-942-1883
e-mail: rsengbus@hubbell.com

Northwest Region Erich Leaverton

Office: 510-336-9574
Fax: 510-531-3892
e-mail: nleavert@hubbell.com

Southwest Region Rick Carlson

Office: 972-690-5601
Fax: 972-690-3933
e-mail: ricarlson@hubbell.com

Customer Service/ Technical Service 800-323-2792

For a searchable list of authorized distributors and sales agents,
visit our website at www.bryant-electric.com