

**HUBBELL**  
**Wiring Device-Kellems**

# Healthcare Solutions

From the creators of the first  
hospital-grade wiring devices








# Delivering reliable power for healthcare

Healthcare facilities and critical care spaces require 100% reliable power and data connections. We design products specifically to meet the needs of healthcare. Along with installation efficiency, ease of connection and secure power connectivity our products stand up in the most demanding environments.

Our compliant solutions ensure safety and enable simpler facility maintenance as well as better patient experience. They offer the quality our partners have grown to trust from 135 years of excellence and innovation. Everything you need for a rapidly changing environment.

## Innovative new products

From GFCIs and outlet assemblies to advanced illuminated receptacles and sanitary switches, we power innovation for medical facilities.



**EdgeConnect™  
Receptacles**



**SnapConnect®  
Receptacles**



**GFCI Receptacles**



**Illuminated  
Receptacles**



**Healthcare Outlet  
Assemblies**



**Power  
Strips**



**SCRUBSWITCH™  
Devices**



**inREACH™ Cord  
Reels**



**SCAN OR CLICK  
TO LEARN MORE**

# EdgeConnect™ Duplex Receptacles

New patented EdgeConnect screwless termination system delivers long-lasting terminations that are actually faster to install. No torque tools required—simply insert the wires, press the plunger, done! Strong levered steel springs eliminate termination screws and hold wires secure.

- Hospital grade
- Fits standard depth electrical boxes
- Adds performance and productivity gains
- No exposed terminal screws add safety



## EdgeConnect Duplex Receptacles

Description	Color	15A 125V	20A 125V
Heavy-duty, hospital grade duplex receptacle with EdgeConnect technology, finder groove, 2P 3W	Gray	<b>HBL8200STGY</b>	<b>HBL8300STGY</b>
	Ivory	<b>HBL8200STI</b>	<b>HBL8300STI</b>
	Red	<b>HBL8200STR</b>	<b>HBL8300STR</b>
	White	<b>HBL8200STW</b>	<b>HBL8300STW</b>
Hospital grade decorator receptacle with EdgeConnect technology, 2P 3W	Gray	<b>HBL2172STGY</b>	<b>HBL2182STGY</b>
	Ivory	<b>HBL2172STI</b>	<b>HBL2182STI</b>
	Red	<b>HBL2172STR</b>	<b>HBL2182STR</b>
	White	<b>HBL2172STW</b>	<b>HBL2182STW</b>
Hospital grade decorator receptacle with EdgeConnect technology, tamper resistant, 2P 3W	Gray	<b>HBL2172STGYTR</b>	<b>HBL2182STGYTR</b>
	Ivory	<b>HBL2172STITR</b>	<b>HBL2182STITR</b>
	Red	<b>HBL2172STRTR</b>	<b>HBL2182STRTR</b>
	White	<b>HBL2172STWTR</b>	<b>HBL2182STWTR</b>
Hubbell-Pro hospital grade duplex receptacle with EdgeConnect technology, 2P 3W	Gray	<b>8200STGY</b>	<b>8300STGY</b>
	Ivory	<b>8200STI</b>	<b>8300STI</b>
	Red	<b>8200STR</b>	<b>8300STR</b>
	White	<b>8200STW</b>	<b>8300STW</b>
Hubbell-Pro hospital grade duplex receptacle with EdgeConnect technology, tamper resistant, 2P 3W	Gray	<b>8200STGYTR</b>	<b>8300STGYTR</b>
	Ivory	<b>8200STITR</b>	<b>8300STITR</b>
	Red	<b>8200STRTR</b>	<b>8300STRTR</b>
	White	<b>8200STWTR</b>	<b>8300STWTR</b>

Note: Additional colors available

# SNAPConnect®

## Duplex Receptacles

SNAPConnect devices provide an ideal solution for larger projects with the potential for future change outs. From new construction and renovation to demanding locations, the modular SNAPConnect design eliminates exposed live parts and replaces pigtails. Consistent, safe, and reliable connections are ensured during rough-in installation. Once walls are up, the protective cover is removed, and the connector simply snaps into the device. Going forward, device change outs by maintenance personnel are simple and easy.



- Hospital grade
- Modular wiring provides the long-term benefit of safe, easy, fast device replacement
- Ability to energize and test circuits at rough-in and resolve issues during less critical project stages
- Widest modular device line on the market

### EdgeConnect Duplex Receptacles

Description	Color	Type	15A 125V	20A 125V
SNAPConnect extra heavy duty hospital grade receptacles with power indicating LED	White	Duplex	<b>SNAP8200WL</b>	<b>SNAP8300WL</b>
		Decorator	<b>SNAP2172WL</b>	<b>SNAP2182WL</b>
SNAPConnect extra heavy duty hospital grade receptacles with power indicating LED, tamper resistant	White	Duplex	<b>SNAP8200WLTRA</b>	<b>SNAP8300WLTRA</b>
		Decorator	<b>SNAP2172WLTRA</b>	<b>SNAP2182WLTRA</b>
SNAPConnect extra heavy duty hospital grade receptacles	White	Duplex	<b>SNAP8200WNA</b>	<b>SNAP8300WNA</b>
		Decorator	<b>SNAP2172WNA</b>	<b>SNAP2172WTRA</b>
SNAPConnect extra heavy duty hospital grade receptacles, tamper resistant	White	Duplex	<b>SNAP8200WTRA</b>	<b>SNAP8300WTRA</b>
		Decorator	<b>SNAP2182WNA</b>	<b>SNAP2182WTRA</b>

Note: Additional colors available

Description	Color	15A 125V	20A 125V
Right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; polycarbonate housing material, for use with receptacles	Clear	<b>SNAP1RNA</b>	<b>SNAP2RNA</b>
	Red (Emergency circuit)	<b>SNAP1REM</b>	<b>SNAP2REM</b>
	Blue (Surge circuit)	<b>SNAP1RS</b>	<b>SNAP2RS</b>
	Orange (Isolated ground circuit)	<b>SNAP1RIG</b>	<b>SNAP2RIG</b>

# GFCI Receptacles

Combine GFCI protection and tamper-resistant safety for an ideal solution. Our tamper resistant devices also provide UV and corrosion resistance for harsh, damp applications. These GFCIs protect people in bathrooms, scrub rooms, kitchenettes, and other potentially wet locations throughout healthcare facilities. They should not be used in critical care areas, ICUs, or operating rooms because of the possibility of power interruption.

- Hospital grade
- Fed Spec UL Listed Hospital Grade
- Single LED provides visual indication of status
- Patented Autoguard® self-test technology



## EdgeConnect Duplex Receptacles


Description	Color	15A 125V	20A 125V
SNAPConnect® hospital grade ground fault receptacle, tamper and weather resistant	Ivory	<b>SNAPGFTW82I</b>	<b>SNAPGFTW83I</b>
	Red	<b>SNAPGFTW82R</b>	<b>SNAPGFTW83R</b>
	White	<b>SNAPGFTW82W</b>	<b>SNAPGFTW83W</b>
SNAPConnect hospital grade ground fault receptacle	Ivory	<b>SNAPGF82I</b>	<b>SNAPGF83I</b>
	Red	<b>SNAPGF82R</b>	<b>SNAPGF83R</b>
	White	<b>SNAPGF82W</b>	<b>SNAPGF83W</b>
Hospital grade ground fault receptacle, tamper and weather resistant	Ivory	<b>GFRTW82I</b>	<b>GFRTW83I</b>
	Red	<b>GFRTW82R</b>	<b>GFRTW83R</b>
	White	<b>GFRTW82W</b>	<b>GFRTW83W</b>
Hospital grade ground fault receptacle	Ivory	<b>GFR82I</b>	<b>GFR83I</b>
	Red	<b>GFR82R</b>	<b>GFR83R</b>
	White	<b>GFR82W</b>	<b>GFR83W</b>

Note: Additional colors available

# inLIGHT™ Illuminated Receptacles


Highly visible LED faces let users know power is present for safety. The design ensures that the light can be seen even when appliances are plugged in. An industry first, inLIGHT receptacles combines the installation benefits of the modular SNAPConnect® system with the convenience, flexibility, and best-in-class performance of Hubbell Hospital Grade receptacles!

- Hospital grade
- Fully illuminated duplex faces
- Hospital Grade tamper-resistant devices
- SNAPConnect termination for fast, efficient installation



## inLIGHT Illuminated Receptacles

Description	Color	15A 125V	20A 125V
SNAPConnect® duplex receptacle, hospital grade, tamper-resistant, face LED indicator	Gray	SNAP8200GYLTR	SNAP8300GYLTR
	Ivory	SNAP8200ILTR	SNAP8300ILTR
	Red	SNAP8200RLTR	SNAP8200RLTR
	White	SNAP8200WLTR	SNAP8300WLTR



Audible snap indicates solid connection

# Healthcare Outlet Assemblies

Hubbell's healthcare outlet assemblies (HCOAs) are the ONLY UL Listed power strips approved by CMS for use in patient and critical care areas of a healthcare facility. They include line to neutral surge protection. Non-surge protected relocatable power tap (RPT) models are also available.

- UL2930 Listed
- Tamper-resistant flip covers
- Includes equipment grounding terminal



## UL 2930 Healthcare Outlet Assembly (HCOA)

Description	Cord Length	# Outlets	15A 125V	20A 125V
L-N surge protection, white	6	6	<b>HBL6MG6</b>	<b>HBL6MG620</b>
		4	<b>HBL4MG6</b>	<b>HBL4MG620</b>
	15	6	<b>HBL6MG15</b>	<b>HBL6MG1520</b>
		4	<b>HBL4MG15</b>	<b>HBL4MG1520</b>
Relocatable Power Tap (RPT), white	6	6	<b>HBL6MGRPT6</b>	<b>HBL6MGRPT620</b>
		4	<b>HBL4MGRPT6</b>	<b>HBL4MGRPT620</b>
	15	6	<b>HBL6MGRPT15</b>	<b>HBL6MGRPT1520</b>
		4	<b>HBL4MGRPT15</b>	<b>HBL4MGRPT1520</b>
HCOA Mounting Bracket, Allows strips to be easily mounted to IV poles or other medical devices, black				<b>HBLHCOAMB</b>



# Power Strips

SpikeShield® surge protective power strips and non-surge protected RPTs are cULus Listed to UL1449. They feature Hospital Grade tamper-resistant receptacles and durable heavy-duty metal housings. Choose a Hospital Grade plug or heavy-duty plug.

- UL2930 Listed
- 15A and 20A 125V versions
- 6 ft and 15 ft cord lengths




## Power Strips

Description		# Outlets	Cord Length	15A 125V	20A 125V
SpikeShield® Surge Protective Devices (SPD), UL Type 3 SPD, heavy duty metal housing	Hospital grade tamper resistant receptacles and hospital grade plug, white	6	6	<b>HBL6HG6</b>	<b>HBL6HG620</b>
		4; 2 USB	15	<b>HBL6HG15</b>	<b>HBL6HG1520</b>
	Tamper resistant receptacles and heavy duty plug, white	6	6	<b>HBL6SS6</b>	<b>HBL6SS620</b>
			15	<b>HBL6SS15</b>	<b>HBL6SS1520</b>
Relocatable Power Tap (RPT), white	Hospital grade tamper resistant receptacles, white	6	6	<b>HBL6RPT6</b>	<b>HBL6RPT620</b>
			15	<b>HBL6RPT15</b>	<b>HBL6RPT1520</b>
	Specification grade tamper resistant receptacles, black	6	6	<b>HBL6RPT6BK</b>	<b>HBL6RPT620BK</b>
			15	<b>HBL6RPT15BK</b>	<b>HBL6RPT1520BK</b>

# ScrubSwitch™ Touchless Switches

Sealed ScrubSwitch devices are the first switches designed to withstand the rigors of medical cleaning solutions and elevated sanitizing schedules for high touch surfaces. Proximity sensing technology allows a simple tap on or off, like a phone. However, skin contact isn't required, so it works with a latex gloved hand, or an elbow in a shirt sleeve. Helps reduce the transmission of viruses and bacteria.

- Designed to be disinfected
- 100% sealed against liquids, 3R rated
- Installs in a standard electrical box
- 8A, 120/277Vac, Single pole and 3-way capable
- Tested for aggressive cleaning with: Bleach, Hydrogen peroxide, Alcohol/Quat, Phenols



## ScrubSwitch Touchless Switches

Description	Type	15A 125V
Proximity tap switch, single gang	Stainless steel plate	<b>WSS1277SS</b>
	ABS antimicrobial plastic plate, white	<b>WSS1277PW</b>
	Base module only, plate sold separately	<b>WSS1277</b>
Proximity tap switch, 2 gang	ABS antimicrobial plastic plate, white	<b>WSS2277PW</b>
Cover plate, single gang	Stainless steel plate	<b>WSS1SS</b>
	ABS antimicrobial plastic plate, white	<b>WSS1PW</b>
Cover plate, 2 gang	ABS antimicrobial plastic plate, white	<b>WSS2PW</b>

*Note: All units can be used as SP, 3- & 4-way; additional ScrubSwitch devices need to be used. Do not use a mechanical switch.*

# inREACH™ Cord Reels

Cord reels with Hospital Grade plugs and receptacles provide safe, convenient, and reliable power in demanding medical applications. All-white construction complies with sanitary practices by making contamination more visible and easier to clean. Our plenum-rated enclosure is the first of its kind, allowing you to securely mount cord reels in drop ceilings while isolating it from the plenum space.

- Cast aluminum reel housing withstands corrosive environments
- Hospital Grade, tamper-resistant receptacles with illuminated LED to clearly indicate available power
- UL 2416 Listed plenum rated steel enclosure complies with NEC300.22



## inREACH Industrial Cord Reels

Description	Amps	Voltage	Cable Length ft (m)	Cable Type	Weight lbs. (kg)	Catalog Number
White reel, white portable outlet box, GFCI module, and (2) 20A Hospital Grade receptacles	20A	125V AC	45 (13.7)	12/3 SJO	34.9 (15.8)	<b>HBLIWC45123GF220HG</b>
White reel, white portable outlet box, and (2) 20A Hospital Grade receptacles	20A	125V AC	45 (13.7)	12/3 SJO	34.4 (15.6)	<b>HBLIWC45123R220HG</b>
White reel and Hospital Grade connector HBL8319C	20A	125V AC	45 (13.7)	12/3 SJO	33.6 (15.2)	<b>HBLIWC45123C20HG</b>

# HUBBELL

## Wiring Device-Kellems

Count on Hubbell Wiring Device-Kellems for the most reliable and innovative wiring device product line in North America.

### GET IN TOUCH:



[email@hubbell.com](mailto:email@hubbell.com)



[\(800\) 555-1234](tel:(800)555-1234)



[www.hubbell.com/url](http://www.hubbell.com/url)



Hubbell Wiring Device-Kellems  
40 Waterview Drive  
Shelton, CT 06484



A Hubbell brand

©2024 Brand. All rights reserved.  
Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.

EP-WDK-BR-EN-00895 | REV 11/2024