

OBCT

OIL-TYPE BUSHING CURRENT TRANSFORMER

APPLICATION:

The internally mounted Oil-type BCT is designed to be mounted onto a high voltage bushing shank along the ground collar, inside the tank of a power transformer, power circuit breaker or voltage regulator, that uses oil as the insulating medium. When properly installed, the Oil-type BCT can be used on higher system voltage levels while maintaining its own mere 600 Volt class rating. Its simple construction provides a low leakage product with extremely high short circuit capabilities.

OFFERINGS:

- Inner diameter: 3.5" [89mm] to 36" [915mm]
- Outer diameter: 5" [127mm] to 40" [1016mm]
- Primary currents: 25 – 8,000 Amps
- Secondary current: 1 & 5 Amps typ, others available
- Frequency: 50 and 60 Hz
- Rating Factors: Up to 2.0 @ 95°C Ambient
- Relaying class: Up to C800 / 5P20-200VA standard, up to C1200 and higher as non-standard.
- Metering class: 0.15S thru 2.4 / 0.2S thru 5.0
- Burdens: B0.1 thru B1.8 / 2.5 – 45 VA
- Available in a variety of winding arrangement, Single Ratio (SR), Dual Ratio (DR) or Multi Ratio (MR)
- NOTE: Sizes and accuracy class depend on current ratio

OPTIONS:

- Designs can be engineered to match existing CT characteristics.
- Primary currents greater than 8,000 Amps.
- Higher temperature class rating of 155°C.
- Gapped cores for remanence control and transient response.
- Air core linear couplers.



Scan the QR Code or visit MeramecUSA.com for more information.



hubbelpowersystems.com



For product inquiries, please contact your Hubbell sales representative or customer service at InstrumentTransformers@Hubbell.com or (573) 885-2521.

©2021 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_02_51E