




UL 943 Compliant Self-testing Portable GFCI Devices

Protect workers on the jobsite or assembly floor with Hubbell's portable GFCI devices. They provide effective ground fault protection both indoors and out, interrupting power to equipment loads when leakage to ground reaches 4-6 milliamperes. These rugged modules, line cords, and plugs are self-testing per the latest UL943 standard.

Applications

- Power generators
- Welders
- Submersible pumps
- Portable power tools
- Food processing
- Production assembly
- Spa and hot tubs
- Vending machines
- Cord drops
- Temporary lighting
- De-icing equipment
- Agricultural equipment



www.hubbell.com/wiringdevice-kellems

Minimize electrical shock hazards

Circuit Guard® self-test portable GFCI modules, line cords, and plugs protect people in indoor or outdoor applications. Manual Set feature adds safety for situations where operator injury might occur if equipment restarts after an interruption, like drills, saws, lathes, and grinders. Automatic Set models auto-restore power to equipment after a temporary power failure. Perfect for applications requiring continuous operation, such as pumps or refrigeration.

NEC 590.6(A) All 125-volt, single-phase, 15-, 20-, and 30-ampere receptacle outlets that are not a part of the permanent wiring of the building or structure and that are in use by personnel shall have ground-fault circuit-interrupter protection for personnel. Cord sets or devices incorporating listed ground-fault circuit-interrupter protection for personnel identified for portable use shall be permitted.



GFCI Module

- The only GFCI device module on the market that mounts in a single gang box
- Available with either automatic or manual set feature to fit the application
- Watertight housing maximizes safety in harsh environments
- Bright indicator light provides fault confirmation from a distance

Portable GFCI Line Cords and Plugs

- Available with either automatic or manual set feature to fit the application
- Watertight housing maximizes safety in harsh environments
- Bright indicator light provides fault confirmation from a distance
- Heavy-duty construction provides long, reliable service

Part Numbers & Ordering Information

Circuit Guard® Portable GFCI Line Cords



Description	Length	GFCI Cord Line	w/Stripped Leads
15A 120V AC	18 in.	GFPST4C15x	—
	6 ft.	GFPST6C15x	—
	15 ft.	—	GFPSTOEMx
20A 120V AC	25 ft.	GFPST25C15x	—
	3 ft.	GFPST3C20M	—

Xx A (Automatic) or M (Manual) Set

GFCI Module UL Type 3R Rated



Description	Rating	Cat. No
Manual set	20A 120V AC	GFMST20
Auto set	60 Hz	GFMST20A

Circuit Guard® Wired On Straight Blade Portable GFCI Plugs



15A 125V AC Industrial Grade

Description	Cat. No
Manual Set, plug, black	GFPST5266C
Manual Set, plug, yellow	GFPST5266CY
Manual Set, plug w/1 ft. Line Cord	GFPST1C

Multiple Outlet Portable GFCI



Description	Rating	Cat. No
4 Outlet; 2 Duplex	15A 120V AC	GFP15M
Manual set	20A 120V AC	GFP20M

HUBBELL®
Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems



Hubbell Wiring Device-Kellems Hubbell • Incorporated (Delaware) • 40 Waterview Dr. • Shelton, CT 06484 • Phone (800) 288-6000 • FAX (800) 255-1031
Printed in U.S.A. Specifications subject to change without notice.

* is a registered trademark of Hubbell Incorporated.

HHI_WDK_SF_EN_00066