

# Deadends

## For Overhead Connections

No matter the application, Hubbell has a deadend solution to meet your needs. Choose from any of our Anderson or Fargo deadends to create a reliable overhead distribution connection.

**Note:** Bolted and automatic deadends for copper and steel applications are also available. Scan the QR code to view our product catalog for more information.



Product	Type	Material	Installation Speed	Hardware Type	Range Taking	Meets ANSI C119.4 Partial Tension (40% RBS)	Additional Features
 Fargo GDW	Automatic, side-opening wedge	Aluminum alloy body & jaws (nickel-plated jaws available)		No hardware			Jaws lock open for easy positioning; can be repositioned during install
 Fargo GD	Automatic	Aluminum alloy shell & jaws		No hardware			Several bail options available, color-coded funnel guides for easy ID
 Anderson ASOD	Bolted, straight-line, spring-loaded, side-opening deadend	Aluminum alloy body & keeper, galvanized steel hardware		Single U-bolt with captive nuts			Spring-loaded keeper & single side-mounted U-bolt for fast side install
 Anderson ADEZ	Bolted, straight-line, spring-loaded, side-opening deadend	Aluminum alloy body & keeper, galvanized steel hardware		Double U-bolt with captive nuts			Spring-loaded keeper disengages from U-bolt for side-open install
 Anderson ADS	Bolted, straight-line	Aluminum alloy body & keeper, galvanized steel hardware		Double U-bolt			Lifting eye for manual keeper opening



A proud member of the Hubbell family.