

HOT BOX[®] MODULAR ENCLOSURES

HOTBOX

Legacy Quality & Dependability in a new package.

FEATURES AND BENEFITS


- Hot Box Modular features prepackaged components and accessories for easy on the job assembly
- Prepackaged units create a smaller storage footprint providing more storage space and the ability to store inside a warehouse
- Interlocking panel design make for easy assembly in the field
- Side located drain ports allow for field installation of custom penetrations
- Wall mounted heaters provide better long term performance when compared to slab mounts
- Lightweight, insulated panels and roof make for quick and easy assembly in the field
- Smaller units sized to be standard truck-bed friendly
- Stucco embossed finish allows for longer lasting visual appeal hiding any imperfections as a result of the elements
- Multiple size options for use with all manufacturers standard backflow and valve systems
- Standard aluminum, green and federal brown (mill finish) colors available
- Unheated or heated options available featuring preferred wall-mounted heater location
- All components meet the necessary requirements set forth by ASSE 1060
- Meets OSHA weight requirements
- NAFTA friendly



hubbelpowersystems.com

**For product inquiries, please contact
waterhlc@hubbell.com or call 1-800-346-3061**

©2019 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement,
we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_07_123E



Hot Box® Modular Product Information

Catalog Part Number	Model Number	Pipe Size	Inside Width (in)	Inside Length (in)	Inside Height (in)	Heaters	Doors	Weight #
HK026070045	HBM3E	2.5 - 3"	26	70	45	(1) 1500W	2	110
HK036088055	HBM4E	4"	36	88	55	(1) 1900W	2	163
HK036100055	HBM6N	6"	36	100	55	(2) 1500W	2	177
HK036100064	HBM6E	6"	36	100	64	(2) 1500W	2	210
HK038118080	HBM8E	8"	38	118	80	(2) 1500W	4	280
HK038142080	HBM10E	10"	38	142	80	(2) 1500W	4	319
LK026070045	LBM3E	2.5 - 3"	26	70	45	Unheated	2	98
LK036088055	LBM4E	4"	36	88	55	Unheated	2	151
LK036100055	HBM6N	6"	36	100	55	Unheated	2	165
LK036100064	LBM6E	6"	36	100	64	Unheated	2	186
LK038118080	LBM8E	8"	38	118	80	Unheated	4	256
LK038142080	LBM10E	10"	38	142	80	Unheated	4	295

