



Stud-Mount Transformer Connectors

Type RLB

Insulated Slip-Fit with SharkBite™ Mount allows left or right-hand mounting

- Patented two-in-one SharkBite™ mounting hole feature allows the connector to fit on a 5/8” or 1” transformer stud. Both sizes fit in the same hole.
- SharkBite™ mounting hole feature provides over 10 times the surface area contact on the transformer stud versus traditional connectors.
- The SharkBite™ feature also securely locks the connector onto the stud to eliminate wobble.
- Fully tested to ANSI C119.4 for Class ‘A’ connectors.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Supplied with aluminum radial-tipped set-screws.
- Includes inhibitor in all ports and stud-mounting hole.



Stud Mount Transformer Connectors

Catalog Number	No. of Cond.	Cond. Range AWG	Trans. Stud	Dimensions - Inches		
				H	W	L
RLB500-4I	4	500-10	5/8-11 or 1-14	2.73	3.00	4.59
RLB500-5I	5	500-10	5/8-11 or 1-14	2.73	3.00	6.99
RLB500-6I	6	500-10	5/8-11 or 1-14	2.73	3.00	9.39
RLB500-7I	7	500-10	5/8-11 or 1-14	2.73	3.00	10.59
RLB500-8I	8	500-10	5/8-11 or 1-14	2.73	3.00	11.78
RLB750-4I	4	750-2	5/8-11 or 1-14	2.95	4.91	9.28
RLB750-6I	6	750-2	5/8-11 or 1-14	2.95	4.91	12.00
RLB750-8I	8	750-2	5/8-11 or 1-14	2.95	4.91	14.73

Street light tap available - add suffix "SL" to catalog number
 Note: For omissions of CO-OX oxide inhibitor delete suffix - "I".



A proud member of the Hubbell family.

©2024 Connector Manufacturing Company. All rights reserved.
 Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.
 3501 Symmes Road, Hamilton, OH 45011
www.cmclugs.com | cmcservice@hubbell.com | 513-860-4455