


MOTOR OPERATOR

For group operated switches

HUBBELL POWER SYSTEMS INTRODUCES THE SF210 and SF220 MOTOR OPERATORS, EXPANDING OUR OFFERING.

FEATURES AND BENEFITS

- CUSTOMIZABLE TO FIT CUSTOMER SPECIFICATIONS
- HIGH TORQUE OUTPUT FOR EASY OPERATION OF LARGE SWITCHES
- WEATHERPROOF ENCLOSURE
- INTERNAL HEATER CONTROLS CONDENSATION
- EASY ACCESS TO INTERNAL COMPONENTS FOR INSTALLATION AND ADJUSTMENT



Hubbell has a policy of continuous product improvement. Please contact your HPS Customer Service Representative to confirm current design specifications.

	SF-210	SF-220
Torque	10,000 inch-pounds	20,000 inch-pounds
Rotation	0 to 180°, 3 to 4 seconds	0 to 180°, 6 to 8 seconds
Operating Voltage	24VDC, 48VDC, 120VAC, 125VDC	
Voltage Range	24VDC: 18-28V, 48VDC: 36-56V, 120VAC: 104-127V, 125VDC: 90-140V	
Rated Load Current	24VDC: 32A, 48VDC: 16A, 20VAC: 8A, 125VDC: 8A	
Stall Current	24VDC: 140A, 48VDC: 85A, 120VAC: 35A, 125VDC: 35A	
Auxiliary Switches	Standard: 8 Maximum: 12	
Temperature Range	-40°F to 160°F	
Pipe Coupling	1-1/2 or 2 IPS	
Standard	Optional	
Local/Remote Switch	Special Terminal Block	
Heavy Duty, Permanent Magnet Motors	Auxiliary Relays	
Worm Gear Driven/Pad-lockable	Open/Close Counter	
Cabinet Heater: 100 Watts	Select Batteries and Charger	
Clockwise Opening Rotation	Low DC Voltage Alarm	
	Loss of AC Alarm	



hubbellpowersystems.com

For product inquiries, please contact your local sales representative or customer service representative.

©2019 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice. Printed in the U.S.A. | SF_10_294E