

Selection Guide

Select from the catalog breakdown table options below. Enter the desired selection in the corresponding position

ULT **B** **S** **XX**

1 2 3 4 5 6 7 8 9

(1) Capacitor Switch Model

Model	Code
UltraVacLT®	ULT

(2) kV Rating & kV BIL Rating

Voltage Class	kV BIL Rating	Code
15kV	95	15-095
	110/125 (open gap/L-G)	15-125
27kV	125	27-125
	150	27-150

(3) Phase & Current Rating

Phase	Current Rating	Code
1 phase	200A	B

(4) Control Operating Voltage

Voltage	Code
120VAC (standard)	1
240VAC	2
125VDC*	3

*125VDC is not offered with the code W5 auxiliary type

(5) Auxiliary Type & Control Connection Type - Receptacle Pin (Connector)

Auxiliary Type	Receptacle Pin	Code
None	5	X5
Form C (SPDT - common is control voltage neutral) [standard] Not offered with the 125VDC option.	5	W5
Form A (NO dry)	5	A5
Form B (NC dry)	5	B5
Form C (SPDT dry)	6	C6
Form A & Form B (dry)	7	D7
Form A & Form B (dry)	8	D8

(6) Mounting Bracket & Style

Description	Code
Stainless steel band and pole mounting bracket	S

(7) Nameplate Language


Language	Code
English (standard)	E
Portuguese	P
Spanish	S

(8) Terminations & Ground

Termination Type	Ground Type	Code
Eyebolt Bushing Termination (8AWG-2/0)	Stud and washer nut ground (standard)	1
	Eyebolt ground	2
	Parallel groove connector ground	3

(9) Options

Description	Code
None (standard)	XX



Switch Standards

- Two wildlife protectors
- Manual open and close handle
- Please contact factory for any special options not listed above

