

## Hubbell-PRO 15A & 20A 250V Duplex Receptacles


*Superior Performance*

*Compact Design*

*Installation Ease*

Hubbell-PRO NEMA 6-15R and 6-20R receptacles are engineered to meet UL498 and Fed. Spec. W-C-596. The unique construction allows for successful installation in panel mount applications, such as indoor horticultural lighting controls, and AV and power distribution rack equipment.

The featured compact design is ideal for applications where space is limited and reliability is a necessity.



### FEATURES

- Back and side wired
- Fed-Spec UL listed
- Smooth nylon face
- Brass triple-wipe contacts

### APPLICATIONS

- Indoor horticultural lighting control manufacturers
- AV rack manufacturers
- Power distribution rack manufacturers
- OEM equipment



### Configurable Options

- Prewired leads
- WAGO quick connect terminations
- Remove ears/bridge
- Split circuit
- Remove screws



# Hubbell-PRO NEMA 6-15R & 6-20R Duplex Receptacles

**HUBBELL®**  
Wiring Device-Kellems



**15A 250V**  
NEMA 6-15R  
UL CSA  
1.5 HP



**20A 250V**  
NEMA 6-20R  
UL CSA  
2 HP

## Hubbell-PRO Heavy Duty Specification Grade Receptacles

Description	Color	15A 250V	20A 250V
Smooth nylon face, duplex, back and side wired.	Almond	<b>5662AL</b>	<b>5462AL</b>
	Black	<b>5662BK</b>	<b>5462BK</b>
	Blue	<b>5662BL</b>	<b>5462BL</b>
	Brown	<b>5662B</b>	<b>5462B</b>
	Gray	<b>5662GY</b>	<b>5462GY</b>
	Green	<b>5662GN</b>	<b>5462GN</b>
	Ivory	<b>5662IV</b>	<b>5462IV</b>
	Light Almond	<b>5662LA</b>	<b>5462LA</b>
	Red	<b>5662R</b>	<b>5462R</b>
	White	<b>5662WHI</b>	<b>5462WHI</b>



## Listings

UL Listed to UL498 File No. E2186  
Certified to CSA C22.2 No.42  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

## Performance

<i>Electrical</i>	Current Interrupting	Certified for current interrupting at full rated current
	Dielectric Voltage	Withstands 2,000V minimum
<i>Mechanical</i>	Product Identification	Ratings are a permanent part of the device
	Terminal Accommodation	14-10 AWG copper stranded or solid conductor only
	Terminal Identification	Terminals identified in accordance with UL 498 and CSA
<i>Environmental</i>	Flammability	UL 94 V-2
	Operating Temperatures	Maximum continuous 75°C; Minimum -40°C (w/o impact)

## Online Resources

The Hubbell Wiring Device-Kellems website offers fast and convenient information through our online catalog, technical support, videos and more. Visit [www.hubbell.com/wiringdevice-kellems/en](http://www.hubbell.com/wiringdevice-kellems/en)

## Literature Support

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online.



Hubbell Wiring Device-Kellems  
Full Line Catalog



Tamper-Resistant Receptacles



Configurable Receptacles



Hubbell-PRO Devices



Hubbell-PRO Commercial  
Contractor Solutions

**HUBBELL®**  
Wiring Device-Kellems

[www.hubbell.com](http://www.hubbell.com)



Hubbell Wiring Systems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 • Phone (800) 288-6000 • FAX (800) 255-1031  
Printed in U.S.A. Specifications subject to change without notice.

WLFSB018 6/18