

Hubbell Power Strips



Commercial/Retail | UL1363 RPTs

HUBBELL



Healthcare Facility Outlet Assemblies (HCOA) UL2930 Listed

UL2930 Listed




Hubbell HCOA:

- UL2930 listed for patient care areas
- 15A and 20A 125V versions
- 6 ft. or 15 ft. cord length
- 12/3 AWG cord
- Surge protected models in all configurations
- Non-surge protected RPT models in all configurations
- 4 outlet models feature straight plugs



45° Angle Plug (6 outlet 15A models only)



UL2930 Healthcare Outlet Assembly (HCOA)

Description	Cord Length	Color	# of Outlets	15 Amp	20 Amp
	6 Ft.	White	6	HBL6MG6	HBL6MG620
UL 2930 HCOA	011.	VVIIILE	4	HBL4MG6	HBL4MG620
with L-N Surge Protection	15 Ft.	White	6	HBL6MG15	HBL6MG1520
	15 Ft.	vvriite	4	HBL4MG15	HBL4MG1520
	6 Ft.	White	6	HBL6MGRPT6	HBL6MGRPT620
UL 2930 HCOA	σ Fl.	vvriite	4	HBL4MGRPT6	HBL4MGRPT620
Relocatable Power Tap (RPT)	15 Ft.	White	6	HBL6MGRPT15	HBL6MGRPT1520
	ıə Ft.	vvriite	4	HBL4MGRPT15	HBL4MGRPT1520

Hubbell HCOA Mounting Bracket

Description	Color	Catalog Number
Allows strips to be easily mounted to IV poles or other medical devices	Black	HBLHCOAMB

UL2930 HCOA Specifications

	HBL4MG6/15 HBL6MG6/15	HBL4MG620/1520 HBL6MG620/1520	HBL4MGRPT6/15 HBL6MGRPT6/15	HBL4MGRPT620/1520 HBL6MGRPT620/1520	Physical Specifications		5
	TIDEOWIGO, TO	TIDEOWIGOZO/ TOZO	TIBLOMATII 10/10	TIDEOWIGHT TOZO/ TOZO	Cord		12/3 SJT
Electrical Specifications					Housing		18G Galvanized Steel
Current	15A	20A	15A	20A	Color		White Powder Coat
Voltage	125V	125V	125V	125V	Receptacles		HG Tamper Resistant
Frequency	60Hz	60Hz	60Hz	60Hz	Plug:	15A	HG 45° Angle
Surge Component	MOV	MOV	n/a	n/a		20A	HG 90° Angle
Performance					LED (HBL4MG and Green Power Indicated HBL6MG Series only)		Green Power Indicator
UL VPR L-N L-G, N-G		00V n/a			Dimensions	oy,	
EMI Noise Filtration:		(10kHz to 100MHZ)			HBL4MG Series	s:	HBL4MGRPT Series:
In (Nominal Discharge Current) MCOV Peak Current Rating L-N Leakage Current:	1 3	BKA 50V OKA 1mA	n/a	n/a	Length 11.90" (3 Width 2.22" (56 Depth 1.92" (48	3.4mm) [^]	Length 9.15" (232.4mm) Width 2.22" (56.4mm) Depth 1.92" (48.7mm)
Total Joules (L-N)	Ę	550			HBL6MG Series	s:	HBL6MGRPT Series:
Environmental Specifications		•			Length 15.20" (3 Width 2.22" (50	,	Length 11.90" (302.3mm) Width 2.22" (56.4mm)
Operating Temperature			(-40°C to 70°C)		VVIGIT 2.22 (0)	J. T 111111)	1 VIGG 2.22 (00. 111111)

Certifications

UL 2930; UL File # E488399; RoHs Compliant; NFPA 99; ANSI/IEEE Category A (HBL4MG & HBL6MG Series Only)



Heavy Duty SpikeShield® Surge Protection for Industrial and Healthcare Applications





cULus Listed 1449 4th EditionHeavy Duty Metal Housing

• Available with a 2-Port USB Charging Outlet



Industrial Grade:

- Tamper-Resistant Receptacles with a Heavy Duty Plug
- cULus Listed to UL1449 4th Edition
- Heavy Duty Metal Housing



SpikeShield $^{\mbox{\tiny B}}$ Surge Protective Devices (SPD) with

Hospital Grade ● Tamper-Resistant Receptacles and Hospital Grade ● Plug

Description	# of Outlets	Cord Length	Color	15 Amp	20 Amp
UL Type 3 SPD,	6	6 Ft.	White	HBL6HG6	HBL6HG620
Heavy Duty Metal Housing	6	15 Ft.	White	HBL6HG15	HBL6HG1520
UL Type 3 SPD, Heavy Duty Metal Housing with 2-port USB	4	6 Ft.	White	HBL6HGUSB6	_



SpikeShield® Surge Protective Devices (SPD) with

Industrial Grade Tamper-Resistant Receptacles and Heavy Duty Plug

Description	# of Outlets	Cord Length	Color	15 Amp	20 Amp
UL Type 3 SPD, Heavy Duty	6	6 Ft.	White	HBL6SS6	HBL6SS620
Metal Housing	6	15 Ft.	White	HBL6SS15	HBL6SS1520

-40°F to 160°F (-40°C to 70°C)



SpikeShield® SPD Specifications

Environmental Specifications
Operating Temperature

	15 Amp HBL6SS/HBL6HG Se	15 Amp HBL6SS/HBL6HG Series				
Electrical Specifications						
Current	15A		20A			
Voltage	125V		125V			
Frequency	60Hz	60Hz 60Hz				
Surge Component	MOV	MOV MOV				
Over Current Protection	15A CB	15A CB 20A CB				
2-Port USB (HBL6HGUSB6)	3A 5V DC Type A	3A 5V DC Type A n/a				
UL VPR	L-N	L-N L-G N-G				
	500V	600V	600V			
MCOV		150V				
Peak Current Rating L-N	30kA					
Leakage Current:	<.5mA					
EMI / RFI Noise Rejection	-11 dB to	-11 dB to -68 dB (10kHz to 100MHZ)				
Total Joules (all modes)		1100j				

Certifications

cULus Listed to UL1449 4th Edition UL File # E143272 RoHs Compliant ANSI / IEEE Category A cULus Listed to UL1310 (2-Port USB)

Physical Specifications

HBLH6USB6:	
Length	15.67" (398.0mm)
Width	2.22" (56.4mm)
Depth	1.78" (45.2mm)
HBL6HG Series:	
HBL6SS Series:	
Length	14.42" (366.3mm)
Width	2.22" (56.4mm)
Depth	1.70" (43.3mm)





Heavy Duty Relocatable Power Taps for Industrial, Commercial and Retail Applications

Listed to UL1363



- Heavy-duty 18 gauge galvanized steel housing with durable powder coat finish
- Available in 15A and 20A configurations
- 6' and 15' cord length options for all models
- 15A models feature a 45° angle plug
- 20A models feature a 90° angle plug
- All models come with built in circuit breaker for over current protection
- Church-key openings on the back of the RPT for temporary mounting ease
- White powder coat RPTs feature UL Listed Hospital Grade, Tamper-Resistant Receptacles
- Black powder coat RPTs feature Specification Grade, Tamper-Resistant Receptacles



Relocatable Power Tap with Hospital Grade Tamper-Resistant Receptacles

Description	# of Outlets	Cord Length	Color	15A 125V	20A 125V
RPT, Heavy Duty Metal Housing	6	6 Ft.	White	HBL6RPT6	HBL6RPT620
	6	15 Ft.	White	HBL6RPT15	HBL6RPT1520



Description	# of Outlets	Cord Length	Color	Catalog Number	20A 125V
RPT, Heavy Duty Metal Housing	6	6 Ft.	Black	HBL6RPT6BK	HBL6RPT620BK
nr i, neavy Duty Metal nousling	6	15 Ft.	Black	HBL6RPT15BK	HBL6RPT1520BK



Relocatable Power Tap Specifications

	15A	20A
Electrical Specifications		
Current	15A	20A
Voltage	125V	125V
Frequency	60Hz	60Hz
Over Current Protection	15A CB	20A CB

Physical Spec	ifications	
Length	11.12" (282.4)	
Width	2.22" (56.4)	
Heiaht	1.6" (40.5)	

Environmental Specifications Operating -40°F to 160°F (-40°C Temperature to 70°C) Certifications cULus Listed UL1363 RPT



