

ADSS SUSPENSION CLAMPS

HEAVY DUTY, VERSATILE, AND RELIABLE SOLUTION

The Hubbell ADSS suspension clamp is a heavy duty, versatile, and reliable solution for securely suspending ADSS (All Dielectric Self-Support) aerial fiber optic cable. The versatility of the clamp allows the installer to either fix the clamp to the pole using a through bolt or band. If a loose tangent is required, the clamp can be suspended using a standard J-hook. Accepting a range of sizes and multiple installation methods, the Hubbell ADSS suspension clamp is sure to meet your tangent needs.

MATERIAL


- Body: Galvanized Steel
- Insert: Neoprene Sleeve

BENEFITS

- Two sizes to cover the full range of ADSS cables from 0.394" to 0.787"
- Installation in just a few seconds with standard tools
- Versatility in installation methods

SPECIFICATIONS

- Tangent suspension for spans up to 600 ft.
- Less than 20° angle on cable routes between spans (For angles greater than 20°, double deadend or false deadend)



PART NUMBER	CABLE DIAMETER RANGE				ULTIMATE BODY STRENGTH (LBS.)
	MIN (IN.)	MAX (IN.)	MIN (MM.)	MAX (MM.)	
ASCF102	0.394	0.591	10.0	15.0	3000
ASCF114	0.591	0.787	15.0	20.0	3000

Hubbell has a policy of continuous product improvement. Please visit hubbellpowersystems.com to confirm current design specifications