

Hubbell Marine

Hubbell Marine is proud to offer a line of Marine Isolation Transformers for the Marine Industry. Suitable for 50 and 100 Amp Shore Power Systems, our new UL Listed Isolation Transformers assure proper wiring conditions on your boat, and greatly minimizes the possibility of stray current from entering the water.

Clean and Safe Power - Now Available from Hubbell.

Hubbell Marine will offer 15 kVA and 25 kVA models, 60-Cycle in White Powder Coated Steel and #316 Stainless Steel. International-rated (50/60 Cycle) systems also are available.

FEATURES

- UL Listed and CSA Certified
- Compact Size and Weight
- 12.5% Taps (10% initially on white 25 kVA model)
- Two Full Current-Carrying Shields
- Vibration-Resistant
- Exceeds ABYC's 4000 Volt HIPOT test requirement
- Made for the Marine Industry by The Shore Power Experts



UL Listed Isolation Transformers

Isolation Transformers

Description	Weight	Color	Catalog Number
15 kVA Isolation Transformer, 60 Hz	170	White Powder Coated Steel	HBL50AITW
15 kVA Isolation Transformer, 60 Hz	170	#316 Stainless Steel	HBL50AITSS
25 kVA Isolation Transformer, 60 Hz	250	White Powder Coated Steel	HBL100AITW
25 kVA Isolation Transformer, 60 Hz	250	#316 Stainless Steel	HBL100AITSS
15 kVA Isolation Transformer, 50/60 Hz	170	White Powder Coated Steel	HBL32AITW
15 kVA Isolation Transformer, 50/60 Hz	170	#316 Stainless Steel	HBL32AITSS
25 kVA Isolation Transformer, 50/60 Hz	250	White Powder Coated Steel	HBL63AITW
25 kVA Isolation Transformer, 50/60 Hz	250	#316 Stainless Steel	HBL63AITSS



FEATURES

- UL listed, CSA certified and UL-3R enclosures meets or exceeds all listing criteria including NEMA, ANSI and OSHA standards
- Shielded for cleaner power
- Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air. UL Type 3R enclosure for indoor or outdoor service. Encapsulation eliminates corrosion and insulation deterioration
- Quiet operation with sound levels well below NEMA standards
- Long life UL class 155°C insulation system. 115°C rise thru .750 kVA; 180°C insulation system, 115°C rise, 1 kVA and above

OFFERING

- 15 kVA and 25 kVA Models
- 60 Hz and 50/60 Hz Models
- White Powder Coated Steel and Type #316 Stainless Steel

Dimensions inch (mm)

Description	Pounds	Height	Width	Depth
15 kVA Models	170	16.94" (43.0)	14.12" (35.9)	11.59" (29.4)
25 kVA Models	250	18.44" (46.8)	16.13" (41.0)	13.34" (33.9)