


NYLON CABLE RACK INSULATOR PAD

NEW PRODUCT FOR UNDERGROUND CABLE RACKING

Non-porcelain option for cable support for t-slot channel type underground cable racking



Catalog Number
C2031120P

FEATURES AND BENEFITS

- Resist chipping and breakage
- C2031120P is a direct replacement for porcelain equivalent C2031120
- Meets requirements of ANSI C135.35



hubbellpowersystems.com

For product inquiries, please contact
your local sales representative or customer service representative.

©2020 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement,
we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_06_152E

INSULATOR PAD

Catalog Number	Length	Width	Cable Radius	Approx. Ship Wt. per Each
C2031120P	3"	2-3/4"	1-1/2"	0.34 lbs.

CABLE RACKING

Catalog Number	Number of Holes for Support Hooks	Overall Length	Mounting Hole Spacing	Approx. Ship Wt. per Each
C2031124	8	15"	13 1/2"	1.62 lbs.
C2031125	14	24"	22 1/2"	2.30 lbs.
C2031126	18	30"	28 1/2"	2.80 lbs.
C2030313	37	55 1/4"	N/A	5.70 lbs.
C2030314	47	70 1/4"	N/A	7.20 lbs.

ANSI Standard, C135.35

CABLE RACK SUPPORT HOOKS

Standard Catalog Number	Length from Face of Rack	ANSI Load Rating	Steel Size	Approx. Ship Wt. per Each
C2031131	4"	600 lbs.	1-1/2" x 1-1/8" x 3/16"	0.42 lbs.
C2031132	7 1/2"	400 lbs.	1-1/2" x 1-1/8" x 3/16"	0.96lbs.
C2031133	10'	300 lbs.	1-1/2" x 1-1/8" x 3/16"	1.08 lbs.
C2030317	10"	Non-ANSI Style	1-1/2" x 2-1/16" x 13/64"	1.76 lbs.
C2030315	14"	300 lbs.	1-1/2" x 1-35/64" x 3/16"	2.04 lbs.
C2030316	18"	200 lbs.	1-1/2" x 1-35/64" x 3/16"	2.68 lbs.

ANSI Standard, C135.35

