

Tamper-Resistant 15A & 20A 250V Single Receptacles

NEC® 2017 Code Requirement

Ideal for Use with Commercial Packaged Terminal Air Conditioner (PTAC) Units

Equipped with Hubbell's best in class tamper-resistant shutters, the 250-volt single receptacle is the perfect solution to meet the updated standards in the 2017 National Electrical Code.® Designed to the same quality standards you're accustomed to with Hubbell receptacles, the impact resistant nylon face and base, combined with engineered tamper-resistant dual shutter mechanisms, ensure a safe, lasting and reliable receptacle.



2017 National Electrical Code® Change

2017 Section 406.12 requires **all non-locking 15- and 20-ampere, 125- and 250-volt receptacles** in the areas specified in 406.12(1) through (7) **shall be listed tamper-resistant receptacles.**

- (1) Dwelling units in all areas specified in 210.52 and 550.13
- (2) Guest rooms and guest suites of hotels and motels
- (3) Child care facilities
- (4) Preschools and elementary education facilities
- (5) Business offices, corridors, waiting rooms and the like in clinics, medical and dental offices and outpatient facilities
- (6) Subset of assembly occupancies described in 518.2 to include places of waiting transportation, gymnasiums, skating rinks, and auditoriums
- (7) Dormitories.

*National Electrical Code® and NEC® are registered trademarks of the National Fire Protection Association, Quincy, MA.



FEATURES

- Best in class tamper-resistant mechanism for easy plug insertion
- Durable nylon construction for heavy use applications
- Modular wiring eliminates screw terminals and increases installation efficiency
- No exposed metal for a safer installation
- Clear polycarbonate connector cover to inspect contacts

APPLICATIONS

- Hotels and Motels
- Schools
- Child Care Facilities
- Medical and Dental Offices
- Dormitories



Tamper-Resistant 15A & 20A 250V Single Receptacles

HUBBELL®
Wiring Device-Kellems

SNAPConnect® Extra Heavy Duty Standard Single Receptacles

Description	Color	15A 250V	20A 250V
Specification grade, Tamper-Resistant, smooth nylon face, modular receptacle	Black	SNAP5661BKTR	SNAP5461BKTR
	Brown	SNAP5661TR	SNAP5461TR
	Gray	SNAP5661GYTR	SNAP5461GYTR
	Ivory	SNAP5661ITR	SNAP5461ITR
	Light Almond	SNAP5661LATR	SNAP5461LATR
	White	SNAP5661WTR	SNAP5461WTR



SNAPConnect® Right Angle Pigtailed 250V Connector

Description	Solid Wire	Stranded Wire
Clear right angle terminal with 6 inch leads, 600V, #12 AWG THHN/THWN-2; Polycarbonate housing material	SNAP251RA	SNAP252RA



Listings

UL Listed to UL498 File No. E2186
Certified to CSA C22.2 No.42
Fed. Spec. W-C-596H
NEMA® WD-6 Compliant

Performance

<i>Electrical</i>	Current Interrupting	Certified for current interrupting at full rated current
	Dielectric Voltage	Withstands 2,000V minimum
<i>Mechanical</i>	Product Identification	Ratings are a permanent part of the device
	Terminal Identification	Terminals identified in accordance with UL 498 and CSA C22.2 No. 42
<i>Environmental</i>	Flammability	UL 94 V-2
	Operating Temperatures	Maximum continuous 75°C; Minimum -40°C (w/o impact)

Online Resources

The Hubbell Wiring Device-Kellems website offers fast and convenient information through our online catalog, technical support, videos and more. Visit www.hubbell.com/wiringdevice-kellems/en

Literature Support

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online.



Hubbell Wiring Device-Kellems
Full Line Catalog



Tamper-Resistant Receptacles



SNAPConnect® Devices



Installation Efficient
Product Solutions



2017 NEC® Code Changes

HUBBELL®
Wiring Device-Kellems

hubbell.com/wiringdevice-kellems/en

