


Series 16 Single Pole Terminals

Quick Disconnect for Temporary Power

Series 16 Single Pole Terminals eliminate the need for hard wire connections on high amperage or large gauge cable.

Hubbell's one piece contact design assures maximum performance and long connector life in temporary power applications.




FEATURES

- Accommodates a variety of application configurations
- One piece solid brass construction
- cULus listed
- Highest performance, coolest running connection
- Easily identifies power phases, neutral and ground
- Straight and angled contacts
- Available in eight colors




Series 16 Single Pole Terminals




Offset Straight Style Terminals

Description	Color	Female	Male
400 amp Terminal, thermoplastic elastomer, mates with 300 and 400 amp plugs.	Black	HBLFOSBK	HBLMOSBK
	White	HBLFOSW	HBLMOSW
	Green	HBLFOSGN	HBLMOSGN
	Red	HBLFOSR	HBLMOSR
	Blue	HBLFOSBL	HBLMOSBL
	Brown	HBLFOSBN	HBLMOSBN
	Orange	HBLFOSO	HBLMOSO
	Yellow	HBLFOSY	HBLMOSY


Dimensions (mm)



HBLFOS




HBLMOS




Offset Angled Style Terminals

Description	Color	Female	Male
400 amp Terminal, thermoplastic elastomer, mates with 300 and 400 amp plugs.	Black	HBLFOABK	HBLMOABK
	White	HBLFOAW	HBLMOAW
	Green	HBLFOAGN	HBLMOAGN
	Red	HBLFOAR	HBLMOAR
	Blue	HBLFOABL	HBLMOABL
	Brown	HBLFOABN	HBLMOABN
	Orange	HBLFOAO	HBLMOAO
Yellow	HBLFOAY	HBLMOAY	



HBLFOA



HBLMOA

Certification / Environmental

UL and cUL Listed.
Flammability: HB per UL94 or CSA 22.2. 0.17.
UL 1691 single pole locking-type separable connectors.
National Electric Code (NEC®), ANSI/NFPA 70.