

Hubbell is redefining the Weatherproof world of wiring devices with an exciting new line up of switches, recessed receptacles and covers for a better way to protect electrical systems for outdoor living.

Weatherproof Style Line® Decorator Switches

Hubbell leads the way with another first, a switch designed especially for the great outdoors. Utilizing a patented internal sealing system, this new switch meets and exceeds the 3R outdoor rating and then some. You no longer need to use a weatherproof cover. Weather protection is built in, making this the ideal device for performance and styling.


These weatherproof switches are designed for wet and damp applications.

- 20 Amp 120/277V AC
- Single Pole / 3-Way Capable
- cULus listed and NEMA 3R



Style Line® Decorator Weatherproof Switches

Description	Color	Catlog Number
Weatherproof rocker, self-grounding, back and side wired, 20A, 120/277V AC	Gray	RSD120WPGY
	Light Almond	RSD120WPLA
	White	RSD120WPW



Weatherproof Non-Metallic EXTRA DUTY® While-In-Use Covers

Hubbell has added a unique solution to our weatherproof, non-metallic device cover line up with the low profile Recessed In-Use Extra Duty rated cover. This is a great alternative for locations to meet the NEC code when space and aesthetics are important.

- Aesthetically pleasing flat profile
- Meets EXTRA DUTY® rating
- Compatible with all common siding types and materials: vinyl, wood, stucco and brick/block
- Mounts horizontally or vertically
- Includes an electrical box and optional siding flange
- Compatibility with duplex, GFCI and single receptacles (receptacle not included)
- cULus listed and NEMA 3R
- Gray, white or bronze housings available with clear covers



Non-Metallic While-In-Use Covers

Description	Color	Catlog Number
1-Gang Weatherproof	Clear/Gray	RW5420CG
EXTRA DUTY® Recessed	Clear/White	RW5420CW
While-In-Use Cover	Clear/Bronze	RW5420CZ



Weatherproof Heavy Cast Aluminum Lockable Cover

Made of heavy cast aluminum that provides high strength. Suitable for industrial and commercial applications.

- Flush enclosure, cover has mounting plate, fits standard 4 inch or 4 11/16 electrical box
- Adapter plates for GFCI, duplex, single 2.16 inch receptacles or switch
- NEMA Type 3R
- cULus listed



Weatherproof Aluminum Lockable Cover

Description	Catalog Number
1 Gang weatherproof 4 in 1 flush enclosure heavy cast aluminum lockable cover	WP4600

Stainless Steel Weatherproof Flip Covers

Stainless steel weatherproof flip covers are suitable for use in heavy duty applications where corrosion and sanitation are vital concerns. Heavy duty 316 stainless steel provides an excellent finish and superior corrosion resistance in all applications.

- Manufactured in heavy duty 316 stainless steel for superior corrosion resistance
- Polished finish for a clean aesthetic appearance
- Smooth surfaces to allow ease of cleaning
- Horizontal and vertical mounting positions
- Duplex and GFCI versions

UL Type 3R

Rain-tight and sleet (ice) resistant
Self-closing lid

UL Type 4X

Watertight, dust-tight and corrosion resistant for wash-down applications
Latching cover



Stainless Steel Weatherproof Flip Covers

Description	Type 3R	Type 4X
1-Gang stainless steel duplex cover	HBLSS83R	HBLSS84X
1-Gang stainless steel GFCI cover	HBLSS263R	HBLSS264X



Duplex cover



GFCI cover