

STINGER COVER

NEW CLASS 3 OFFERING



FEATURES AND BENEFITS

- Designed and tested per ASTM D1050
- Class 3 Type II (ozone-resistant)
- Maximum use voltage of 26.5kV phase-to-phase
- Protection from accidental brush contact with energized components during line maintenance
- For use on overhead lines and transformer stingers
- Maximum conductor size of 1.1inches (28mm)
- 100% visually inspected, electrically tested, and date stamped

Catalog Number	Description	Weight
PSC4060748	Class 3 Type II Rubber Stinger Cover 36" (914 mm)	5.0lb (2.3Kg)



hubbelpowersystems.com



For product inquiries, please contact your local sales representative or customer service representative.

©2020 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_09_217E