

### ASSEMBLY INSTRUCTIONS : ID SEAL® CON-STAB

#### IMPORTANT

**For use on:**  
Polyethylene gas pipe meeting the requirements of  
ASTM D 2513

**Pressure Rating:** Designed to meet or exceed pressure  
rating of PE pipe per 49 CFR Part 192 and ASTM D 2513

**Operating Temperature:** -20 to 140° F



Scan to view  
installation video

**1** Verify the stab fitting is the correct size for the polyethylene (P.E.) pipe. Verify the SDR (or wall thickness) of the pipe matches the SDR (or wall thickness) printed on the fitting label.



**2** Cut pipe ends square.



**3** Clean piping thoroughly to assure there is no dirt, grease or oil in assembly area.



**4a** Chamfer end of pipe using [Continental's ID chamfering tool with ID gauge.](#)


or



**4b** Chamfer end of pipe using [Continental's double ended ID chamfering tool.](#)



**IMPORTANT**  
CHAMFER THE  
ID OF PIPE



CONTINUED ON OTHER SIDE

PATENT #'S 5,366,260, 5,692,785 & 5,853,272



## The Ultimate Connection

Phone: 1-800-558-1373 • Fax: 1-800-788-1668 • [www.conind.com](http://www.conind.com)




**5** Mark the stab depth by inserting pipe into ID chamfer tool and marking the pipe at the entrance as shown.



**7** Stab pipe completely into fitting entrance.



**6** If using ID chamfer tool with gauge, check for proper chamfer by inserting pipe on gauge up to the o ring. With proper chamfer, o ring will begin to enter pipe.



**8** Stab pipe completely into fitting so that the mark on the pipe is within 1/8" from the fitting entrance.



**9** Repeat steps 1 thru 8 for all Con-Stab joints.

**10** To assure proper assembly and to comply with 49 CFR 192 Subpart J—Test Requirements, the joint shall be leak tested.