


AGCH5V - ALUMINUM CENTER BREAK VEE

RATINGS:

15 - 245kV

1200 - 4000A



- Bearings - utilizes stainless steel balls and stainless steel races with galvanized ductile iron housings and operating arms. The bearings are greaseless and sealed at the factory for maintenance free service. Factory adjusted stops are provided with the bearing for ease of synchronization during installation.
- Laminated shunt - transfer of current at the hinge end of the blade is accomplished with a welded aluminum laminated conductor, precisely formed and assembled to give thousands of trouble-free operations. Welded connections create a single conductive metallic path from the hinge terminal pad to the jaw end of the blade. The laminated conductor is constructed of commercially pure aluminum strip, which does not work harden during operation.
- Base - low profile design reduces structure costs, saving the customer time and money
- Operation - unique design allows for low operating force
- Silver plated copper jaw contacts - different silver application processes and hardnesses used on the male and female contacts provide superior anti-galling and reduced wear over the life of the switch



hubbellpowersystems.com

For product inquiries, please contact your local sales representative or customer service representative.

©2019 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_10_235E