

# ELECTRO COMPOSITES STATION POST INSULATORS

## Solid Cycloaliphatic Epoxy Insulator Solutions for your most demanding applications.

Electro Composites™ introduces the EC Cycloaliphatic Epoxy Station Post insulator to Hubbell's line of substation insulators.



### FEATURES

- Meets or exceeds ANSI C29.8 and C29.9 standards for mechanical and electrical ratings
- Solid-core construction with EC proprietary cycloaliphatic epoxy system
- Encapsulated zinc plated steel inserts (optional brass or stainless-steel)
- Offers rigidity like porcelain but lighter weight
- Non-tracking, UV resistant material
- Operating temperature range -50°C to 90°C
- Animal resistant sheds (rodents, birds)
- Optional 130°C thermal limit resin system for high temperature applications
- Custom made-to-order configurations available on request

MODEL	TR NUMBER	BIL RATING (kV)	SYSTEM VOLTAGE (kV)	LENGTH (in)	TOP BC	BOTTOM BC	CANTILEVER STRENGTH CLASS (lbf)
T202A	TR 202	95	8.7	7.5	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T205A	TR 205	110	15	10	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T007A	TR 7	150	25	12	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T208A	TR 208	150	25	14	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T010A	TR 10	200	34.5	15	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T210A	TR 210	200	34.5	18	(4) 1/2-13 on 3" BC	(4) 1/2-13 on 3" BC	2000
T222B	TR 222	95	8.7	10	(4) 5/8-11 on 5" BC	(4) 5/8-11 on 5" BC	4000
T225A	TR 225	110	15	12	(4) 5/8-11 on 5" BC	(4) 5/8-11 on 5" BC	4000



[hubbellpowersystems.com](http://hubbellpowersystems.com)

For more information about Electro Composite products and services, contact your local Hubbell representative or call our factory at 450-431-2777 or email us at [bushings@hubbell.com](mailto:bushings@hubbell.com)

©2023 Hubbell Incorporated.  
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.  
Printed in the U.S.A. | SF\_02\_018E