

Hubbell SystemOne

Recessed Fire-Rated
Poke-Throughs

4, 6, 8 and 10 inch



from the Leader in Delivery Systems

Hubbell SystemOne Recessed FRPTs

Hubbell's SystemOne Recessed Fire-Rated Poke-Throughs (FRPT) enhance functionality providing increased power, data and AV capacity. Safety is improved with recessed connectivity, a low profile flange, and egress doors that hinge inwards. Building value is enhanced with plated finishes to match and blend with modern building décor.

4 Inch Concrete Core Hole Applications...



4 Inch Quad Sub-Plate


The pre-wired quad sub-plate assembly includes 12 inches of stranded wire which can be wired as one or two individual circuits with standard or isolated grounds.




4 Inch 2X2 Sub-Plate

The 2x2 sub-plates are available with Style Line® or traditional duplex openings and can accommodate up to two keystone jacks.

4 Inch Recessed Access



Quad Sub-Plate



Multi & Single Service Sub-Plates

6 Inch Concrete Core Hole Applications...



60/40 6 Inch Sub-Plate Split


An Industry first, the 60/40 sub-plate layout allows for unmatched capacity with up to 12 keystone jacks and one 20A duplex.



50/50 6 Inch Sub-Plate Split

Two duplexes with ample AV and data are achieved by using the 50/50 sub-plate layout. Additionally this layout will accommodate two Style Line® devices for GFCI, surge, etc. applications.

6 Inch Recessed Access



60/40 split Sub-Plates



50/50 split Sub-Plates

Hubbell SystemOne Recessed FRPTs

Hubbell's SystemOne Recessed Fire-Rated Poke-Throughs (FRPT) enhance functionality by providing increased power, data and AV capacity. Safety is improved with recessed connectivity, a low profile flange, and egress doors that hinge inwards. Building value is enhanced with plated finishes to match and blend with modern building décor.

8 Inch Concrete Core Hole Applications...



High Capacity Multimedia Applications


Sub-plate layout for the center three gangs of the eight inch FRPT allows for maximum AV capacity. The NEMA spacing allows the product flexibility to easily accept 3rd party products.



Sub-Plates Offer Application Flexibility

Perimeter sub-plates for the eight inch FRPT help compliment the AV or data in the center three gangs. Additionally these plates can be exchanged for other low voltage compatible plates.

8 Inch Recessed Access



Center Sub-Plates
with Perimeter Sub-plates

10 Inch Concrete Core Hole Applications...



High Capacity Multimedia Applications


Sub-plate layout for the center four gangs of the ten inch FRPT allows for maximum AV capacity. The NEMA spacing plate allows the product flexibility to easily accept 3rd party products.



Sub-Plates Offer Application Flexibility

Perimeter sub-plates for the ten inch FRPT help compliment the AV or data in the center four gangs. Additionally these plates can be exchanged for other low voltage compatible plates.

10 Inch Recessed Access



Center Sub-Plates
with Perimeter Sub-plates

Fire-Rated Poke-Throughs

ScrubShield®
Complies with UL514A



How to Order 4, 6, 8 and 10 Inch SystemOne Products

STEP 1: Select Recessed Access Poke-Through

4 Inch



6 Inch



8 Inch



10 Inch



Or Select Furniture Feed Poke-Through

4 Inch



6 Inch



10 Inch




STEP 2: Select Recessed Access Sub-Plate

4 Inch




Quad
Sub-Plates

6 Inch




60/40 Split
Sub-Plates

8 Inch



Center Sub-Plates
with Perimeter Sub-plates

10 Inch



Center Sub-Plates
with Perimeter Sub-plates




2X2
Sub-Plates



50/50 Split
Sub-Plates



3-Gang Data/AV Center Extension with
Perimeter Power Sub-Plates



Open Data/AV Center Sub-Plate with
Perimeter Power Sub-Plates

Note: Furniture feed version does not require sub-plates.

Fire-Rated Poke-Throughs

ScrubShield®
Complies with UL514A



How to Order 4, 6, 8 and 10 Inch SystemOne Products

STEP 3: Select Recessed Cover (Aluminum cover shown, see below for all available finishes)

4 Inch



6 Inch



8 Inch



10 Inch



Note: Tamper-Resistant 10 inch covers are also available.

Or Select Furniture Feed Cover (Aluminum cover shown, see below for all available finishes)

4 Inch



6 Inch



10 Inch




Available Cover Finishes

Brushed Aluminum



Brushed Brass Plated



Antique Bronze Plated



Black Powder Coat



Gray Powder Coat



Satin Nickel Plated



Recommended Fire-Rated Poke-Through Size Chart

To avoid over or under utilizing the capacity of the fire-rated poke-through, first determine how many gangs of power, data and AV are required for the application. The matrix below will guide you to the correct poke-through size.

Recommended Fire-Rated Poke-Through Size						
POWER GANGS	5	8"	10"	10"	10"	Exceeds capacity of Hubbell recessed poke-throughs
	4	8"	8"	10"	10"	10"
	3	6"	8"	8"	10"	10"
	2	6"	6"	8"	8"	10"
	1	4"	6"	6"	8"	8"
	0	—	4"	6"	8"	8"
DATA AND AV GANGS						
		0	1	2	3	4
		5	4	3	2	1

Example: 2-gangs of power, 1-gang of AV and 1-gang of data is required. Find the intersection for 2 power gangs with 2 data/AV gangs. The highlighted intersection defines the recommended FRPT.

Features and Benefits

SystemOne Recessed 4 Inch Fire-Rated Poke-Through Fittings

- Maintains concrete floor fire rating up to two hours
- Junction box standard, 27 cubic inches
- (1) ¾ inch conduit for power and (2) ½ inch conduits for low voltage
- For use in the City of Chicago applications, junction box is NOT included
- Works with time and labor saving 4" concrete pre-pour tube



4 Inch FRPT
with Accessories



FRPT Design

- Step down installation
- Flexible single or dual service
- Recessed connections




Covers

- Durable die-cast aluminum cover
- 1,000 lb, static load rated cover
- Available in six architectural finishes



Chamber

- 3-inch deep user access chamber
- Deep wiring chamber for GFCI and USB devices
- Low voltage dividers
- Perimeter chamber:
(2) ½ inch EMTs bottom feed
- Center chamber:
(1) ¾ inch EMT bottom feed



Easy Mount Device Plates

- Field configurable device plates
- Multiple, open architecture mounting plates for power, data and AV



Safety

- Low profile flange, 0.15 inch exceeds ADA requirements
- Hide-away egress door folds under cover while in use
- 180° opening of main door



4 Inch Sub-Plate Features

- Sub-plates accept Hubbell keystone jacks
- Third party sub-plates accept Ortronics® TracJack®


TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

SystemOne Recessed 4 Inch Core Hole Kits, for Use In Concrete Floors

Pre-Wired, 4 Inch Quad Receptacle Kit, Recessed Connectivity, Fire-Rated Poke-Through for Power Only

Kits include:

- (1) Hubbell SystemOne 4 inch recessed floor fitting (S1R4PTFIT)
- (1) Hubbell pre-wired quad receptacle with mounting plate (S1R4SPQUAD)
- (1) Hubbell SystemOne 4 inch recessed activation cover (S1R4CVRxx)
- (1) Hubbell Junction box (S1FRPTJB)



Cover Finish	Catalog Number
Brushed Aluminum	S1R4PTQUADALU
Black Powder Coat	S1R4PTQUADBLK
Brushed Brass Plated	S1R4PTQUADBRS
Antique Bronze Plated	S1R4PTQUADBRZ
Gray Powder Coat	S1R4PTQUADGRY
Satin Nickel Plated	S1R4PTQUADNKL



S1R4PTQUADALU

4 Inch Fire-Rated Poke-Through Kit, Recessed Connectivity

Kits include:

- (1) Hubbell SystemOne 4 inch recessed floor fitting (S1R4PTFIT)
- (1) Hubbell SystemOne 4 inch recessed activation cover (S1R4CVRxx)
- (1) Hubbell Junction box (S1FRPTJB)



Cover Finish	Catalog Number
Brushed Aluminum	S1R4PTALU
Black Powder Coat	S1R4PTBLK
Brushed Brass Plated	S1R4PTBRS
Antique Bronze Plated	S1R4PTBRZ
Gray Powder Coat	S1R4PTGRY
Satin Nickel Plated	S1R4PTNKL



S1R4PTBRS

Note: xx indicates finish options.

SystemOne Recessed 4 Inch FRPT and Covers, for Use In Concrete Floors

4 Inch Fire-Rated Poke-Throughs

Description	Catalog Number
4 Inch FRPT includes: Junction box and low voltage dividers.	S1R4PTFIT
4 Inch FRPT includes: Low voltage dividers, junction box NOT included.	S1R4PTFITCHI
4 Inch FRPT includes: Quad sub-plate and junction box.	S1R4PTQUAD

Note: See page 8 for sub-plates and accessories.



S1R4PTFIT
S1R4PTFITQUAD

Recessed 4 Inch Covers

Single fold under cable egress door. Unit includes solid cast aluminum construction, carpet gasket and mounting hardware.



Cover Finish	Catalog Number
Brushed Aluminum	S1R4CVRALU
Black Powder Coat	S1R4CVRBLK
Brushed Brass Plated	S1R4CVRBRS
Antique Bronze Plated	S1R4CVRBRZ
Gray Powder Coat	S1R4CVRGRY
Satin Nickel Plated	S1R4CVRNKL

Note: COVER LOAD RATING: 1,000 lb with 2x safety factor. Load applied through a 3" (76mm) dia. mandrel at the center of the cover.
Rated for static loads only.



S1R4PTFITCHI

Fire-Rated Poke-Throughs

ScrubShield®
Complies with UL514A



SystemOne Recessed 4 Inch Sub-Plates and Accessories

The 4 Inch recessed cover is available in a number of durable, yet beautiful finishes to match any décor. The flange height of 0.15 inch exceeds ADA requirements and suitable for use on any floor finish. All covers are UL514A, scrubwater compliant.



Device Mounting Plates

Description / Catalog Number	Sub-plate	Description / Catalog Number	Sub-plate	Description / Catalog Number	Sub-plate
2X2 Sub-plate with (1) Style Line® decorator device opening and (2) keystone jack openings S1R4SP2X2STYLE		(1) Style Line® decorator device opening for power or datacom applications S1R4SPSTYLE		2X2 Sub-plate with (1) Style Line® decorator device opening and (2) Ortronics® TracJack® openings S1R4SP2X2STYLETJ	
2X2 Sub-plate with (1) duplex device opening and (2) keystone jack openings S1R4SP2X2DUPLEX		(1) Duplex device opening for power or datacom applications S1R4SPDUPLEX		2X2 Sub-plate with (1) duplex device opening and (2) Ortronics® TracJack® openings S1R4SP2X2DUPLEXTJ	
(4) Single 20A receptacles. Can be wired as single or two circuit with isolated ground capability, 12" wire leads S1R4SPQUAD		(1) 1.60" opening for 20A or 30A Twist-Lock® receptacle S1R4SPTWIST		(1) 1.40" opening for simplex receptacle S1R4SPSIMPLEX	

Note: See page 25 for data jacks and frames.



For low light applications (i.e. under tables or podiums) consider using Hubbell's LED illuminated receptacles: HBL8200ILW 15A, LED or HBL8300ILW 20A, LED.

HBL8300ILW



S1R4PPT



S1R4FRPTADMTBK

S1R4DIV

4 Inch Accessories

Description	Catalog Number
Pre-pour tube, includes hardware.	S1R4PPT*
Abandonment plate, black finish.	S1R4FRPTADMTBK
Low voltage replacement divider.	S1R4DIV

Note: *Not UL Listed.

Design Solutions for:

Retail, Cafeterias, Commercial Office Space, Mass Transit Hubs, Education



Tile



Carpet



Terrazzo

For Technical files, including BIM models, CAD files and Customer drawings, please visit www.hubbell.com/wiringdevice-kellems/en under the Technical tab.

TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

Features and Benefits

SystemOne Recessed 4 Inch Furniture Feed Fire-Rated Poke-Through Fittings

- Excellent solution for retrofit and new construction
- Maintains concrete floor fire rating up to 4 hours
- One ¾ inch conduit for power and one 1½ inch conduit for low voltage
- Junction box standard, 27 cubic inches
- For use in the City of Chicago, junction box is NOT included
- Works with time and labor saving 4" concrete pre-pour tube



4 Inch Furniture Feed FRPT with Accessories



FRPT Design

- Step down installation
- Flexible single or dual service
- Adjustable lower fire barrier accommodates concrete floor thicknesses from 2¼ to 7 inch



Cover Construction

- Durable die-cast aluminum cover
- 1,000 lb, static load rated cover
- Available in six architectural finishes



Chambers

- Fittings include removable metallic low voltage divider
- Cover hubs in-line with fitting EMT conduits for easy wiring
- (1) 1½ inch EMT conduit for low voltage
- (1) ¾ inch EMT conduit for power



Furniture Feed Cover Design

- Seamless one piece design
- (1) 1½ inch EMT conduit for low voltage
- (1) ¾ inch EMT conduit for power
- 5½ inch diameter flange



Safety

- Low profile flange, 0.15 inch exceeds ADA requirements
- UL514A scrubwater compliant



Application Compatibility

- Hubbell PolyTuff® I conduits
- Hubbell SwivelLok® fittings
- Metallic/Non-metallic liquidtight fittings

SystemOne Furniture Feed 4 Inch Core Kits, Covers and Accessories



S1R4PTFFALU

SystemOne Furniture Feed 4 Inch Core Kits, Use In Concrete Floors

Flush Connectivity

	Cover Finish	Without Junction Box	With Junction Box
Kits Include: (1) Hubbell SystemOne 4 Inch flush furniture feed fitting (S1R4PTAVFIT) (1) Hubbell SystemOne 4 Inch flush furniture feed activation cover (S1R4FFCVRxx)	Brushed Aluminum	S1R4PTFFALU	S1R4PTFFALUJ
	Black Powder Coat	S1R4PTFFBLK	S1R4PTFFBLKJ
	Brushed Brass Plated	S1R4PTFFBRS	S1R4PTFFBRSJ
	Antique Bronze Plated	S1R4PTFFBRZ	S1R4PTFFBRZJ
	Gray Powder Coat	S1R4PTFFGRY	S1R4PTFFGRYJ
	Satin Nickel Plated	S1R4PTFFNKL	S1R4PTFFNKLJ



S1R4PTFFBLKJ

SystemOne Furniture Feed 4 Inch FRPT and Covers, Use In Concrete Floors

Description	Catalog Number
Includes: low voltage divider, junction box NOT included	S1R4PTAVFIT
Includes: low voltage divider and junction box	S1R4PTAVFITJ

Flush 4 Inch Furniture Feed Covers

One piece cover solid cast aluminum construction with (1) 1½" hub for low voltage and (1) ¾" hub for power. Liquid-tight fittings not included.



S1R4PTAVFIT



Cover Finish	Catalog Number
Brushed Aluminum	S1R4FFCVRALU
Black Powder Coat	S1R4FFCVRBLK
Brushed Brass Plated	S1R4FFCVRBRS
Antique Bronze Plated	S1R4FFCVRBRZ
Gray Powder Coat	S1R4FFCVRGRY
Satin Nickel Plated	S1R4FFCVRNKL

Note; COVER LOAD RATING: 1,000 lb with 2x safety factor. Load applied through a 3" (76mm) dia. Mandrel at the center of cover without fittings installed. Rated for static loads only.



S1R4PPT

4 Inch Furniture Feed Accessories

Description	Catalog Number
Pre-pour tube, includes mounting hardware.	S1R4PPT*
Abandonment plate, black finish.	S1R4FFADMTBK

*Note: *Not UL Listed.*



S1R4FFADMTBK

SystemOne Fire-Rated Poke-Through and Floor Box Recessed Covers



Two Concrete Floor Applications

Fire-Rated Poke-Throughs are used when the conduits can't be installed in the concrete floor and for tenant improvements.




Floor boxes in concrete applications are used when the connecting conduits can be installed into the concrete floor.



Same Results!

Round low profile durable cover with recessed connections.



Features and Benefits

SystemOne Recessed 6 Inch Fire-Rated Poke-Through Fittings

- Maintains concrete floor fire rating up to two hours
- Junction box standard
- Includes (1) 2 inch data/AV EMT and (1) ¾ inch power EMT
- For use in the City of Chicago applications, junction box is NOT included
- Features ScrubShield® technology that exceeds UL514A scrubwater exclusion requirements
- Works with time and labor saving 6" concrete pre-pour tube



6 Inch FRPT
with Accessories



FRPT Design

- Step down installation
- Flexible single or dual service
- Recessed connections




Covers

- Durable die-cast aluminum cover
- 1,000 lb, static load rated cover
- Available as recessed or furniture feed
- Available in six architectural finishes



Chamber

- Recessed 3.5 inch deep connectivity chamber
- Large wiring compartments divides up to 2.9 inch (73mm) deep
- Adaptable low voltage divider
- 2-inch EMT bottom feed
- ¾-inch EMT bottom feed



Easy Mount Device Plates

- Multiple, open architecture mounting plates for power, data and AV



Safety

- Low profile flange, 0.15 inch exceeds ADA requirements
- Two hide-away egress doors fold under cover while in use
- 180° opening of main door



6 Inch Sub-Plate Features 60/40 or 50/50 Device Plate Combinations

- Allows for a wide array of data and AV connectivity with a 20A duplex receptacle
- The two plates can be independently wired


SystemOne Recessed 6 Inch Core Hole Kits, for Use In Concrete Floors

Pre-Wired 60/40 Split 6 Inch Fire-Rated Poke-Through for Data AV Kits

Kits include:

- (1) Hubbell SystemOne 6 inch floor fitting (S1R6PTFIT)
- (2) Decorator opening sub-plate (S1R6SPW)
- (2) 20A, pre-wired receptacle with 18 inch wire leads (S1R6SPZ)
- (1) 6 inch flange and universal cover assembly (S1R6CVRxx)

Receptacles feature single circuit wiring.



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R6PTWZALU
S1R6PTWZBLK
S1R6PTWZBRS
S1R6PTWZBRZ
S1R6PTWZGRY
S1R6PTWZNKL



S1R6PTWZALU


Pre-Wired 50/50 Split 6 Inch Fire-Rated Poke-Through for Hubbell Data AV Kits

Kits include:

- (1) Hubbell SystemOne 6 inch floor fitting (S1R6PTFIT)
- (4) 1 Unit Hubbell iSTATION openings (S1R6SPD)
- (1) Decorator opening and (2) keystone openings (S1R6SPE)
- (4) 20A, pre-wired receptacles (S1R6SPH)
- (1) 6 inch flange and universal cover assembly (S1R6CVRxx)

Opening architecture Keystone openings accept Hubbell modular jacks and many others.

Receptacles feature single or two circuit wiring and isolated ground capability.



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R6PTDEHALU
S1R6PTDEHBLK
S1R6PTDEHBRS
S1R6PTDEHBRZ
S1R6PTDEHGRY
S1R6PTDEHNKL



S1R6PTDEHBLK


Pre-Wired 50/50 Split 6 Inch Fire-Rated Poke-Through for Hubbell or Third Party Devices Kits

Kits include:

- (1) Hubbell SystemOne 6 inch floor fitting (S1R6PTFIT)
- (3) Extron® AAP openings (S1R6SPA)
- (5) Extron® MAPP openings (S1R6SPC)
- (1) Decorator opening and (2) Hubbell keystone openings (S1R6SPE)
- (4) 20A, pre-wired receptacles (S1R6SPH)
- (1) 6 inch flange and universal cover assembly (S1R6CVRxx)

Opening architecture Keystone openings accept Hubbell modular jacks and many others.

Receptacles feature single or two circuit wiring and isolated ground capability.



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R6PTACEHALU
S1R6PTACEHBLK
S1R6PTACEHBRS
S1R6PTACEHBRZ
S1R6PTACEHGRY
S1R6PTACEHNKL



S1R6PTBRS

6 Inch Fire-Rated Poke-Through with Finished Cover Kits

Kits include:

- (1) Hubbell SystemOne 6 inch floor fitting (S1R6PTFIT)
- (1) 6 inch flange and universal cover assembly (S1R6CVRxx)



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R6PTALU
S1R6PTBLK
S1R6PTBRS
S1R6PTBRZ
S1R6PTGRY
S1R6PTNKL



S1R6PTFFNKL

6 Inch Fire-Rated Poke-Through for Furniture Feed Applications Kits

Kits include:

- (1) Hubbell SystemOne 6 inch floor fitting (S1R6PTFIT)
- (1) 6 inch furniture feed flange and cover assembly (S1R6FFCVRxx)
- (1) 2 inch conduit fitting
- (1) ¼ inch conduit fitting



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R6PTFFALU
S1R6PTFFBLK
S1R6PTFFBRS
S1R6PTFFBRZ
S1R6PTFFGRY
S1R6PTFFNKL

Note: xx indicates finish options.

Extron® is a registered trademark of Extron Electronics.

SystemOne Recessed 6 Inch FRPT and Covers, for Use In Concrete Floors



S1R6PTFIT



S1R6PTFITCHI



S1R6PPT



S1R6ADMTBK



S1FRPTJB



S1R6DIV



S1R6SPEXT



S1RFFFIT2



S1RPLUG2ALU



S1RPLUG075ALU

6 Inch Fire-Rated Poke-Throughs

Description	Catalog Number
6 Inch Fire-Rated Poke-Through.	S1R6PTFIT
6 Inch Fire-Rated Poke-Through; for use in the City of Chicago.	S1R6PTFITCHI

Recessed 6 Inch Covers

6 Inch FRPT cover assembly unit includes solid cast aluminum construction, carpet gasket and mounting hardware.



Cover Finish	Catalog Number	Furniture Feed Option
Brushed Aluminum	S1R6CVRALU	S1R6FFCVRALU
Black Powder Coat	S1R6CVRBLK	S1R6FFCVRBLK
Brushed Brass Plated	S1R6CVRBRS	S1R6FFCVRBRS
Antique Bronze Plated	S1R6CVRBRZ	S1R6FFCVRBRZ
Gray Powder Coat	S1R6CVRGRY	S1R6FFCVRGRY
Satin Nickel Plated	S1R6CVRNKL	S1R6FFCVRNKL

Note: COVER LOAD RATING: 1,000 lb with 2x safety factor. Load applied through a 3 in. (76) mandrel at the center of the cover. Static loads only.

6 Inch Accessories

Description	Catalog Number
Pre-pour tube, includes hardware.	S1R6PPT*
Abandonment plate, black finish.	S1R6ADMTBK
Low voltage replacement divider.	S1R6DIV
Power junction box, 27.0 cubic inches; (1) 3/4 inch and (1) 1 inch EMT connector.	S1FRPTJB
Replacement 1 1/2 inch extension kit.	S1R6SPEXT
Power junction box.	S1FRPTJB2

*Note: *Not UL Listed.*

Replacement Furniture Feed Fitting

Description	Catalog Number
2 inch furniture feed fitting.	S1RFFFIT2

Replacement Plugs

Finish	2 Inch	3/4 Inch
Brushed Aluminum	S1RPLUG2ALU	S1RPLUG075ALU
Black Powder Coat	S1RPLUG2BLK	S1RPLUG075BLK
Brushed Brass Plated	S1RPLUG2BRS	S1RPLUG075BRS
Antique Bronze Plated	S1RPLUG2BRZ	S1RPLUG075BRZ
Satin Nickel Plated	S1RPLUG2NKL	S1RPLUG075NKL

SystemOne Recessed 6 Inch Sub-Plates, for Use In Concrete Floors

60/40 Device Plate Combination

- Allows for up to twelve data/AV jacks plus a 20A duplex receptacle
- Two plates which can be wired independently



Left 60% Sub-Plates

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(1) Extron® MAAP opening, (4) Extron® MAAP openings, (1) Extron® MAAP opening, left side only		(2) 1.5 unit Hubbell iSTATION openings, left side only (2) Extron® AAP openings, left side only	
S1R6SPT*		S1R6SPU*	
(1) Style Line® decorator and (2) Extron® MAAP openings, left side only		(2) Style Line® decorator openings, left side only	
S1R6SPV*		S1R6SPW*	
(1) Style Line® decorator and (2) Extron® AAP openings, left side only		(1) Style Line® decorator and (2) 1.5 unit Hubbell iSTATION openings, left side only (See section Y for modules)	
S1R6SPX*		S1R6SPY*	

Right 40% Sub-Plates

(2) 20A pre-wired receptacles; 18" lead; one circuit, right side only (Supplied with isolated ground sticker)		(2) 20A pre-wired receptacles; 25 foot lead; one circuit, right side only (Supplied with isolated ground sticker)	
S1R6SPZ		S1R6SPZ25	
(2) 20A pre-wired receptacles; 18" lead; one circuit, right side only (Supplied with isolated ground sticker); Marked with "Controlled"			
S1R6SPZC			

Note: Sub-plates can not be rotated to create additional layouts. When assembled, sub-plates can not overlap. Custom plates available upon request and may be subject to minimum order quantity.

*Sub-plates must only be used for Data/AV. Do not mix with power devices. See page 14 for covers and accessories.

Note: See page 25 for data jacks and frames.

Extron® is a registered trademark of Extron Electronics.
TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

50/50 Device Plate Combination

- Allows for up to eight Hubbell data jacks plus two 20A duplex receptacles
- Two plates which can be wired independently



Left 50% Sub-Plates

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(3) Extron® AAP plate openings, left side only		Blank cover plate, left side only	
S1R6SPA		S1R6SPB	
(5) Extron® MAAP plate openings, left side only		(4) 1 unit Hubbell iSTATION openings, left side only (See section Y for modules)	
S1R6SPC		S1R6SPD	
(1) Style Line® decorator and (2) Hubbell keystone openings, left side only		(2) 1.5 unit Hubbell iSTATION openings, left side only (See section Y for modules)	
S1R6SPE*		S1R6SPF	
(3) Extron® MAAP openings and (2) Hubbell keystone jack openings, left side only		(1) Style Line® decorator opening, left side only	
S1R6SPL		S1R6SPM	
(1) Decorator opening and (2) Ortronics® TracJack® openings, left side only			
S1R6SPN			

Right 50% Sub-Plates

(1) Duplex device opening, right side only		(1) Style Line® Decorator device opening, right side only	
S1R6SPI		S1R6SPK	
(1) 1.60" opening for 20A and 30A Twist-Lock®, right side only		(1) 1.40" opening for simplex or 15A Twist-Lock®, right side only	
S1R6SPG		S1R6SPJ	
(4) 20A pre-wired receptacles; one or two circuits, right side only (Supplied with isolated ground sticker)		(4) 20A pre-wired receptacles; 18" leads; one or two circuits, right side only; Marked with "Controlled"	
S1R6SPH (18" leads)		S1R6SPHC4 (4 Controlled)	
S1R6SPH25 (25 foot leads)		S1R6SPHC2 (2 Controlled)	

Features and Benefits

SystemOne Recessed 8 Inch Fire-Rated Poke-Through Fittings

- Perfect for high capacity multimedia applications where power and low voltage are required
- Maintains concrete floor fire rating up to two hours
- Fitting box standard
- For use in the City of Chicago applications, fitting box is NOT included
- Features ScrubShield® technology that exceeds UL514A scrubwater exclusion requirements
- Works with time and labor saving 8" concrete pre-pour tube



8 Inch FRPT
with Accessories



FRPT Design

- Step down installation
- Flexible single or dual service
- Recessed connections




Covers

- Durable die-cast aluminum cover
- 1,000 lb, static load rated cover
- Available in six architectural finishes




Chamber

- Recessed 3.5 inch deep connectivity chamber
- Large wiring compartments
- Fixed wiring chambers
- On-site exchangeable center compartment fitting
- Standard 3/4-inch EMT



Easy Mount Device Plates

- Multiple, open architecture mounting plates for power, data and AV
- 3 center gangs
- 2 independent perimeter gangs



Safety

- Low profile flange, 0.15 inch exceeds ADA requirements
- Two hide-away egress doors fold under cover while in use
- 180° opening of main door



8 Inch Sub-Plate Features

- Center and perimeter plate configurations
- Available in pre-wired 20A duplex receptacles or data/AV plates
- Multiple 20A duplex receptacles can be wired to a common circuit or independently
- NEMA spacing between devices

Fire-Rated Poke-Throughs

ScrubShield®
Complies with UL514A




SystemOne Recessed 8 Inch Core Hole Kits, for Use In Concrete Floors

Pre-Wired 8 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT1)
- (4) 20A, pre-wired receptacles, 18 inch wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with 1 inch and 1½ inch EMT stubs (S1R8JNC1)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R8PTZZ1ALU
S1R8PTZZ1BLK
S1R8PTZZ1BRS
S1R8PTZZ1BRZ
S1R8PTZZ1GRY
S1R8PTZZ1NKL




S1R8PTZZ1NKL

8 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT1)
- (1) Fitting connection box with 1 inch and 1½ inch EMT stubs (S1R8JNC1)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number


S1R8PT1ALU
S1R8PT1BLK
S1R8PT1BRS
S1R8PT1BRZ
S1R8PT1GRY
S1R8PT1NKL

Pre-Wired 8 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT2)
- (4) 20A, pre-wired receptacles, 18 inch wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with (2) 1 inch EMT stubs (S1R8JNC2)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R8PTZZ2ALU
S1R8PTZZ2BLK
S1R8PTZZ2BRS
S1R8PTZZ2BRZ
S1R8PTZZ2GRY
S1R8PTZZ2NKL




S1R8PT2BLK

8 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT2)
- (1) Fitting connection box with (2) 1 inch EMT stubs (S1R8JNC2)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R8PT2ALU
S1R8PT2BLK
S1R8PT2BRS
S1R8PT2BRZ
S1R8PT2GRY
S1R8PT2NKL

Pre-Wired 8 Inch Fire-Rated Poke-Through for Data AV Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT3)
- (4) 20A, pre-wired receptacles, 18 inch wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with one 2 inch EMT stubs (S1R8JNC3)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R8PTZZ3ALU
S1R8PTZZ3BLK
S1R8PTZZ3BRS
S1R8PTZZ3BRZ
S1R8PTZZ3GRY
S1R8PTZZ3NKL



S1R8PTZZ3BRS

8 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 8 inch floor fitting (S1R8PTFIT3)
- (1) Fitting connection box with (1) 2 inch EMT stubs (S1R8JNC3)
- (1) 8 inch flange and universal cover assembly (S1R8CVRxx)



Cover Finish

Brushed Aluminum
Black Powder Coat
Brushed Brass Plated
Antique Bronze Plated
Gray Powder Coat
Satin Nickel Plated

Catalog Number

S1R8PT3ALU
S1R8PT3BLK
S1R8PT3BRS
S1R8PT3BRZ
S1R8PT3GRY
S1R8PT3NKL

Note: xx indicates finish options.

SystemOne Recessed 8 Inch FRPT and Covers, for Use In Concrete Floors



S1R8PTFIT1



S1R8PTFIT2CHI

8 Inch Fire-Rated Poke-Throughs

Description	Catalog Number
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1FRPTJB box and flexible metal conduit. S1R8JNCxx Series fitting box not included.	S1R8PTFIT
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC1 with (1) 1 inch EMT and (1) 1½ inch EMT. (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT1
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC2 with (2) 1 inch EMT (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT2
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC3 with (1) 2 inch EMT (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT3
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC1 with (2) 1 inch EMT and (1) 1½ inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT1CHI
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC2 with (2) 1 inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT2CHI
8 Inch Fire-Rated Poke-Through includes: (1) ¾ inch power EMT plus (1) S1R8JNC3 with (1) 2 inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT3CHI

Recessed 8 Inch Covers

8 Inch FRPT cover assembly unit includes solid cast aluminum construction, carpet gasket and mounting hardware.



Finish	Catalog Number
Brushed Aluminum	S1R8CVRALU
Black Powder Coat	S1R8CVRBLK
Brushed Brass Plated	S1R8CVRBRS
Antique Bronze Plated	S1R8CVRBRZ
Gray Powder Coat	S1R8CVRGRY
Satin Nickel Plated	S1R8CVRNKL

Note: COVER LOAD RATING: 1,000 lb with 2x safety factor. Load applied through a 3" (76mm) dia. mandrel at the center of the cover. Rated for static loads only.



S1R8JNC1



S1R8JNC7



S1R8JNC2



S1R8JNC9



S1R8JNC3



S1R8JNC10



S1R8JNC4



S1R8JNC11



S1R8JNC6



S1R8JNC12

Fitting Boxes

Description	Catalog Number
(1) 1½ inch & (1) 1 inch EMT.	S1R8JNC1
(2) 1 inch EMTs.	S1R8JNC2
(1) 2 inch EMT.	S1R8JNC3
(3) 1 inch EMTs.	S1R8JNC4
(1) 1½ inch & (1) 1¼ inch EMT.	S1R8JNC5
(2) 1¼ inch EMTs.	S1R8JNC6
(1) ¾ inch & (2) 1 inch EMTs.	S1R8JNC7
(1) ¾ inch & (1) 1¼ inch EMT.	S1R8JNC8
(1) ¾ inch & (2) 1¼ inch EMTs.	S1R8JNC9
(1) 1¼ inch & (1) 2 inch EMT.	S1R8JNC10
(1) 1½ inch & (1) 2 inch EMT.	S1R8JNC11
(3) 1¼ inch EMTs.	S1R8JNC12

8 Inch Accessories

Description	Catalog Number
Pre-pour tube, includes hardware.	S1R8PPT*
Abandonment plate, black finish.	S1R8ADMTBK
Low voltage replacement divider.	S1R8DIV
Power junction box, 27.0 cubic inches; (1) ¾ inch and (1) 1 inch EMT connector.	S1FRPTJB

*Note: *Not UL Listed.*



S1R8PPT



S1R8ADMTBK



S1R8DIV



S1FRPTJB

SystemOne Recessed 8 Inch Sub-Plates

Center Plate Configurations

- Allows for 3 duplexes or up to 18 data/AV jacks. Other combinations possible
- Accepts third party AV devices (i.e. Extron®, Crestron®, FSR®)
- Standard NEMA spacing between devices



Perimeter Plate Configurations

- Available in pre-wired duplexes or openings to accommodate third party AV devices
- Multiple duplexes can be wired in the supplied junction box or independently



Center Sub-Plates - Single Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
Blank cover plate		(2) Extron® MAAP openings	
S1R8CSPB		S1R8CSPC	
(1) 1 unit Hubbell iSTATION opening		(1) 1.5 unit Hubbell iSTATION opening (See section Y for modules)	
S1R8CSPD		S1R8CSPE	
(1) 1.60" opening for 20A & 30A Twist-Lock®		(1) Duplex opening	
S1R8CSPG		S1R8CSPI	
(1) 1.40" opening for simplex or 15A Twist-Lock®		(1) Style Line® decorator opening	
S1R8CSPJ		S1R8CSPK	

Perimeter Sub-Plates

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
Blank cover plate		Single Extron® MAAP opening	
S1R8PSPU		S1R8PSPV	
Pull through with 1" bushing opening		Single Extron® AAP opening	
S1R8PSPW		S1R8PSPX	
(1) 1 unit Hubbell iSTATION opening (See section Y for modules)		Dual 20A pre-wired power cubes; one circuit (Supplied with isolated ground sticker)	
S1R8PSPY		S1R8PSPZ (18" leads) S1R8PSPZ25 (25 foot leads)	
Dual 20A pre-wired power cubes; one circuit (Supplied with isolated ground sticker); Marked with "Controlled" (18" leads)		S1R8PSPZC	

Center Sub-Plates - Two Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
Two gang; (4) Extron® AAP openings		Two gang; 3 unit Hubbell iSTATION opening (See section Y for modules)		Two gang; (2) Style Line® Decorator openings		Two gang; device depth extension collar (for use with 3rd party data up to 2.5" depth)	
S1R8CSPA		S1R8CSPL		S1R8CSPM		S1R8CSPEXT	

Center Sub-Plates - Three Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
Three gang; blank cover plate		Three gang; device depth extension collar (for use with 3rd party data up to 2.5" depth)		Three gang extender with two gang opening; device depth extension collar (for use with 3rd party data up to 2.5" depth)	
S1R8CSPN		S1R8CSPEXT3		S1R8CSPEXT32	

Note: Rectangle sub-plates are for center compartment, crescent sub-plates are for perimeter compartments and are not inter-changeable.
See page 18 for covers and accessories and page 25 for data jacks and frames.

Extron® is a registered trademark of Extron Electronics.
Crestron® is a registered trademark of Crestron Electronics, Inc.
FSR® is a registered trademark of FSR Inc.

Features and Benefits

SystemOne Recessed 10 Inch Fire-Rated Poke-Through Fittings

- The most dynamic FRPT system with the largest capacity available to meet all multimedia applications where power and voice/data are required
- Maintains concrete floor fire rating up to two hours
- Tamper-resistant recessed covers available
- Furniture feed cover available with (2) generous 2 inch NPT low voltage hubs and (2) 1 inch NPT power hubs
- Features ScrubShield® technology that exceeds UL514A scrubwater exclusion requirements
- Works with time and labor saving 10" concrete pre-pour tube

10 Inch FRPT with Accessories



FRPT Design

- Step down installation
- Flexible single or multi-service
- Recessed connections



Covers

- Durable die-cast aluminum cover
- 1,000 lb, static load rated cover
- Available as recessed or furniture feed
- Tamper-resistant recessed covers available
- Available in six architectural finishes



FRPT Chambers

- 4 inch deep access chamber
- 4.43 inch deep center device chamber
- Dividers to make up to 8 individual services
- Perimeter to perimeter wiring tunnel




Easy Mount Device Plates

- Multiple, open architecture mounting plates for power, data and AV
- 4 center gangs
- 2 full or 4 half independent perimeter gangs



Safety

- Low profile flange, 0.16 inch exceeds ADA requirements
- Two hide-away egress doors fold under cover while in use
- 180° opening of main door



Bottom Feed Plates

- 9 center chamber and 6 perimeter adaptable feed plates
- Center chamber ranges from 1/2" to 2-1/2"
- Perimeter ranges from 1/2" to 1-1/4"

SystemOne Recessed 10 Inch Core Hole Kits, for Use In Concrete Floors

10 Inch Fire-Rated Poke-Through

Hubbell SystemOne 10 Inch Recessed Floor Fitting with Installation Cover

Catalog Number

S1R10PTFIT

Approved for use in the City of Chicago with EMT and full blank bottom feed plates.



S1R10PTFIT

10 Inch Fire-Rated Poke-Through Kits

Kits include:


- (1) Hubbell SystemOne 10 inch recessed floor fitting (S1R10PTFIT)
- (2) Hubbell SystemOne 10 inch perimeter device mounting brackets (S1R10PSPREPBRKT)
- (4) Hubbell SystemOne 10 inch bottom center pass through plate (S1R10CBFPT)
- (3) Hubbell SystemOne 10 inch bottom perimeter blank plate (S1R10PBFBLANK)
- (1) Hubbell SystemOne 10 inch bottom perimeter ¾ inch plate (S1R10PBF075)
- (1) Hubbell SystemOne 10 inch perimeter divider (S1R10PERIMDIV)
- (1) Hubbell SystemOne 10 inch center divider (S1R10CENTERDIV)
- (1) Hubbell SystemOne 10 inch flange and universal cover assembly (S1R10CVRxx)

Cover Finish

- Brushed Aluminum
- Black Powder Coat
- Brushed Brass Plated
- Antique Bronze Plated
- Gray Powder Coat
- Satin Nickel Plated

Catalog Number

- S1R10PTALU**
- S1R10PTBLK**
- S1R10PTBRS**
- S1R10PTBRZ**
- S1R10PTGRY**
- S1R10PTNKL**



S1R10PTBRS

Pre-Wired 10 Inch Fire-Rated Poke-Through Kits

Kits include:

- (1) Hubbell SystemOne 10 inch recessed floor fitting (S1R10PTFIT)
- (2) 20A pre-wired receptacle sub-plates with 24 inch wire leads (S1R10PSPZ)
- (2) Hubbell SystemOne 10 inch perimeter device mounting brackets (S1R10PSPREPBRKT)
- (4) Hubbell SystemOne 10 inch bottom center pass through plate (S1R10CBFPT)
- (3) Hubbell SystemOne 10 inch bottom perimeter blank plate (S1R10PBFBLANK)
- (1) Hubbell SystemOne 10 inch bottom perimeter ¾ inch plate (S1R10PBF075)
- (1) Hubbell SystemOne 10 inch perimeter divider (S1R10PERIMDIV)
- (1) Hubbell SystemOne 10 inch center divider (S1R10CENTERDIV)
- (1) Hubbell SystemOne 10 inch flange and universal cover assembly (S1R10CVRxx)

Receptacles feature single circuit wiring

Cover Finish

- Brushed Aluminum
- Black Powder Coat
- Brushed Brass Plated
- Antique Bronze Plated
- Gray Powder Coat
- Satin Nickel Plated

Catalog Number

- S1R10PTZALU**
- S1R10PTZBLK**
- S1R10PTZBRS**
- S1R10PTZBRZ**
- S1R10PTZGRY**
- S1R10PTZNKL**



S1R10PTZBLK

Note: xx indicates finish options.

Recessed 10 Inch Covers

The 10 inch FRPT cover assembly unit includes solid cast aluminum construction and mounting hardware. Covers are recessed and available in a number of durable, yet beautiful finishes to match any décor. The flange height of 0.16 inch exceeds ADA requirement and suitable for use on any floor finish. All covers are UL514A, scrubwater compliant.



10 Inch Fire-Rated Poke-Through Covers

Finish	Recessed Cover Catalog Number	TR Recessed Cover* Catalog Number	Furniture Feed Cover** Catalog Number
Brushed Aluminum	S1R10CVRALU	S1R10CVRTRALU	S1R10FFCVRALU
Black Powder Coat	S1R10CVRBLK	S1R10CVRTRBLK	S1R10FFCVRBLK
Brushed Brass Plated	S1R10CVRBRS	S1R10CVRTRBRS	S1R10FFCVRBRS
Antique Bronze Plated	S1R10CVRBRZ	S1R10CVRTRBRZ	S1R10FFCVRBRZ
Gray Powder Coat	S1R10CVRGRY	S1R10CVRTRGRY	S1R10FFCVRGRY
Satin Nickel Plated	S1R10CVRNKL	S1R10CVRTRNKL	S1R10FFCVRNKL

Note: COVER LOAD RATING: 1,000 lb with 2x safety factor. Load applied through a 3" (76mm) dia. mandrel at the center of the cover. Rated for static loads only.

*Tamper-resistant covers ship with (1) S1RTR10BIT Torx-T10 bit.

** (2) 1" NPT plugs for power with (2) 1" to ¾" reducers and (2) 2" NPT plugs for Low Voltage.

SystemOne Recessed 10 Inch Sub-Plates and Bottom Feed Plates

Perimeter Plate Configurations

- Available in pre-wired duplexes or openings to accommodate third party AV devices
- Available in full or 1/2 gang plates



Perimeter Sub-Plates - Full Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(1) Style Line® decorator opening S1R10PSPD		(1) Duplex opening S1R10PSPJ		(1) 1.40" opening for simplex or 15A Twist-Lock® S1R10PSPJ	
(4) Extron® MAPP openings S1R10PSPC		(2) Extron® AAP openings S1R10PSPA		(1) 1.60" opening for 20A & 30A Twist-Lock® S1R10PSPG	

Perimeter Sub-Plates - 1/2 Gang*

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(2) 20A pre-wired receptacles; 24" lead; one circuit (Supplied with isolated ground sticker) S1R10PSPZ		(2) 20A pre-wired receptacles; 25 foot lead; one circuit (Supplied with isolated ground sticker) S1R10PSPZ25		(2) 20A pre-wired receptacles; 24" lead; one circuit (Supplied with isolated ground sticker). Marked with "Controlled" S1R10PSPZC		(2) 20A pre-wired receptacles; 25 foot lead; one circuit (Supplied with isolated ground sticker). Marked with "Controlled" S1R10PSPZ25C	
Blank cover plate S1R10PSPB		(1) Unit Hubbell iSTATION opening S1R10PSPF		(1) VGA/HDMI/DP opening S1R10PSPH		(1) XLR opening S1R10PSPQ	
(2) Extron® MAPP openings S1R10PSPV				Perimeter device bracket S1R10PSPREPBRKT			

Note: *Requires S1R10PSPREPBRKT.

10 Inch Bottom Feed Plates

1-Gang Center Bottom Feed Plates	Catalog Number
1/2 inch EMT Feed	S1R10CBF050
3/4 inch EMT Feed	S1R10CBF075
1 inch EMT Feed	S1R10CBF100
1 1/4 inch EMT Feed	S1R10CBF125
Blank	S1R10CBFBLANK
Pass through	S1R10CBFPT**
2-Gang Center Bottom Feed Plates	
1 1/2 inch EMT Feed	S1R10CBF150
2 inch EMT Feed	S1R10CBF200
2 1/2 inch EMT Feed	S1R10CBF250*
Perimeter Bottom Feed Plates	
1/2 inch EMT Feed	S1R10PBF050
3/4 inch EMT Feed	S1R10PBF075
1 inch EMT Feed	S1R10PBF100
1 1/4 inch EMT Feed	S1R10PBF125
Blank	S1R10PBFBLANK
Pass through	S1R10PBFPT**

Note: *Data/AV wiring only.


**Not approved for use in the City of Chicago.

Extron® is a registered trademark of Extron Electronics.


Crestron® is a registered trademark of Crestron Electronics, Inc.

FSR® is a registered trademark of FSR Inc.

10 Inch FRPT Bottom View



1-Gang Center Bottom Feed Plate



2-Gang Center Bottom Feed Plate



Perimeter Bottom Feed Plate

SystemOne Recessed 10 Inch Sub-Plates

Center Plate Configurations

- 1, 2, 3 and 4 Gang Device Plates
- Accept third party AV devices (i.e. Extron®, Crestron®, FSR®)
- Multi-gang NEMA spaced plates available



Center Sub-Plates - Single Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(1) Style Line® decorator opening		3 Unit Hubbell iSTATION opening		(1) Duplex opening		Blank cover plate	
S1R10CSPD		S1R10CSPL		S1R10CSPI		S1R10CSPB	
(1) XLR opening		(2) XLR openings		(1) 1.40" opening for simplex or 15A Twist-Lock®		(1) 1.60" opening for 20A & 30A Twist-Lock®	
S1R10CSPX		S1R10CSP2X		S1R10CSPJ		S1R10CSPG	
(1) VGA/HDMI/DP opening		(2) VGA/HDMI/DP openings		(4) Extron® MAPP openings		Ortronics® TracJack®/ Series II® opening	
S1R10CSPH		S1R10CSP2H		S1R10CSPC		S1R10CSPK	

Center Sub-Plates - Two Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(2) Style Line® decorator openings NEMA spacing		Blank cover plate		(1) 2.16" opening for 30A & 50A, 3-wire, straight blade receptacle		(4) Extron® APP openings	
S1R10CSPM		S1R10CSP2B		S1R10CSPE		S1R10CSPU	

Center Sub-Plates - Three and Four Gang

Description/Cat. No.	Sub-plate	Description/Cat. No.	Sub-plate
(3) Style Line® decorator openings NEMA spacing		(4) Style Line® decorator openings	
S1R10CSPT		S1R10CSPP	
(4) Blank cover plate		(4) Duplex openings	
S1R10CSPQ		S1R10CSPR	

Note: See page 21 for covers, 22 for bottom feed plates, 24 for accessories and 25 for data jacks and frames.

Extron® is a registered trademark of Extron Electronics.
TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.
Crestron® is a registered trademark of Crestron Electronics, Inc.
FSR® is a registered trademark of FSR Inc.

SystemOne Recessed 10 Inch Accessories and Replacement Parts



S1R10PPT



S1R10ADMTBK



S1R10CVRBRUSH



S1R10TUNNEL

10 Inch Accessories

Description	Catalog Number
Pre-pour tube, includes hardware.	S1R10PPT*
Abandonment plate, black finish.	S1R10ADMTBK
Center divider.	S1R10CENTERDIV
Perimeter divider.	S1R10PERIMDIV
Egress door brushes (1 Pair).	S1R10CVRBRUSH
Perimeter to perimeter wiring tunnel.	S1R10TUNNEL
Power junction box, 27.0 cubic inches; (1) 3/4 inch and (1) 1 inch EMT connector.	S1FRPTJB
Perimeter device bracket.	S1R10PSPREPBRKT

Note: *Not UL Listed.



S1R10CENTERDIV



S1R10FFDIV



S1R10PSPREPBRKT



S1FRPTJB



S1R10INTUMDIV

10 Inch Replacement Parts

Description	Catalog Number
Intumescent replacement divider.	S1R10INTUMDIV
Replacement furniture feed cover dividers (1 pair).	S1R10FFDIV
Replacement tamper-resistant Torx-T10 bit.	S1RTR10BIT*

Note: *Not UL Listed.

Capacity, Capability and Versatility



Fire-Rated Poke-Throughs

Pre-Pour Tubes

For Increased Installation Efficiency

- Creates a circular hole for Fire-Rated Poke-Through installation
- Includes adjustable mounting legs for easy leveling
- For use in poured concrete floors
- Single use

Hubbell SystemOne Pre-pour Tubes save installers time and money when it counts. Designed for second floor applications and above, pre-pour tubes are installed before the concrete slab is poured to provide correctly sized circular holes for Fire-Rated Poke-Through (FRPT) installation. Pre-pour tubes also ensure that the FRPT is placed exactly as specified on the print, while avoiding systems within the concrete floor's construction.

Pre-pour tube installation is quicker and more cost effective as compared to the time-consuming process of concrete core drilling. Additional time and scheduling must be considered for core drilling, along with the possible safety hazards of drilling on job sites. Prior to drilling, professionals take the precaution to use x-ray or ground-penetrating radar (GPR) technology to ensure the core drill does not damage embedded conduits, rebar or tensioned cables. Cutting a tensioned cable can endanger the installer and compromise the structural integrity of the slab. If there is an obstacle, the core drill location must be adjusted, which may impact furniture and powered cubicle layouts.

Hubbell pre-pour tubes are available in 4-, 6-, 8- and 10-inch sizes. They consist of extruded PVC segmented dove-tailed walls which easily slide together and are locked with pre-galvanized steel disks to maintain the tube's circular shape under the stress of the concrete pour. The pre-pour tubes can be use in corrugated steel decking or plywood forms. The mounting hardware provided allows for installation versatility. The PVC walls are then easily removed with hand tools, leaving a clean circular hole for FRPT installation.



Pre-Pour Tubes*

Includes all hardware

Diameter	Catalog Number
4 inches	S1R4PPT
6 inches	S1R6PPT
8 inches	S1R8PPT
10 inches	S1R10PPT



S1R4PPT



S1R6PPT

Fire-Rated Poke-Throughs



Additional Hubbell Products Compatible with Recessed FRPTs

Receptacles, GFCIs and USB Devices

Hubbell's line of receptacles include tamper-resistant that comply with NEC requirements that all 15A and 20A 125V receptacles shall be "tamper-resistant" in child care facilities and residencies.

White Commercial Spec. Grade Receptacles

Description	15A 125V	20A 125V
Style Line decorator, back and side wired	DR15WHI	DR20WHI
Tamper-Resistant Style Line decorator, back and side wired	DR15WHITR	DR20WHITR
Pre-wired Style Line decorator, back and side wired	DR15WHIP2	DR20WHIP2
Pre-wired Tamper-Resistant Style Line decorator, back and side wired	DR15WHITRP2	DR20WHITRP2
Orange Isolated Ground Style Line decorator, back and side wired	IG15DR	IG20DR
Duplex, back and side wired	BR15WHI	BR20WHI
Tamper-Resistant Duplex, back and side wired	BR15WHITR	BR20WHITR
Pre-wired Duplex, side wired	CR15WHIP2	CR20WHIP2
Pre-wired Tamper-Resistant Duplex, side wired	CR15WHITRP2	CR20WHITRP2
Orange Isolated Ground Duplex, back and side wired	IG15CR	IG20CR



DR15WHITR



IG20CR

White Commercial Protection Receptacles

Description	15A 125V	20A 125V
Tamper-Resistant USB Type A & C, 5A 5V USB outlets	USB15AC5W	USB20AC5W
AUTOGUARD self test, internal back wire clamp	GFRST15W	GFRST20W
Tamper-Resistant AUTOGUARD self test, internal back wiring clamp	GFTRST15W	GFTRST20W
Surge protection receptacles with light/alarm, 270J, 15kA peak current	HBL5262WSA	HBL5362WSA



USB15AC5W

White Hospital Grade Receptacles

Description	15A 125V	20A 125V
Style Line decorator, back and side wired	2172W	2182W
Tamper-Resistant Style Line decorator, back and side wired	2172WTRA	2182WTRA
Orange Isolated Ground Style Line decorator, back and side wired	–	IG2182
Duplex, back and side wired	8200WHI	8300WHI
Tamper-Resistant Duplex, back and side wired	8200WTRA	8300WTRA
Orange Isolated Ground Duplex, back and side wired	IG8200	IG8300



USB15AC5W



2182WTRA

White Hospital Grade Devices

Description	15A 125V	20A 125V
Tamper-Resistant USB Type A & C, 5A 5V USB outlets	USB8200AC5W	USB8300AC5W
AUTOGUARD self test, internal back wire clamp	GFRST82W	GFRST83W
Tamper-Resistant AUTOGUARD self test, internal back wiring clamp	GFTWRST82W	GFTWRST83W
Surge protection receptacles with light/alarm, 270J, 15kA peak current	HBL8262WSA	HBL8362WSA
Isolated Ground surge protection receptacle with light and alarm, 270 joules, 15kA peak current.	IG8262WSA	IG8362WSA



USB8200AC5W





Fire-Rated Poke-Throughs

Additional Hubbell Products Compatible with Recessed FRPTs

AV Connections




Hubbell iSTATION products provide a consistent and practical solution for delivering all types of connections where needed—in the wall, floor or table. The modular design allows users to custom configure plate solutions to their specific application.

Communication Outlet Frames, Decorator

			
2-Port	3-Port	4-Port	6-Port
NS612xx	NS613xx	NS614xx	NS616xx

xx = Color: **BK** (Black), **GY** (Gray), **I** (Ivory), **LA** (Light Almond), **W** (White)



3.5mm Stereo Jacks

			
Color	3.5mm to Screw Terminal	3.5mm Pass-Thru, F/F Coupler	3.5mm Pass-Thru, Gold, F/F Coupler
Black	SF35STBK	SF35FFBK	–
Office White	–	SF35FFOW	SF35GFFOW
White	–	SF35FFW	SF35GFFW

Data and AV Connectivity





Hubbell's category rated modular jacks provide leading edge performance to support today's Ethernet protocols, IP devices and high bandwidth AV applications. They install with a snap and provide quick and easy termination.

Data Jacks

		
Description	Category 6	Category 5e
Single pack	HXJ6xx	HXJ5Exx
24-pack	HXJ6xx24	HXJ5Exx24

xx = Color: **BK** (Black), **B** (Blue), **GL** (Gold), **GY** (Gray), **GN** (Green), **EI** (Ivory), **OW** (Office White), **OR** (Orange), **P** (Purple), **R** (Red), **W** (White), **Y** (Yellow); Gold and Purple available as single pack only



F-Type Connectors

			
F-Type Coupler F/F	F-Type Coupler F/F Gold	F-Type to RCA F/F Gold	F-Type Recessed
SFFxxX	SFFGyy	SFRFGyy	SFGRFyy

xx = Color: **B** (Black), **G** (Gray), **E** (Ivory), **W** (White); **SFFX** = Office White
yy = Color: **BK** (Black), **GY** (Gray), **EI** (Ivory), **OW** (Office White), **W** (White)



Note: Light Almond is the same color as Office White

Unloaded Modules

Keystone, 1U	
	
1-Port	2-Port
IM1K1xx	IM2K1xx

xx = Color: **BK** (Black), **EI** (Ivory), **GY** (Gray), **OW** (Office White), **W** (White)

HDMI 4K Connectors

	
1-Port	2-Port
NS801xx	NS802xx

xx = Color: **BK** (Black), **GY** (Gray), **I** (Ivory), **LA** (Light Almond), **W** (White)

USB Connectors

Pass-thru, female to female couplers		
		
Color	USB 3.0, A to A	USB 3.0, A to B
Black	SFUSBA3BK	SFUSBAB3BK
		
	USB 2.0, A to A	USB 2.0, A to B
Blue	SFUSBAAB	SFUSBABB
Office White	SFUSBAAOW	SFUSBABOW
White	SFUSBAAW	SFUSBABW

Hubbell SystemOne Recessed Fire-Rated Poke-Throughs

Hubbell Delivery Systems



Installation Efficiency eTour

This interactive, **360-degree** Installation Efficiency eTour walks users through ten different environments and identifies how and where Hubbell solutions can be used to efficiently deliver power, data, and AV—all while supporting fast installation.

Visit www.hubbell.com/wiringdevice-kellems/en > Resources to take the tour.



University



Library



Product Page

Available Literature




Hubbell SystemOne
Recessed Floor Boxes




Pre-Wired Raceway
Product Guide



Trench, Wall and Underfloor
Duct Products



Wire Basket Tray Systems



Aluminum Service Poles

HUBBELL®
Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems/en



Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 • Phone (800) 288-6000 • FAX (800) 255-1031

Printed in U.S.A. Specifications subject to change without notice.

® is a registered trademark of Hubbell Incorporated.

WLBD027 6/20